


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	2.40 ohms $\pm$ 10%
D.C. RESISTANCE	4-5 @20°C	1.55 ohms $\pm$ 10%
D.C. RESISTANCE	8-9 @20°C	0.420 ohms $\pm$ 10%
D.C. RESISTANCE	7-10 @20°C	0.570 ohms $\pm$ 10%
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	600uH $\pm$ 10%
SATURATION CURRENT	20% rolloff from initial	1.75A
LEAKAGE INDUCTANCE	1-2 tie(4+5, 7+8+9+10), 100kHz, 100mVAC, Ls	15uH typ., 25uH max.
DIELECTRIC	2-10 tie(1+4, 7+9), 4500VAC, 1 second	4500VAC, 1 minute
DIELECTRIC	2-4 1250VAC, 1 second	1000VAC, 1 minute
URNS RATIO	(2-1):(10-7)	4:1, $\pm$ 1%
URNS RATIO	(2-1):(9-8)	4:1, $\pm$ 1%
URNS RATIO	(2-1):(4-5)	5.6:1, $\pm$ 1%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC61558-2-17:
- Reinforced insulation for a primary circuit at a working voltage of 400VDC.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
		Method: Tray PKG-0733 www.we-online.com/midcom		Angles: $\pm$ 1° Decimals: $\pm$.005 [.13] Fractions: $\pm$ 1/64 Footprint: $\pm$.001 [.03]	TRANSFORMER	750813144
6B	3/11	SEE REVISION SHEET FOR	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750813144	SPECIFICATION SHEET 1 OF 1
6A	1/11					