



SUGESTED MATING TAB




- 1 MATERIAL: 1/2 HARD BRASS OR NICKEL PLATED STEEL.
- 2 NO BURRS PERMISSIBLE AT HOLE.
- △ 3 MUST BE FLAT WITHIN 0.076 MM OVER THIS LENGHT.
- 4 TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 107°C.
- 5 HOLE MUST BE SYMMETRICAL ABOUT TAB CENTER WITHIN 0.076 MM.
- △ 6 TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



LOGOTIPO E CODIGO DO PAÍS PRODUTOR
LOGO AND MANUFACTURING COUNTRY CODE.



PARA LINGUETA ESPESSURA 0,8mm
FOR 0,8mm TAB THK.



1- WIRE RANGE >1,00 / 2,50 mm².
INSULATION DIA. RANGE Ø2,70 / 3,70 mm.



OBSOLETE	ESTANHADO/TINNED	LATÃO/BRASS	1380089-2
	NU/NONE	LATÃO/BRASS	1380089-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H.C.CANTERI CHK W.L.STEFANI APVD -	15AUG00 15AUG00 15AUG00 -		 TE Connectivity				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-37058		NAME POSITIVE LOCK MKIII, L.I.F. .250 SERIES RECEPT. -			
		0 PLC ±- 1 PLC ±- 2 PLC ±0,25 3 PLC ±- 4 PLC ±- ANGLES ±1° FINISH		APPLICATION SPEC -		SIZE A2	CAGE CODE 00779	DRAWING NO C=1380089	RESTRICTED TO -
MATERIAL SEE TABLE		SEE TABLE		WEIGHT -		CUSTOMER DRAWING			
						SCALE 10:1	SHEET 1 OF 1	REV C4	