




TYPE 1





TYPE 2





TYPICAL LETTERING

TYPE 3



TYPICAL LETTERING

TYPE 4



TYPICAL LETTERING

REDUCER ADAPTER SLEEVES

CONDUCTOR		CATALOG NO.	O.D. MAX.	'B'	TYPE				'B'
FROM	TO				1	2	3	4	
4/0	#6 STR. (.184 DIA.) #8 STR. (.146 DIA.) #6 SOL. (.162 DIA.)	Y286CR	.534	1.75	X	X		X	1.48
4/0	#5 STR. (.207 DIA.) OR #4 SOL. (.204 DIA.)	Y285CR	.534	1.75	X	X	X	X	1.48
4/0	#4 SOL. (.204 DIA.)	Y284WR	.534	1.75	X	X	X	X	1.48
4/0	#4 STR. (.231 DIA.) OR 40 kcmil	Y284CR	.534	1.75	X	X	X	X	1.48
4/0	#3 STR. (.261 DIA.) OR #2 SOL. (.258 DIA.)	Y283CR	.534	1.75	X	X	X	X	1.48
4/0	#2 STR. (.291 DIA.) OR 80 kcmil	Y282CR	.534	1.75	X	X	X	X	1.48
4/0	#1 STR. (.330 DIA.)	Y281CR	.534	1.75	X	X	X	X	1.48
4/0	1/0 STR. (.373 DIA.)	Y2825R	.534	1.75		X	X	X	
4/0	2/0 STR. (.416 DIA.)	Y2826R	.534	1.75		X	X	X	
250 kcmil	#4 STR. (.231 DIA.)	Y294CR	.582	1.62	X	X			1.48
250 kcmil	#2 STR. (.291 DIA.)	Y292CR	.582	1.62	X	X			1.48
250 kcmil	#1 STR. (.330 DIA.)	Y291CR	.582	1.62	X			X	1.48
250 kcmil	1/0 STR. (.373 DIA.)	Y2925R	.582	1.62	X			X	1.48
250 kcmil	2/0 STR. (.416 DIA.)	Y2926R	.582	1.62	X			X	1.48
250 kcmil	4/0 STR. (.528 DIA.)	Y2928R	.592	1.62		X	X		
300 kcmil	#2 STR. (.291 DIA.)	Y302CR	.637	2.00				X	
300 kcmil	#4 STR. (.232 DIA.)	Y304CR	.637	2.00				X	
300 kcmil	1/0 STR. (.373 DIA.)	Y3025R	.637	2.00				X	
300 kcmil	2/0 STR. (.416 DIA.)	Y3026R	.637	2.00				X	
300 kcmil	3/0 STR. (.470 DIA.)	Y3027R	.637	2.00				X	
300 kcmil	4/0 STR. (.528 DIA.)	Y3028R	.637	2.00		X	X		
300 kcmil	250 kcmil (.575 DIA.)	Y3029R	.647	2.00				X	
350 kcmil	1/0 STR. (.373 DIA.)	Y3125R	.687	2.00	X				1.82
350 kcmil	2/0 STR. (.416 DIA.)	Y3126R	.687	2.00	X		X		1.82
350 kcmil	4/0 STR. (.528 DIA.)	Y3128R	.687	2.00		X			
350 kcmil	250 kcmil (.575 DIA.)	Y3129R	.687	2.00				X	
400 kcmil	3/0 STR. (.470 DIA.)	Y3227R	.749	2.12		X	X		
400 kcmil	4/0 STR. (.528 DIA.)	Y3228R	.749	2.12		X	X		
400 kcmil	250 kcmil (.575 DIA.)	Y3229R	.749	2.12		X	X		
400 kcmil	300 kcmil (.630 DIA.)	Y3230R	.749	2.12		X	X		
400 kcmil	350 kcmil (.681 DIA.)	Y3231R	.757	2.12				X	
500 kcmil	1/0 STR. (.373 DIA.)	Y3425R	.821	2.50	X				
500 kcmil	2/0 STR. (.416 DIA.)	Y3426R	.821	2.50	X				
500 kcmil	3/0 STR. (.470 DIA.)	Y3427R	.821	2.50	X			X	
500 kcmil	4/0 STR. (.528 DIA.)	Y3428R	.821	2.50				X	
500 kcmil	250 kcmil (.575 DIA.)	Y3429R	.821	2.50				X	
500 kcmil	300 kcmil (.630 DIA.)	Y3430R	.821	2.50		X		X	
500 kcmil	350 kcmil (.681 DIA.)	Y3431R	.821	2.50				X	
500 kcmil	400 kcmil (.728 DIA.)	Y3432R	.821	2.50		X	X		
600 kcmil	400 kcmil (.728 DIA.)	Y3632R	.910	2.69		X	X		
600 kcmil	500 kcmil (.814 DIA.)	Y3634R	.910	2.69		X	X		
750 kcmil	400 kcmil (.728 DIA.)	Y3932R	1.017	2.88		X	X		
750 kcmil	500 kcmil (.814 DIA.)	Y3934RG1	1.017	2.25				X	
750 kcmil	600 kcmil (.893 DIA.)	Y3936RG1	1.017	2.25				X	
750 kcmil	650 kcmil (.929 DIA.)	Y3937RG2	1.017	2.25		X	X		
1000 kcmil	750 kcmil (.998 DIA.)	Y4439R	1.159	3.00		X	X		
1250 kcmil	1000 kcmil (1.132 DIA.)	Y4544R	1.296	3.19		X			
1750 kcmil	600 kcmil (.893 DIA.)	Y3936R	1.017	2.88		X	X		
2000 kcmil	1500 kcmil (1.412 DIA.)	Y4846R	1.649	3.44		X			
750 kcmil	500 kcmil (.814 DIA.) 650 kcmil (.929 DIA.)	Y3934R Y3937R	1.017	2.88		X	X	X	
700 kcmil	3/0 STR. (.470 DIA.)	Y3827R	.971	2.81		X			
600 kcmil	350 kcmil (.681 DIA.)	Y3631R	.910	2.69		X			

CONDUCTOR		CATALOG NO.	O.D. MAX.	'B'	TYPE			
FROM	TO				1	2	3	4
#6	#14 STR. (.073 DIA.)	Y6C14R	.185	1.12			X	X
#6	#10 STR. (.116 DIA.)	Y6C10R	.185	1.12			X	X
#4	#14 STR. (.073 DIA.)	Y4C14R	.233	1.12			X	X
#4	#10 STR. (.116 DIA.)	Y4C10R	.233	1.12			X	X
#4	#8 STR. (.146 DIA.)	Y4C8CR	.233	1.12			X	X
#2	#14 STR. (.073 DIA.)	Y2C14R	.293	1.25			X	X
#2	#10 STR. (.116 DIA.)	Y2C10R	.293	1.25			X	X
#2	#8 STR. (.146 DIA.)	Y2C8CR	.293	1.25			X	X
#2	#6 STR. (.184 DIA.)	Y2C6CR	.293	1.25			X	X
#2	#4 STR. (.232 DIA.)	Y2C4CR	.293	1.25			X	X
#2	#4 SOL. (.204 DIA.)	Y2C4WR	.293	1.25			X	
#1	#6 STR. (.184 DIA.)	Y1C6CR	.345	1.38			X	X
#1	#4 STR. (.232 DIA.)	Y1C4CR	.345	1.38			X	X
1/0	#8 STR. (.146 DIA.)	Y258CR	.380	1.38	X	X	X	X
1/0	#6 STR. (.184 DIA.)	Y256CR	.380	1.38	X	X	X	X
1/0	#4 STR. (.232 DIA.)	Y254CR	.380	1.38	X	X	X	X
1/0	#2 STR. (.291 DIA.)	Y252CR	.380	1.38		X	X	X
2/0	#6 STR. (.184 DIA.)	Y266CR	.430	1.50		X	X	X
2/0	#4 STR. (.232 DIA.)	Y264CR	.430	1.50		X	X	X
2/0	#2 STR. (.291 DIA.)	Y262CR	.430	1.50		X	X	X
2/0	#1 STR. (.330 DIA.)	Y261CR	.430	1.50		X	X	X
2/0	1/0 STR. (.373 DIA.)	Y2625R	.436	1.50		X	X	
3/0	1/0 STR. (.373 DIA.)	Y2725R	.477	1.50		X	X	X

MATERIAL:

COPPER

FINISH:

TIN PLATED

REDUCER ADAPTER SLEEVES	
CAT. NO. Y-R & Y-RL (TABLE)	SCALE
DRAWN D.F. 6-16-55	CHECKED D.H. 6-23-55
FRAMATOME CONNECTORS USA INC. BURNDY ELECTRICAL	
DRAWING NO.	REV.
SD16040	18
MANCHESTER, NH 03108 U.S.A. 1-800-346-4175	

18	1/10/00	ADD CAT. # Y3631R TO TABLE PER ECO 5396.	DB	PL
MARK	DATE	REVISION	BY	C.K.D.