

CS1500 90W, High-efficiency PFC w/ LLC Resonant Converter Reference Design

Features

- ❑ Universal Input
 - Mains Range: 90~265 VAC
 - Line Frequency: 45~65 Hz
- ❑ Rated Output Specification: 19 V, 90 W
- ❑ EN6100-3-2 Class-D Compliance
- ❑ Efficiency: 91% @ 90 W, 230 VAC
- ❑ Low No-load Power Dissipation
- ❑ Low PFC Component Count
- ❑ Board Dimension: 61 mm x 135 mm


General Description

The CRD1500-90WLLC circuit has two stages: a digitally controlled front-end PFC and a resonant LLC converter. The CS1500 is a high-performance power factor correction (PFC) controller for universal AC input that uses a proprietary digital algorithm with variable on-time, variable frequency, & DCM, which ensures unity power factor.

The resonant LLC converter uses the L6599A controller in the second stage.

To get the complete data sheet, please visit:

www.cirrus.com/PFCdatasheets/CRD1500-90WLLC-41



Actual Size:
61mm x 135mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cirrus Logic:](#)

[CRD1500-90WLLC](#)