


Features

- Low Saturation Voltage $V_{CE(sat)}=1.5V$ typ. ($I_C=30A$)
- High Speed SW $t_f=120ns$ typ. ($I_C=30A$)

Package


TO-3PF



Applications

- Current Resonance Inverter Switching

Equivalent circuit



Absolute maximum ratings

($T_a=25^{\circ}C$)

Characteristic	Symbol	Rating	Unit
Collector to Emitter Voltage	V_{CES}	600	V
Gate to Emitter Voltage	V_{GES}	± 30	V
Continuous Collector Current	I_C	30	A
Pulsed Collector Current	$I_C(\text{pulse})$ ¹⁾	100	A
Maximum Collector-emitter dv/dt	dv/dt ²⁾	5	V/ns
Maximum Power Dissipation	P_C	60 ($T_c=25^{\circ}C$)	W
Thermal Resistance IGBT	θ_{j-c}	2.08	$^{\circ}C/W$
Junction Temperature	T_j	150	$^{\circ}C$
Storage Temperature	T_{stg}	$-55 \sim 150$	$^{\circ}C$

1) $PW \leq 100\mu sec.$, Duty cycle $\leq 1\%$


2) $T_c \leq 125^{\circ}C$, See Fig.1

Electrical characteristics
●IGBT


(Ta=25°C)

Characteristic	Symbol	Test Conditions	Limits			Unit
			MIN.	TYP.	MAX.	
Collector to Emitter Breakdown Voltage	V(BR)CES	IC=100μA, VGE=0V	600			V
Gate to Emitter Leakage Current	IGES	VGE=±30V			±500	nA
Collector to Emitter Leakage Current	ICES	VCE=600V, VGE=0V			100	μA
Gate Threshold Voltage	VGE(th)	VCE=10V, IC=1mA	3		6	V
Collector to Emitter Saturation Voltage	VCE(sat)	VGE=15V, IC=30A		1.5	1.7	V
Collector to Emitter Saturation Voltage	VCE(sat)	VGE=15V, IC=50A		1.8		V
Input Capacitance	Cies	VCE=20V VGE=0V f=1MHz		2500		pF
Output Capacitance	Coes			150		
Reverse Transfer Capacitance	Cres			80		
Gate charge	Qgate	VCE=300V IC=30A VGE=15V		65		nC
Gate to Collector Charge	Qgc			20		
Gate to Emitter Charge	Qge			20		
Turn-On Delay Time	td(on)	VCE=300V, IC=30A VGE=15V, RG=39Ω L=100uH, Tc=25°C See Fig.1		100		ns
Rise Time	tr			80		
Turn-Off Delay Time	td(off)			300		
Fall Time	tf			120		
Turn-On Delay Time	td(on)	VCE=300V, IC=30A VGE=15V, RG=39Ω L=100uH, Tc=125°C See Fig.1		100		ns
Rise Time	tr			100		
Turn-Off Delay Time	td(off)			300		
Fall Time	tf			200		

Fig.1 Switching Time Test Method









(a) Test Circuit









(b) Waveforms

Characteristic Curves




The information included herein is believed to be accurate and reliable. However, SANKEN ELECTRIC CO., LTD assumes no responsibility for its use ; nor for any infringements of patents or other rights of third parties that may result from its use.

Characteristic Curves



The information included herein is believed to be accurate and reliable. However, SANKEN ELECTRIC CO., LTD assumes no responsibility for its use ; nor for any infringements of patents or other rights of third parties that may result from its use.

Characteristic Curves




The information included herein is believed to be accurate and reliable. However, SANKEN ELECTRIC CO., LTD assumes no responsibility for its use ; nor for any infringements of patents or other rights of third parties that may result from its use.

FGM623S

Jul. 2010

Outline

TO-3PF



Wight Approx : 6.5g

The information included herein is believed to be accurate and reliable. However, SANKEN ELECTRIC CO., LTD assumes no responsibility for its use ; nor for any infringements of patents or other rights of third parties that may result from its use.