

## TM-27 Support Brace Lifting Lid



### ■ Specification

| Model No. | Type  | Unlock Force N(kgf) | Net Weight(g) | Code No. |
|-----------|-------|---------------------|---------------|----------|
| TM-27-L   | Left  | Approx.150 (15.3)   | 48            | 5007     |
| TM-27-R   | Right | Approx.150 (15.3)   | 48            | 5008     |

### ■ Parts List

| No. | Part Name        | Material | Finish          | Quantity |
|-----|------------------|----------|-----------------|----------|
| 1・2 | Arm (A) (B)      | SPCC     | Cr              | 1 Each   |
| 3・4 | Bracket (A) (B)  |          |                 | 1 Each   |
| 5   | Plate Spring (A) | SUP      | —               | 1        |
| 6   | Plate Spring (B) |          |                 | 1        |
| 7   | Rivet (A)        | C2700    | Sn-Co(Cr Color) | 2        |
| 8   | Rivet (B)        |          |                 | 1        |
| 9   | Washer           | SPCC     | Zn              | 1        |
| 10  | Nylon Washer     | PA       | Primary Color   | 2        |
| 11  | Ball             | S        | —               | 2        |

### ■ Characteristic


Small and no wide space is needed to install.

### ■ Note

Beveling must be processed to the attached side when using countersunk screws or rivets.

### ■ Application

Measuring instruments /  
Telecommunication devices



The figure shows left side fixing type.

## TM-59 Support Brace Lifting Lid



### ■ Specification

| Model No. | Type  | Unlock Force N(kgf) | Net Weight(g) | Code No. |
|-----------|-------|---------------------|---------------|----------|
| TM-59-L   | Left  | Approx.34.3 (3.5)   | 32.5          | 5049     |
| TM-59-R   | Right | Approx.34.3 (3.5)   | 32.5          | 5050     |

### ■ Parts List

| No. | Part Name            | Material | Finish          | Quantity |
|-----|----------------------|----------|-----------------|----------|
| 1・2 | Arm (A)・(B)          | SPCC     | Cr              | 1 Each   |
| 3・4 | Bracket (A)・(B)      |          |                 | 1 Each   |
| 5・6 | Plate Spring (A)・(B) | SUS301   | —               | 1 Each   |
| 7   | Rivet (A)            | C2700    | Sn-Co(Cr Color) | 1        |
| 8   | Rivet (B)            |          |                 | 2        |
| 9   | Washer               | SPCC     | Zn              | 1        |
| 10  | Nylon Washer         | PA       | Primary Color   | 2        |
| 11  | Ball                 | S        | —               | 2        |

### ■ Characteristic


An instant stopper is fixed at the center part of the brace.

### ■ Note

Beveling must be processed to the attached side when using countersunk screws or rivets.

### ■ Application

Cabinets / Furniture



The figure shows left side fixing type.