





PART NUMBER	ITEM ① BODY	ITEM ② CRIMP SLEEVE
142-0003-801	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN
142-0003-806	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	COPPER NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN



NOTES:

1. SPECIFICATIONS:

CABLE ACCEPTABILITY: RG 188/U, RG 316/U, RG 161/U
 RG 174/U, RG 179/U, RG 187/U
 CABLE HEX CRIMP SIZE: .128
 CABLE RETENTION: 20 LBS
 IMPEDANCE: 50 OHMS

DRAWING NO. C - 142-0003-801/810	
0	REVISIONS
ENGINEERING RELEASE	
1	8-25-98 R H K T R ECN 45822

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED
 PER ANSI Y 14.5M - 1982

"μSTATION"

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED	DRAWN BY KAS	DATE 5/19/98	 Cinch Connectivity Solutions 299 Johnson Ave Ste 100 Waseca, MN 56093 1-800-247-8256	
DECIMALS .XX	CHECKED BY KAS	DATE 8-27-98		
.XXX -- .003	APPROVED BY TAK	DATE 9-9-98	TITLE CABLE TERMINATION, .068 END LAUNCH, RG 316	
MATL	APPROVED BY RJB	DATE 9-11-98		
FINISH	RELEASE DATE		CODE NO. C - 142-0003-801/810	DRAWING NO. C - 142-0003-801/810
SCALE 10:1			U/M INCH	SHEET 2 OF 2