

MN657011H

Low Power 8-Bit, 3-Channel CMOS D/A Converter for Image Processing

■ Overview

The MN657011H is an 8-bit, 3-channel CMOS digital-to-analog converter with a maximum conversion rate of 20 MSPS.

It is a 3.5 volt version of the MN65701FHP.


■ Features

- Maximum conversion rate: 20 MSPS (min.)
- Linearity error: ± 0.2 LSB (typ.)
- Differential linearity error: ± 0.2 LSB (typ.)
- Power supply voltage: 3.5 ± 0.1 V
- Full scale current: 4 mA (typ.)
- Power consumption: 84 mW (typ.) ($f_{CLK}=15$ MHz)


■ Applications

- Digital television
- Digital video equipment
- Digital image processing equipment

■ Pin Assignment



■ Block Diagram



■ Pin Descriptions

Pin No.	Symbol	Function Description
1	DC4	C (chroma) digital input
2	DC3	C (chroma) digital input
3	DC2	C (chroma) digital input
4	DC1	C (chroma) digital input (MSB)
5	CLK	Sampling clock
6	DV _{SS}	Ground for digital circuits
7	N.C.	No connection
8	DV _{DD}	Power supply for digital circuits
9	DY8	Y (luminance) digital input (LSB)
10	DY7	Y (luminance) digital input
11	DY6	Y (luminance) digital input
12	DY5	Y (luminance) digital input
13	DY4	Y (luminance) digital input
14	DY3	Y (luminance) digital input
15	DY2	Y (luminance) digital input
16	DY1	Y (luminance) digital input (MSB)
17	N.C.	No connection
18	N.C.	No connection
19	AV _{DD}	Power supply for analog circuits
20	AV _{DD}	Power supply for analog circuits
21	I _{REF}	Full scale adjustment resistor
22	V _{REF}	Reference voltage input
23	COMP	Phase compensation
24	VIB	Capacitor connection
25	I _{OY}	Y signal analog current output
26	N.C.	No connection
27	I _{OU}	U signal analog current output
28	N.C.	No connection
29	I _{OV}	V signal analog current output
30	N.C.	No connection
31	AV _{SS}	Ground for analog circuits
32	AV _{SS}	Ground for analog circuits
33	N.C.	No connection
34	N.C.	No connection
35	N.C.	No connection
36	N.C.	No connection
37	N.C.	No connection
38	N.C.	No connection
39	N.C.	No connection
40	NTCS	Format selection (two's complement/binary) for C (chroma) signal
41	UVSEL	U/V signal discrimination for C (chroma) signal
42	DV _{SS}	Ground for digital circuits

■ Pin Descriptions (continued)

Pin No.	Symbol	Function Description
43	N.C.	No connection
44	DV _{DD}	Power supply for digital circuits
45	DC8	C (chroma) digital input (LSB)
46	DC7	C (chroma) digital input
47	DC6	C (chroma) digital input
48	DC5	C (chroma) digital input

■ Absolute Maximum Ratings $T_a=25^\circ C$

Parameter	Symbol	Rating	Unit
Power supply voltage for digital circuits	DV _{DD}	-0.3 to +7.0	V
Power supply voltage for analog circuits	AV _{DD}	-0.3 to +7.0	V
Input voltage	V _I	DV _{SS} -0.3 to DV _{DD} +0.3	V
Output voltage	V _O	AV _{SS} -0.3 to AV _{DD} +0.3	V
Operating ambient temperature	T _{opr}	-20 to +70	°C
Storage temperature	T _{stg}	-55 to +125	°C


■ Recommended Operating Conditions $V_{DD}=AV_{DD}=DV_{DD}=3.5V$, $V_{SS}=AV_{SS}=DV_{SS}=0V$, $T_a=25^\circ C$

Parameter	Symbol	min	typ	max	Unit
Power supply voltage	V _{DD}	3.4	3.5	3.6	V
Reference voltage	V _{REF}	1.5	1.9	3.5	V
Reference resistance	R _{REF}		820		Ω
External compensation capacitor	C _{COMP}	0.33	1.0	3.3	μF
Output load resistance	R _{OUT}		200		Ω
Digital input voltage	"H" level	V _{IH}	V _{DD} × 0.5	V _{DD}	V
	"L" level	V _{IL}	V _{SS}	V _{DD} × 0.16	V
Clock	"H" level pulse width	t _{WH}	15		ns
	"L" level pulse width	t _{WL}	15		ns

■ Electrical Characteristics $DV_{DD}=AV_{DD}=3.5V$, $DV_{SS}=AV_{SS}=0V$, $T_a=25^\circ C$

Parameter	Symbol	Conditions	min	typ	max	Unit
Power supply voltage	I _{DD}	V _{DD} =3.5V, f _{CLK} =15MHz R _{OUT} =200Ω, Output amplitude = 0.8V T=25°C		24	40	mA
Resolution	RES			8		bit
Linearity error	E _L	V _{DD} =3.5V, R _{OUT} =200Ω		±0.2	±0.5	LSB
Differential linearity error	E _D	R _{REF} =820Ω		±0.2	±0.5	LSB
Full scale current	I _{FS}	V _{REF} =1.9V		4		mA
Setup time	t _S		10			ns
Hold time	t _H		10			ns
Settling time	t _{ST}	V _{DD} =3.5V, R _{OUT} =200Ω		30	50	ns
Maximum conversion speed	F _{C(max.)}	R _{REF} =820Ω V _{REF} =1.9V	20	33		MSPS
Analog output delay time	t _d			10		ns

■ Timing Chart




t_d : Analog output delay time

t_{ST} : Settling time

■ Package Dimensions (Unit:mm)

QFH048-P-0707



Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

Please read the following notes before using the datasheets

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.