




D


C

B

A



PCB Layout, Component side



SPECIFICATION

Mating Cycles	500
Filter type	C
Capacitance	1000pF ± 20%
Working Voltage	100V
Current rating	7,5A
Insulation Resistance	>1GΩ

Minimum Insertion Loss

FREQUENCY (MHz)	ATTENUATION dB
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

09641247237	M3
09641247236	4-40UNC-2B
Part number	Nut thread

			Dat.	Name		
			Detail.	8- JUL -02		CV
			Insp.			
			Stand.			
31864	23/01/04	AF	HARTING EURL F-95972 Paris			
31058	8- JUL -02	CV				
Mod.	Dat.	Name				

D-Sub, male, angled, 9 Poles, turned solder pin tin plated shell and metal bracket with nut		Mo?Ms lab/ Scale
		1.5:1
TB 0964124723x		Blatt/ Page
		3 / 4
Sub.		