




1	2	3	4	5
---	---	---	---	---



PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING: UL94-V0
COLOR: WHITE
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 500 MATING CYCLES


ENVIRONMENTAL
OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 125 VAC
INSULATION RESISTANCE: >500 MΩ
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
 CERTIFIED: E324776

SOLDERING
JEDEC LEAD FREE WAVE SODLERING PROCESS

PACKAGING
TRAY

RoHS Compliant				PROJECTION: 	GENERAL TOLERANCE .X = $\pm$ 0.2 .XX = $\pm$ 0.15	 DESCRIPTION: 45° ENTRY SHIELDED 8P8C MODULAR JACK REVERSE MATAL POST TAIL WERI PART NO: 615 008 145 121 SIZE A4		
G								
F								
E	03-APR-14	DRAWING UPDATE	QL					
D	03-JAN-14	UL & TEMP UPDATE	QL					
C	07-JUL-10	NEW MEASURES	GG	APPROVAL: RJ	UNIT: MM			
B	08-OCT-09	NEW DRAW	JP		SCALE:			
A	23-FEB-09	PDF	JP		SHEET: 1/1			
REV	DATE	FILE	BY		DRAW:			