







ORDERING INFORMATION

SERIES	D	B	V	25	P	3	64	G	T	X	XXX	LF	LEAD FREE
SHELL SIZE	E,A,B,C,D												SPECIAL CODES
PANEL MOUNTING OPTIONS													DIMPLES
BLANK-STANDARD													X-ON MALE CONNECTORS ONLY
V-FEM. SCREW LOCK (UNC)													SHELL PLATING
N-FEM. SCREW LOCK M3													BLANK-ZINC (Cr+3)
S-SPACER RIVETTED TO SHELL													T-STD. TIN Over Cu
L-CLINCH NUT (M3)													PCB MOUNTING OPTIONS
O-CLINCH NUT (UNC)													BLANK-STANDARD
													G-HARPOON
NO. OF CONTACTS													CONTACT PLATING
09,15,25,37,50													64 - 200 MATING CYCLES
CONTACTS													65 - 500 MATING CYCLES
P - PIN													
S - SOCKET													
TERMINATION TYPE													
3-STRAIGHT SPILL													
4-WIRE WRAP													


"This LF product meets European Union Directives and other country regulations as described in GS-22-008"

The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board.

Packaging as per GS-14-920




EXTENDED FEMALE SCREW LOCK WITH SPACER




ORD CODE -8630-01-062

SPACERS RIVETTED TO SHELL



PREFIX:- S

MALE SCREW LOCK



ORD CODE:-

8630- 05(E.A.B.C.)
8630-03 D SHELL FEMALE
8630-15 D SHELL MALE
8630-04 E,A,B,C SHELL
WITH METAL HOOD

FOR 440 UNC 2A THREADED ADD UNC
TO THE CORRESPONDING ORD. CODE.

mat'l. code

SEE NOTE 4

surface

ISO 1302

tolerance

ISO 406 ISO 1101

projection

MM

product family

title

D- SUB S/S W/W CONNECTOR
(WITH ASSEMBLY OPTIONS)

dwg no

sheet 1 of 1

size

C-DSUB-0065

A3

type

Product

Customer

Drawing

sheet

revision

H

index

sheet

1