



Magnecraft & Struthers-Dunn
Your Contact for Industrial Relays

SECTION 1

SOCKET COMPATIBLE AND
FLANGE MOUNTED RELAYS
1 TO 30 AMPERES

SOCKET COMPATIBLE & FLANGE MOUNT RELAYS

RELAY SERIES



FEATURES

- 0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS
- FLAG INDICATOR
- L.E.D. STATUS LAMP
- PUSH BUTTON
- FINGER GRIP COVER
- I.D. TAG/WRITE LABEL
- OPTIONAL FLANGE AND DIN ADAPTERS
- UL LISTED WHEN USED WITH 70-781D-1 SOCKET

- 0.100 SOLDER PLUG-IN TERMINALS
- HERMETICALLY SEALED VACUUM BAKED AND DRY NITROGEN FILLED
- GRAY LACQUER FINISH OVER STEEL ENCLOSURE
- MEETS UL STANDARD FOR CLASS 1 DIVISION 2 HAZARDOUS LOCATIONS
- UL LISTED WHEN USED WITH 70-461-1 SOCKET

- 0.100 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS
- FLAG INDICATOR
- L.E.D. STATUS LAMP
- PUSH BUTTON WITH LOCK DOWN DOOR
- FINGER GRIP COVER
- I.D. TAG/WRITE LABEL OPTIONAL
- FLANGE AND DIN ADAPTERS AVAILABLE
- UL LISTED WHEN USED WITH 70-461-1 SOCKET

CONTACT DATA

CONTACT CONFIGURATION:

SPDT

4PDT

DPDT, 4PDT

CONTACT MATERIAL:

SILVER ALLOY,
GOLD FLASHED

SILVER, GOLD OVERLAY (1 AMP)
SILVER, GOLD FLASHED (3 AMPS)
SILVER ALLOY (5 AMPS)

SILVER, GOLD OVERLAY (3 AMPS)
SILVER, GOLD FLASHED (3 AMPS)
SILVER ALLOY, GOLD FLASHED (10 AMPS)

MAX. CONTACT RATING:

15 AMPS, 110/120 VAC 50/60Hz
15 AMPS, 28 VDC
12 AMPS, 220/277 VAC 50/60Hz

1 AMP, BIFURCATED
120/240 VAC/28 VDC
3 AMPS, 120/240 VAC/28 VDC
5 AMPS, 120/240 VAC/28 VDC

3 AMPS, BIFURCATED,
120/240VAC/28 VDC
3 AMPS, 120/240 VAC/28 VDC
10 AMPS, 120/240 VAC/28 VDC
8 AMPS, 220/277 VAC 50/60Hz

COIL DATA

STANDARD VOLTAGE

AC:

DC:

6,12, 24,120, 220/230, 240 VAC
6,12, 24, 48,110 VDC

6,12, 24,120, 240 VAC
6,12, 24, 48,110 VDC

6,12, 24,120, 220/230, 240 VAC
6,12, 24, 48,110 VDC

NOMINAL COIL POWER

VA: (VAC)

WATTS: (VDC)

0.9 VA
0.7 WATTS

1.2 VA
0.9 WATTS

1.2 VA
0.9 WATTS

INSULATION SYSTEM PER
UL STANDARD 1446

CLASS "B" (130°C)

CLASS "B" (130°C)

CLASS "B" (130°C)

GENERAL DATA

AMBIENT TEMPERATURE

OPERATING:

-40°C TO +70°C

-45°C TO +70°C

-40°C TO +70°C

STORAGE:

-40°C TO +100°C

-60°C TO +130°C

-40°C TO +105°C

DIELECTRIC STRENGTH:
(COIL TO FRAME)

1500 V rms

1240 V rms

1500 V rms

LIFE EXPECTANCY

ELECTRICAL:

MECHANICAL:

150,000 OPERATIONS
10,000,000 OPERATIONS

100,000 OPERATIONS
10,000,000 OPERATIONS

200,000 OPERATIONS
10,000,000 OPERATIONS

MATING SOCKETS

SEE SECTION 8

70-781D-1, 70-781F-1, 70-781T-1

PAGE 18, 19

70-461-1, 70-378-1, 70-379-1

PAGE 14, 15

70-461-1, 70-378-1, 70-379-1

PAGE 14, 15

AGENCY APPROVALS



PAGE NUMBER

1...1

PAGE 9 - 10

PAGE 11 - 12


PAGE 13 - 15

SOCKET COMPATIBLE & FLANGE MOUNT RELAYS



L W H 1.61 x 0.858 x 1.410	L W H 1.60 x 1.215 x 1.080	L W H 1.60 x 1.595 x 1.080
0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS - FLAG INDICATOR - L.E.D. STATUS LAMP - PUSH BUTTON WITH LOCK DOWN DOOR - FINGER GRIP COVER - I.D. TAG/WRITE LABEL - OPTIONAL FLANGE AND DIN ADAPTERS - UL LISTED WHEN USED WITH 70-782D-1 OR 70-459-1 SOCKETS	0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS - FLAG INDICATOR - PUSH BUTTON - FINGER GRIP COVER - I.D. TAG/WRITE LABEL - OPTIONAL FLANGE AND DIN ADAPTERS - UL LISTED WHEN USED WITH 70-783D-1 SOCKET	0.187 QUICK CONNECT/ SOLDER PLUG-IN ORPRINTED CIRCUIT TERMINALS - FLAG INDICATOR - PUSH BUTTON - FINGER GRIP COVER - I.D. TAG/WRITE LABEL - OPTIONAL FLANGE AND DIN ADAPTERS - UL LISTED WHEN USED WITH 70-784D-1 SOCKET
DPDT	3PDT	4PDT
SILVER ALLOY, GOLD FLASHED	SILVER ALLOY, GOLD FLASHED	SILVER ALLOY, GOLD FLASHED
15 AMPS, 110/120 VAC 50/60Hz 12 AMPS, 220/277 VAC 50/60Hz 12 AMPS, 28 VDC	15 AMPS, 110/120 VAC 50/60Hz 12 AMPS, 220/277 VAC 50/60Hz 12 AMPS, 28 VDC	15 AMPS, 110/120 VAC 50/60Hz 12 AMPS, 220/277 VAC 50/60Hz 12 AMPS, 28 VDC
6,12,24,120, 220/230, 240 VAC 6,12, 24,48,110 VDC	6,12, 24,120, 220/230, 240 VAC 6,12, 24, 48,110 VDC	6,12, 24,120, 220/230, 240 VAC 6,12, 24,48,110 VDC
1.2 VA 0.9 WATTS	1.7 VA 1.5 WATTS	2.0 VA 1.5 WATTS
CLASS "B" (130°C)	CLASS "B" (130°C)	CLASS "B" (130°C)
-40°C TO +70°C -40°C TO +105°C	-30°C TO +70°C -30°C TO +105°C	-30°C TO +70°C -30°C TO +105°C
1500 V rms	1500 V rms	1500 V rms
200,000 OPERATIONS 10,000,000 OPERATIONS	150,000 OPERATIONS 10,000,000 OPERATIONS	150,000 OPERATIONS 10,000,000 OPERATIONS
70-459-1, 70-401-1, 70-402-1, 70-782D-1	70-783D-1	70-784D-1
PAGE 13, 15, 20	PAGE 21	PAGE 22

SOCKET COMPATIBLE & FLANGE MOUNT RELAYS

RELAY SERIES	  78 ISO 9002 QS 9000	  750 ISO 9002 QS 9000	  A314 ISO 9002 QS 9000
	L W H 1.375 x 0.858 x 1.10	L W H 2.150 x 1.375 x 1.410	L W H 2.25 x 1.37 x 1.37
FEATURES	0.100 OR 0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS - OPPOSITE POLARITY ARC BARRIER BETWEEN ADJACENT POLES - UL LISTED WHEN USED WITH 70-461-1 OR 70-459-1 SOCKETS	8 & 11 PIN OCTAL BASE - FLAG INDICATOR - L.E.D. STATUS LAMP - PUSH BUTTON WITH LOCK DOWN DOOR - FINGER GRIP COVER I. D. TAG/WRITE LABEL - UL LISTED WHEN USED WITH 70-464-1, 70-465-1, 70-750D8-1 OR 70-750D11-1 SOCKETS	8 & 11 PIN OCTAL BASE - BLOWOUT MAGNET FOR DC SWITCHING TO 150 VDC - UL LISTED WHEN USED WITH 70-464-1 OR 70-465-1 SOCKETS
CONTACT DATA			
CONTACT CONFIGURATION:	SPDT, DPDT, 4PDT	DPDT, 3PDT	SPDT, DPDT, 3PDT
CONTACT MATERIAL:	SILVER, GOLD OVERLAY (3 AMP) SILVER, GOLD FLASHED (3 AMP) SILVER ALLOY, GOLD FLASHED (5 & 15 AMP)	SILVER ALLOY, GOLD FLASHED	SILVER ALLOY, GOLD FLASHED
MAX. CONTACT RATING:	4PDT: 3 AMPS, BIFURCATED 120/240 VAC/30 VDC, 3 AMPS, 120 VAC/30 VDC 5 AMPS, 120/240 VAC/30 VDC DPDT: 15 AMPS, SPDT: 15 AMPS, 120/240 VAC/30 VDC	12 AMPS, 120/240 VAC 12 AMPS, 28 VDC	SPDT: 12 AMPS, 120/240VAC, 10 AMPS, 28 VDC DPDT: 12 AMPS, 120 VAC, 10 AMPS, 240 VAC, 10 AMP, 28 VDC 3PDT: 10 AMPS, 120/240 VAC, 10 AMPS, 28 VDC DPDT: 3 AMPS, 150VDC WITH BLOWOUT MAGNET
COIL DATA			
STANDARD VOLTAGE			
AC:	6,12,24,120, 240 VAC	6,12,24,120, 220/230, 240 VAC	24,120, 240 VAC
DC:	6,12, 24,48,110 VDC	6,12, 24,48,110 VDC	12, 24 VDC
NOMINAL COIL POWER			
VA: (VAC)	1.2 VA	2 TO 3.55 VA	2 TO 2.75 VA
WATTS: (VDC)	0.9 TO 1.1 WATTS	1.4 WATTS	1.2 WATTS
INSULATION SYSTEM PER UL STANDARD 1446	CLASS "B" (130°C)	CLASS "B" (130°C)	
GENERAL DATA			
AMBIENT TEMPERATURE			
OPERATING:	-40°C TO +70°C	-30°C TO +50°C (AC) -30°C TO +65°C (DC) -30°C TO +100°C	-30°C TO +55°C (AC) -30°C TO +70°C (DC) -45°C TO +105°C
STORAGE:	-40°C TO +100°C		
DIELECTRIC STRENGTH: (COIL TO FRAME)	1500 V rms	2500 V rms	1500 V rms
LIFE EXPECTANCY			
ELECTRICAL:	200,000 OPERATIONS	200,000 OPERATIONS	100,000 OPERATIONS
MECHANICAL:	10,000,000 OPERATIONS	5,000,000 OPERATIONS	10,000,000 OPERATIONS
MATING SOCKETS			
SEE SECTION 8	70-459-1, 70-461-1, 70-401-1 70-402-1, 70-378-1, 70-379-1, 70-782D-1 PAGE 13, 14, 15	70-464-1, 70-465-1, 70-750D8-1, 70-750D11-1, 70-169-1, 70-170-1 PAGE 7, 8, 9, 10, 11, 12	70-464-1, 70-465-1, 70-750D8-1, 70-750D11-1, 70-169-1, 70-170-1 PAGE 7, 8, 9, 10, 11, 12
AGENCY APPROVALS	   	   	   
PAGE NUMBER	PAGE 21 - 24	PAGE 25 - 26	PAGE 27 - 28
1...3			



788

ISO 9002
QS 9000

L W H
2.28 x 1.375 x 1.410

- 0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS
- FLAG INDICATOR
- PUSH BUTTON WITH LOCK DOWN DOOR
- FINGER GRIP COVER
- I.D. TAG/WRITE LABEL
- UL LISTED WHEN USED WITH 70-463-1 SOCKET



A283

ISO 9002
QS 9000

L W H
1.90 x 1.53 x 1.40

- BASE PLUG-IN OR FLANGE MOUNT
- 0.187 QUICK CONNECT/ SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS
- UL LISTED WHEN USED WITH 70-463-1 SOCKET



A283 FOR DC SWITCHING

ISO 9002
QS 9000

L W H
1.90 x 1.53 x 1.40

- 0.187 QUICK CONNECT/ SOLDER PLUG-IN
- A283 BUILT FOR DC SWITCHING TO 150 VDC
- UL LISTED WHEN USED WITH 70-463-1 SOCKET

DPDT, 3PDT

SILVER ALLOY,
GOLD FLASHED

12 AMPS, 110/120 VAC 50/60Hz
12 AMPS, 28 VDC

6,12,24,120, 220/230, 240 VAC
6,12, 24, 48,110 VDC

2 TO 3.55 VA
1.4 WATTS

CLASS "B" (130°C)

-30°C TO +50°C (AC)
-30°C TO +65°C (DC)
-30°C TO +100°C

2500 V rms

200,000 OPERATIONS
5,000,000 OPERATIONS

70-463-1, 70-124-1,70-124-2,
70-178-1, 70-178-2

PAGE 16, 17



PAGE 29 - 30

SPDT, DPDT, 3PDT

SILVER ALLOY,
GOLD FLASHED

15 AMPS, 120/240 VAC 50/60Hz
10 AMPS, 28 VDC

24,120, 240 VAC
12, 24,110 VDC

2.275 VA
1.2 WATTS

CLASS "B" (130°C)

-30°C TO +50°C (AC)
-30°C TO +65°C (DC)
-30°C TO +100°C

2000 V rms

100,000 OPERATIONS
5,000,000 OPERATIONS

70-463-1, 70-124-1, 70-124-2,
70-178-1, 70-178-2

PAGE 16, 17



PAGE 31 - 33

DPDT, SPST-NO-DM

SILVER ALLOY,
GOLD FLASHED

15 AMPS, 120/240 VAC 50/60Hz
10 AMPS, 28 VDC
DPDT: 3 AMPS, 150 VDC
SPST-NO-DM: 10 AMPS, 150 VDC

120 VAC
12, 24,110 VDC

2.275 VA
1.2 WATTS

CLASS "B" (130°C)

-30°C TO +50°C (AC)
-30°C TO +65°C (DC)
-30°C TO +100°C

2000 V rms

100,000 OPERATIONS
5,000,000 OPERATIONS

70-463-1, 70-124-1, 70-124-2 ,
70-178-1, 70-178-2

PAGE 16, 17



PAGE 31, 34

RELAY SERIES	 388J  ISO 9002 QS 9000 L W H 1.90 x 1.53 x 1.40	 388V  ISO 9002 QS 9000 L W H 1.90 x 1.53 x 1.40	 389F  ISO 9002 QS 9000 L W H 1.90 x 1.53 x 1.40
FEATURES	0.187 QUICK CONNECT / SOLDER PLUG-IN TERMINALS - FLAG INDICATOR - PUSH BUTTON - FINGER GRIP COVER - UL LISTED WHEN USED WITH 70-463-1 SOCKET	0.187 QUICK CONNECT/ SOLDER PLUG-IN TERMINALS - PUSH BUTTON - HIGH VOLTAGE SWITCHING - MEETS 8 mm EUROPEAN SPACING REQUIREMENTS 3 MILLIMETER CONTACT GAP - UL LISTED WHEN USED WITH 70-463-1 SOCKET	- FLANGE MOUNT, 0.250 QUICK CONNECT/ SOLDER TERMINALS - SWITCHING UP TO 25 AMPS - FLAG INDICATOR - PUSH BUTTON
CONTACT DATA			
CONTACT CONFIGURATION:	DPDT, 3PDT	DPST-NO, 3PST-NO	DPDT
CONTACT MATERIAL:	SILVER ALLOY, GOLD FLASHED	SILVER ALLOY, GOLD FLASHED	SILVER ALLOY, GOLD FLASHED
MAX. CONTACT RATING:	DPDT: 20 AMPS, 300 VAC 50/60Hz 20 AMPS, 28 VDC 3PDT: 16 AMPS, 250 VAC 50/60Hz 16 AMPS, 28 VDC	15 AMPS, 120/240 VAC 50/60Hz 15 AMPS, 28 VDC	25 AMPS, 300 VAC 50/60Hz 13 AMPS, 28 VDC
COIL DATA			
STANDARD VOLTAGE	24, 120, 240 VAC 12, 24 VDC	24, 120, 240 VAC 12, 24 VDC	24,120, 240 VAC 12, 24 VDC
NOMINAL COIL POWER VA: (VAC) WATTS: (VDC)	2 TO 3.5 VA 1.44 WATTS	1 TO 1.2 VA 3.0 WATTS	2 TO 3.5 VA 1.44 WATTS
INSULATION SYSTEM PER UL STANDARD 1446	CLASS "B" (130°C)	CLASS "B" (130°C)	CLASS "B" (130°C)
GENERAL DATA			
AMBIENT TEMPERATURE OPERATING:	-30°C TO +50°C (AC) -30°C TO +65°C (DC)	-30°C TO +50°C (AC) -30°C TO +65°C (DC)	-30°C TO +50°C (AC) -30°C TO +65°C (DC)
STORAGE:	-30°C TO +100°C	-30°C TO +100°C	-30°C TO +100°C
DIELECTRIC STRENGTH: (COIL TO FRAME)	2200 V rms	2000 V rms	2200 V rms
LIFE EXPECTANCY ELECTRICAL: MECHANICAL:	100,000 OPERATIONS 5,000,000 OPERATIONS	100,000 OPERATIONS 5,000,000 OPERATIONS	100,000 OPERATIONS 5,000,000 OPERATIONS
MATING SOCKETS SEE SECTION 8	70-463-1, 70-124-1, 70-124-2 , 70-178-1, 70-178-2 PAGE 16, 17	70-463-1, 70-124-1, 70-124-2, 70-178-1, 70-178-2 PAGE 16, 17	—
AGENCY APPROVALS	    UL Recognized File No. E43641 168986 LISTED	    UL Recognized File No. E43641 168986 LISTED	   UL Recognized File No. E43641 168986
PAGE NUMBER	PAGE 35 - 36 1...5	PAGE 37 - 38	PAGE 39 - 41



389



ISO 9002
QS 9000

L W H
1.90 x 1.53 x 1.40

- FLANGE MOUNT, 0.250 QUICK CONNECT/ SOLDER TERMINALS
- SWITCHING UP TO 30 AMPS

SPDT, DPDT, 3PDT, SPST-NO-DM
SPST-NO-NC-DM-DB

SILVER ALLOY,
GOLD FLASHED

SPST-DM, SPST-DB-DM:
30 AMPS, 300 VAC 50/60Hz, 30 AMPS, 28 VDC
SPDT, DPDT: 25 AMPS, 300 VAC 50/60Hz,
13 AMPS, 28 VDC
3PDT: 20 AMPS, 300 VAC, 50/60Hz,
13 AMPS, 28 VDC

24,120, 240 VAC
12, 24 VDC

2 TO 3.5 VA
1.44 WATTS

CLASS "B" (130°C)

-30°C TO +50°C (AC)
-30°C TO +65°C (DC)
-30°C TO +100°C

2200 V rms

100,000 OPERATIONS
5,000,000 OPERATIONS



PAGE 39, 40 & 42



300



ISO 9002
QS 9000

L W H
1.90 x 1.53 x 1.40

- FLANGE MOUNT, 0.250 QUICK CONNECT / SOLDER OR PRINTED CIRCUIT TERMINALS
- 2 MILLIMETER CONTACT GAPS
- ARC BARRIER BETWEEN CONTACTS
- OPTIONAL BLOWOUT MAGNET FOR HIGH VOLTAGE SWITCHING
- OPTIONAL DIN RAIL CASE

DPDT-SPDT-NO-NC-DM-DB

SILVER ALLOY,
GOLD FLASHED

30 AMPS, 120/240/277 VAC 50/60Hz
30 AMPS, 28 VDC, 15 AMPS, 600 VAC
DPDT: 5 AMPS, 150 VDC
SPDT-DB-DM: 10 AMPS, 150 VDC

6, 12, 24, 120, 240 VAC
6, 12, 24, 48, 110/125, 220/225 VDC


3.0 VA
2.0 WATTS

CLASS "B" (130°C)
CLASS "F" (155°C) AVAILABLE

-30°C TO +50°C (AC)
-30°C TO +60°C (DC)
-40°C TO +105°C

4000 V rms

100,000 OPERATIONS
10,000,000 OPERATIONS



PAGE 43 - 44



9A

L W H
1.980 x 1.08 x 1.10

- EPOXY SEALED IMMERSION CLEANABLE WITH TAPE SEAL
- PRINTED CIRCUIT BOARD OR FLANGE MOUNT STYLES
- CLASS "F" INSULATION SYSTEM
- 0.250 SPADE TERMINALS ACCEPT INSULATED 0.250 QUICK CONNECT TERMINALS. & 0.187 COIL QUICK CONNECT TERMINALS.
- OPTIONAL DIN RAIL ADAPTER AVAILABLE

SPST-NO & SPDT

SILVER ALLOY

SPST-NO: 30 AMPS, 240 VAC,
20 AMPS, 28 VDC
SPDT: 30 AMPS, 240 VAC
20 AMPS, 28 VDC (NO),
15 AMPS, 240 VAC, 10 AMPS, 28 VDC (NC),

5, 12, 24, 48 & 110 VDC


0.95 VA
2.8 WATTS MAX.

- 55°C TO +85°C
- 55°C TO +130°C

2500 V rms

100,000 OPERATIONS
10,000,000 OPERATIONS

OPTIONAL DIN ADAPTER
16-9A DIN-1



PAGE 45 - 46

RELAY SERIES	92 	W67 	219  ISO 9002 QS 9000
	L W H 2.70 x 1.36 x 1.495	L W H 1.20 x 0.735 x 0.978 to 1.592	L W H 2.59 x 1.468 x 2.625 / 3.062
FEATURES	- EPOXY SEALED IMMERSION CLEANABLE WITH TAPE SEAL - PRINTED CIRCUIT BOARD OR FLANGE MOUNT STYLES - CLASS "F" INSULATION SYSTEM. 0.250 SPADE TERMINALS ACCEPT 0.250 QUICK CONNECT TERMINALS - OPTIONAL DIN RAIL ADAPTER AVAILABLE	0.100 SOLDER PLUG-IN OR PRINTED CIRCUIT TERMINALS - UP TO 6 POLES SWITCHING PLUG-IN STYLES HAVE 3-48 UNC GROUND STUDS	12 OR 14 PIN PLUG-IN WITH LOCKING CLIP - ENCAPSULATED COIL - WIDE RANGE OF CONTACT CONFIGURATIONS - WIDE CHOICE OF OPTIONS - UL LISTED WHEN USED WITH 27390 OR 33377 SOCKET
CONTACT DATA			
CONTACT CONFIGURATION:	DPST-NO. & DPDT	DPDT THRU 8PDT	VARIOUS
CONTACT MATERIAL:	SILVER ALLOY	SILVER GOLD OVERLAY	SILVER ALLOY, GOLD DIFFUSED
MAX. CONTACT RATING:	DPDT-NO: 30 AMPS, 277 VAC. 20 AMPS, 28 VDC DPST-NO: 30 AMPS, 277 VAC. 20 AMPS, 28 VDC DPDT-NC: 3 AMPS, 277 VAC. 28 VDC	5 AMPS, 120 VAC 50/60Hz / 28 VDC BIFURCATED 3AMPS, 1240 VAC 50/60Hz / 28 VDC	10 AMPS, 120/240 VAC 50/60Hz 10 AMPS, 28 VDC
COIL DATA			
STANDARD VOLTAGE			
AC:	24, 120 & 240 VAC	120 VAC	6,12, 24, 120, 220/230, 240 VAC
DC:	12, 24, 48 & 110 VDC	5, 12, 24, 48, 115 VDC	6, 12, 24, 48, 110 VDC
NOMINAL COIL POWER			
VA: (VAC)	4 VA	1.5 TO 2.5 VA	1.2 VA
WATTS: (VDC)	1.7 WATTS	1 TO 2.0 WATTS	0.9 WATTS
INSULATION SYSTEM PER UL STANDARD 1446			CLASS "B" (130°C)
GENERAL DATA			
AMBIENT TEMPERATURE OPERATING:	- 40°C TO +65°C (AC) - 40°C TO +85°C (DC)	-55°C TO +70°C	-40°C TO +70°C
STORAGE:	- 55°C TO +155 C	-55°C TO +105°C	-40°C TO +105°C
DIELECTRIC STRENGTH: (COIL TO FRAME)	4000 V rms	1500 V rms	1500 V rms
LIFE EXPECTANCY			
ELECTRICAL:	100,000 OPERATIONS	100,000 OPERATIONS	100,000 OPERATIONS
MECHANICAL:	5,000,000 OPERATIONS	10,000,000 OPERATIONS	10,000,000 OPERATIONS
MATING SOCKETS	OPTIONAL DIN ADAPTER 16-92 DIN-1	70-303-1, 70-305-1, 70-307-1, 70-304-1, 70-306-1, 70-308-1 PAGE 23, 24	27390, 33377, 70-219D-12 OR 70-219D-14 PAGE 25
AGENCY APPROVALS	 US UL Recognized File No. E43641	 US UL Recognized File No. E52197  168986	 US UL Recognized File No. E13224  168986  LISTED
PAGE NUMBER	PAGE 47 - 48	PAGE 49 - 50	PAGE 51 - 52

750H



21



L W H
1.281 x 0.910 x 1.156

L W H
2.84 X 1.85 X 2.47

- 8 & 11 PIN OCTAL BASE
- HERMETICALLY SEALED VACUUM BAKED AND DRY NITROGEN FILLED
- GRAY LACQUER FINISH OVER STEEL ENCLOSURE
- MEETS UL STANDARD FOR CLASS 1 DIVISION 2 HAZARDOUS LOCATIONS
- UL LISTED WHEN USED WITH 70-464-1 OR 70-465-1 SOCKETS

- PLUG-IN BASE WITH POLARIZING PIN
- SWITCHES TUNGSTEN LOADS UP TO 20 AMPS
- MEETS NEMA STD. TS 2-1992 APPROVED BY D. O. T.

DPDT, 3PDT

DPDT

SILVER ALLOY,
GOLD DIFFUSED

SILVER ALLOY

DPDT: 12 AMPS, 120 VAC 50/60Hz
8 AMPS, 240 VAC 50/60Hz,
10 AMPS, 28 VDC
3PDT: 10 AMPS, 120 VAC 50/60Hz
6 AMPS, 240 VAC 50/60Hz,
10 AMPS, 28 VDC

30 AMPS, 120/240 VAC 50/60Hz
20 AMP, 28 VDC
20 AMPS, 120 VAC 50/60Hz, TUNGSTEN
10 AMPS, 240 VAC 50/60Hz, TUNGSTEN

12, 24, 120 VAC
12, 24, 110 VDC

120 VAC RECTIFIED

2 - 2.75 VA
1.2 WATTS

4.0 VA

CLASS "B" (130°C)

-45°C TO +55°C (AC)
-45°C TO +70°C (DC)
-40°C TO +105°C

-40°C TO +84°C
-40°C TO +105°C

1250 V rms

1500 V rms

100,000 OPERATIONS
5,000,000 OPERATIONS

200,000 OPERATIONS
5,000,000 OPERATIONS

70-464-1, 70-465-1

—

PAGE 7, 8

UL US
UL Recognized
File No. E43641

UL
LISTED

UL US
UL Recognized
File No. E43641

SP
168986

PAGE 53 - 54

PAGE 55

Magnecraft & Struthers-Dunn
Your Contact for Industrial Relays

U. S. A.

TELEPHONE: (843) 393-5778

FAX: (843) 393-4123

WEBSITE: www.magnecraft.com

EMAIL: info@magnecraft.com

EUROPE

TELEPHONE: 4989 / 75080310

FAX: 4989 / 7559344

WEBSITE: www.magnecraft.com

EMAIL: renatesteinback@magnecraft.de

FEATURES

FLAG INDICATOR:

SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.

BI - POLAR
L.E.D. STATUS LAMP:

SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.

PUSH BUTTON:

ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER. IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.

FINGER-GRIP COVER:

ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE EASILY THAN CONVENTIONAL RELAYS.

I.D. TAG/WRITE LABEL:

USED FOR IDENTIFICATION OF RELAYS IN MULTI-RELAY CIRCUITS.

COVER ADAPTERS:

DIN RAIL ADAPTER OR TOP/BOTTOM FLANGE ADAPTER, ALLOWS THE 781 RELAY TO BE DIRECT MOUNTED TO A DIN RAIL OR PANEL.

BENEFITS

SPDT, 15 AMPS

UL Recognized
File No. E43641

97899

LISTED 367G
IND. CONT. EQ.

C US

WHEN USED WITH
SOCKETS 70-781D-1CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT

GENERAL SPECIFICATIONS

COIL

Pull-in Voltage:	75% of nominal voltage or less for DC coils, 80% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%, AC-30% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±15% measured @ 25°C.
Coil Power:	0.7 watts DC, 0.9 VA (60Hz) AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation:	2.3 watts DC, 2.55 VA (60Hz) AC @ 25°C
Duty:	Continuous

CONTACTS

Contact Material:	Silver alloy, gold flashed
Contact Rating:	15 amps @ 110/120 VAC 50/60Hz. 12 amps @ 220/277 VAC 50/60Hz. 15 amps @ 28 VDC. 1/2Hp @ 110/120 VAC 50/60Hz. 1Hp @ 220/250 VAC 50/60Hz. B300 pilot duty 50/60Hz. 10 amps @ 120 VAC general purpose 10 amps @ 240 VAC general purpose (general purpose load, 75% to 80% power factor)

DIELECTRIC STRENGTH

Coil to Frame:	1500 V rms
Across Open Contacts:	1000 V rms
Contacts to Frame:	1500 V rms
Insulation Resistance:	100 megohms @ 500 VDC

TEMPERATURE

Operating:	-40°C to +70°C
Storage:	-40°C to +100°C

LIFE EXPECTANCY

Electrical:	150,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Weight:	29 grams approx.

MANUFACTURED UNDER
ISO 9002 & QS 9000

STANDARD COVER

STANDARD COVER WITH
FLANGE ADAPTER 16-781C1
ON TOPSTANDARD COVER WITH
FLANGE ADAPTER 16-781C1
ON BOTTOMSTANDARD COVER
WITH DIN ADAPTER
16-781CDIN ADAPTER ORDERED AND
SHIPPED SEPARATELY

Mating Sockets

70-781D-1: SCREW/DIN

70-781F-1: SOLDER


70-781T-1: PRINTED CIRCUIT

See section 8, page 18, 19



NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).




SPDT, 15 AMPS

PRINTED CIRCUIT MOUNTING HOLE LAYOUT (BOTTOM VIEW)



WIRING DIAGRAM (VIEWED FROM PIN END)



BI - POLAR L.E.D. STATUS LAMP ALLOWS FOR REVERSE POLARITY APPLICATIONS

ORDERING CODE FOR RELAYS

CLASS: 781

CONTACT CONFIGURATION: XAX
SPDT: XAX

TERMINAL STYLE: ML
QUICK CONNECT SOLDER / PLUG-IN TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

OPTIONAL PLAIN COVER: -120A
CODE C

STANDARD COVER FEATURES:
PUSH BUTTON : **CODE M**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

OPTIONAL PLAIN COVER FEATURES:
PUSH BUTTON : **CODE M**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

COIL VOLTAGE:
6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

STANDARD PART NUMBERS SPDT	COIL MEASURED @ 25°C		
	PLAIN COVER	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP			
781XAXML-24A	781XAXC-24A	24 VAC, 50/60Hz	180 Ω
781XAXML-120A	781XAXC-120A	120 VAC, 50/60Hz	4,430 Ω
781XAXML-240A		240 VAC, 50/60HZ	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP			
781XAXML-12D		12 VDC	120 Ω
781XAXML-24D	781XAXC-24D	24 VDC	470 Ω
781XAXML-110D		110 VDC	10,000 Ω
AC OPERATED - PRINTED CIRCUIT, 15 AMP			
781XAXTML-120A		120 VAC, 50/60Hz	4,430 Ω
DC OPERATED - PRINTED CIRCUIT, 15 AMP			
781XAXTML-12D		12 VDC	120 Ω
781XAXTML-24D		24 VDC	470 Ω

RETROFITS IDEC RH1B- & RH1V2-. SEE END OF SECTION 1 FOR CROSS REFERENCE CADMIUM-FREE CONTACTS AVAILABLE, CONTACT FACTORY FOR DETAILS

FEATURES**VACUUM BAKED & DRY
NITROGEN FILLED**REMOVES CONTAMINANTS AND PROVIDES A CLEAN & DRY
ATMOSPHERE FOR CONTACTS.**HERMETICALLY SEALED
METAL ENCLOSURE**IDEAL FOR USE IN HAZARDOUS LOCATIONS. UL CERTIFIED FOR
CLASS 1 DIVISION 2 GROUP A, B, C & D HAZARDS. WHEN RELAY IS
USED WITH 70-461-1 SOCKET, THE HOLD-DOWN CLIP 16-1328 IS
REQUIRED.**CHOICE OF CONTACT RATINGS
1 AMP, 3 AMPS AND 5 AMPS**PROVIDES FOR LOW LEVEL SWITCHING APPLICATIONS UP TO
5 AMPS POWER LOADS.**PLUG-IN STYLE OR SIDE
MOUNTING STUD WITH
ANTI-ROTATION TAB**WHEN USED WITH 70-461-1 SOCKET THE 782H CAN BE DIN RAIL
MOUNTED OR PANEL MOUNTED. THE SIDE STUD PROVIDES FOR
DIRECT MOUNT & SOLDERED WIRE APPLICATIONS.**BENEFITS****4PDT, 1, 3 & 5 AMPS****UL** **us**
UL Recognized
File No. E209950**SP** 168986**UL** **US**
LISTED 367G
IND. CONT. EQ.WHEN USED WITH
SOCKET 70-461-1CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS**CE**

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	75% of nominal voltage or less for DC coils, 80% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%, AC-30% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±15% measured @ 25°C
Coil Power:	0.9 watts DC. 1.2 VA (60Hz) AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard. 1446)
Max. Coil Dissipation:	2.0 watts DC, 2.5 VA (60Hz) AC. @ 25°C. 5 minutes maximum @ 25°C
Duty:	Continuous

CONTACTS

Contact Material:	See ordering code
Contact Rating:	See ratings table

TIMING

Operate Time:	13 mS max @ nominal voltage
Release Time:	6 mS max @ nominal voltage

DIELECTRIC STRENGTH

Contacts to Coil:	1240 V rms
Across Open Contacts:	500 V rms
Contacts to Frame:	1240 V rms
Insulation Resistance:	100 megohms @ 500 VDC

TEMPERATURE

Operating:	-45°C to +70°C
Storage:	-60°C to +130°C

VIBRATION RESISTANCE

Functional:	10 to 55Hz; 6 g's (double amplitude)
-------------	--------------------------------------

SHOCK RESISTANCE


Functional:	10 g's (11mS)
-------------	---------------

LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Grey metal case, hermetically sealed
Weight:	45 grams approx.

**MANUFACTURED UNDER
ISO 9001****UL GROUPS A, B, C & D CERTIFIED
CLASS 1 DIVISION 2 FOR
HAZARDOUS LOCATIONS**


Mating Sockets
70-461-1: SCREW/DIN
70-378-1: SOLDER
70-379-1: PRINTED CIRCUIT
 See section 8, page 14, 15




4PDT, 1, 3 & 5 AMPS

NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



WIRING DIAGRAM
(VIEWED FROM PIN END)



UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD	MINIMUM LOAD
4 POLES	1 AMP	120/240	50/60 Hz	RESISTIVE	DRY CIRCUIT
	3 AMP	120/240	50/60 Hz	RESISTIVE	100 mA 12 VAC
	5 AMP	120/240	50/60 Hz	RESISTIVE	500 mA 12 VAC
	1 AMP	30	DC	RESISTIVE	DRY CIRCUIT
	3 AMP	30	DC	RESISTIVE	100 mA 12 VDC
	5 AMP	30	DC	RESISTIVE	500 mA 12 VDC

ORDERING CODE FOR RELAYS

782 XDX H 32 - 24D

CLASS: _____

CONTACT CONFIGURATION: _____
4PDT: XDX

HERMETICALLY SEALED: _____

CONTACT RATING: _____
1 AMP BIFURCATED: **CODE 32**
(SILVER CROSS BAR WITH GOLD OVERLAY)
3 AMP: **CODE 10**
(SILVER GOLD FLASHED)
5 AMP: **CODE 21**
(SILVER CADMIUM OXIDE)

TERMINALS & MOUNTING STYLE: _____
SOLDER/PLUG-IN: **NO CODE**
SOLDER WITH STUD ON BROAD SIDE: **CODE 2**

COIL VOLTAGE: _____
6, 12, 24, 120, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

STANDARD PART NUMBERS 4PDT	COIL MEASURED @ 25°C	
	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 3 AMP		
782XDXH10-24A	24 VAC, 50/60Hz	7160 Ω
782XDXH10-120A	120 VAC, 50/60Hz	3,900 Ω
DC OPERATED - SOLDER/PLUG-IN, 3 AMP		
782XDXH10-12D	12 VDC	160 Ω
782XDXH10-24D	24 VDC	650 Ω
782XDXH10-110D	110 VDC	11,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 5 AMP		
782XDXH21-120A	120 VAC, 50/60Hz	3,900 Ω
DC OPERATED - SOLDER/PLUG-IN, 5 AMP		
782XDXH21-12D	12 VDC	160 Ω
782XDXH21-24D	24 VDC	650 Ω

RETROFITS POTTER & BRUMFIELD KHS OR OMRON MY4H.
SEE END OF SECTION 1 FOR CROSS REFERENCE

FEATURES**BENEFITS****FLAG INDICATOR:**

SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.

BI - POLAR**L.E.D. STATUS LAMP:**

SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.

PUSH BUTTON:

ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER. IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.

LOCK-DOWN DOOR:

WHEN ACTIVATED, HOLDS PUSH BUTTON AND CONTACTS IN THE OPERATE POSITION. EXCELLENT FOR ANALYZING CIRCUIT PROBLEMS.

FINGER-GRIP COVER:

ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE EASILY THAN CONVENTIONAL RELAYS.

I.D. TAG/WRITE LABEL:

USED FOR IDENTIFICATION OF RELAYS IN MULTI-RELAY CIRCUITS.

COVER ADAPTERS:

DIN RAIL FLANGE ADAPTER OR TOP/BOTTOM FLANGE ADAPTER, ALLOWS THE 782 RELAY TO BE DIRECT MOUNTED TO A DIN RAIL OR PANEL.

**DPDT & 4PDT
3, 10 & 15 AMPS**

UL **us**
UL Recognized
File No. E43641



UL **us**
LISTED 367G
IND. CONT. EQ.

WHEN USED WITH
SOCKETS 70-782D-1,
70-459-1 OR 70-461-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

**MANUFACTURED UNDER
ISO 9002 & QS 9000****GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage: 75% of nominal voltage or less for DC coils,
80% of nominal voltage or less for AC coils
Dropout Voltage: DC-10% , AC-30% of nominal voltage or more
Max. Voltage: 110%
Resistance: $\pm 15\%$ measured @ 25°C
Coil Power: 0.9 watts DC, 1.2 VAC (60Hz) AC @ 25°C
Insulation System: Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation: 2.3 watts DC, 2.55 VAC (60Hz) AC @ 25°C
Duty: Continuous

CONTACTS

Contact Material: 3 amps bifurcated silver gold plated. 3 amps silver gold flashed
10 & 15 amps, silver alloy, gold flashed
Contact Rating: **DPDT, 4PDT-** Bifurcated 3 amps @ 120/240 VAC 30 VDC.
1/16Hp (2.8 amp FLA), 120 VAC. Pilot duty - 5 amps make,
1/2 amp break, 3 amps continuous, 120 VAC
DPDT, 4PDT- 3 amps @ 120/240 VAC, 30 VDC,
1/6 Hp 120/240 VAC, C300 pilot duty.
DPDT, 4PDT- 10 amps @ 110/120 VAC, 8 amps @ 220/277 VAC.
8 amps @ 28 VDC, 1/3 Hp 250 VAC, B300 pilot duty.
DPDT- 15 amps @ 110/120 VAC, 12 amps @ 220/277 VAC (20 amps max.)
12 amps 28 VDC, 1/2 Hp, 120 VAC. 1 Hp 250 VAC, B300 pilot duty

DIELECTRIC STRENGTH

Coil To Frame: 1500 V rms
Across Open Contacts: 1000 V rms
Contacts To Frame: 1500 V rms
Insulation Resistance: 100 megohms @ 500 VDC

TEMPERATURE

Operating: -40°C to +70°C
Storage: -40°C to +105°C

LIFE EXPECTANCY

Electrical: 200,000 operations @ rated resistive load
Mechanical: 10,000,000 operations @ no load

MISCELLANEOUS

Operating Position: Any
Insulation Material: Molded plastic
Enclosure: Polycarbonate dust cover
Weight: 36 grams approx

**STANDARD COVER****STANDARD COVER WITH
FLANGE ADAPTER 16-782C1
ON TOP****STANDARD COVER WITH
FLANGE ADAPTER 16-782C1
ON BOTTOM****STANDARD COVER
WITH DIN ADAPTER
16-782C****DIN ADAPTER ORDERED AND
SHIPPED SEPARATELY****Mating Sockets**

70-782D-1, 70-461-1,
70-459-1: **SCREW/DIN**
70-379-1, 70-378-1: **SOLDER**
70-401-1, 70-402-1:
PRINTED CIRCUIT

See section 8, page 13, 14, 15




NEW
From The Market
Leader in Industrial
Relays


OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**PRINTED CIRCUIT
MOUNTING HOLE LAYOUT**
(BOTTOM VIEW)

DPDT, 3 & 10 AMPS



WIRING DIAGRAM
(VIEWED FROM PIN END)



ORDERING CODE FOR RELAYS

782 **XBX** **M4L** **-120A**

CLASS: _____

CONTACT CONFIGURATION: _____
DPDT: XBX

TERMINAL STYLE: _____
QUICK CONNECTSOLDER/
PLUG-IN TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

CONTACT RATING: _____
3 AMP: **CODE 1**
10 AMP: **CODE 2**
3 AMP BIFURCATED CONTACT: **CODE 3**

OPTIONAL PLAIN COVER: _____
CODE C

STANDARD COVER FEATURES: _____
PUSH BUTTON & LOCK-DOWN DOOR: **CODE M4**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

OPTIONAL STANDARD COVER DELETION: _____
PUSH BUTTON AND BI - POLAR L.E.D. WITHOUT
LOCK-DOWN DOOR: **CODE ML**

OPTIONAL PLAIN COVER FEATURES: _____
PUSH BUTTON WITHOUT LOCK-DOWN DOOR: **CODE M**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

COIL VOLTAGE: _____
6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 110 ADD "D" FOR DC COILS

BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS

STANDARD PART NUMBERS DPDT	COIL MEASURED @ 25°C	
	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 10 AMP		
782XBX2M4L-24A	24 VAC, 50/60Hz	72 Ω
782XBX2M4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XBX2M4L-240A	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 10 AMP		
782XBX2M4L-12D	12 VDC	120 Ω
782XBX2M4L-24D	24 VDC	470 Ω
782XBX2M4L-110D	110 VDC	10,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
782XBX3M4L-24A	24 VAC, 50/60Hz	72 Ω
782XBX3M4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XBX3M4L-240A	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
782XBX3M4L-12D	12 VDC	120 Ω
782XBX3M4L-24D	24 VDC	470 Ω
782XBX3M4L-110D	110 VDC	10,000 Ω

RETROFITS SCHRACK PT.
SEE END OF SECTION 1 FOR CROSS REFERENCE
CADMIUM-FREE CONTACTS AVAILABLE,
CONTACT FACTORY FOR DETAILS

NEW
From The Market
Leader in Industrial
Relays


4PDT, 3 & 10 AMPS

OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS)

PRINTED CIRCUIT MOUNTING HOLE LAYOUT


(BOTTOM VIEW)



AVAILABLE WITHOUT
LOCK-DOWN DOOR: CODE "M"

WIRING DIAGRAM

(VIEWED FROM PIN END)



ALL 4 POLE RELAYS HAVE OPPOSITE POLARITY ARC BARRIERS AS A STANDARD FEATURE TO PROVIDE GREATER VOLTAGE PROTECTION BETWEEN ADJACENT POLES

ORDERING CODE FOR RELAYS

782 XDX M4L -120A

CLASS:

CONTACT CONFIGURATION:
4PDT: XDX

TERMINAL STYLE:

QUICK CONNECTSOLDER/
PLUG-IN TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

CONTACT RATING:

3 AMP: **CODE 1**
10 AMP: **CODE 2**
3 AMP BIFURCATED CONTACT: **CODE 3**

**OPTIONAL PLAIN COVER:
CODE C**

STANDARD COVER FEATURES:

PUSH BUTTON & LOCK-DOWN DOOR: **CODE M4**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

OPTIONAL STANDARD COVER DELETION:

PUSH BUTTON AND BI - POLAR L.E.D.WITHOUT
LOCK-DOWN DOOR: **CODE ML**

OPTIONAL PLAIN COVER FEATURES:

PUSH BUTTON WITHOUT LOCK-DOWN DOOR: **CODE M**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

COIL VOLTAGE:

6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

**BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS**

COIL MEASURED @ 25°C

STANDARD PART NUMBERS 4PDT	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - QUICK CONNECT SOLDER/PLUG-IN, 3 AMP		
782XDX1M4L-24A	24 VAC, 50/60Hz	72 Ω
782XDX1M4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XDX1M4L-240A	240 VAC, 50/60HZ	9,100 Ω
DC OPERATED - QUICK CONNECT SOLDER/PLUG-IN, 3 AMP		
782XDX1M4L-12D	12 VDC	120 Ω
782XDX1M4L-24D	24 VDC	470 Ω
782XDX1M4L-110D	110 VDC	10,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 10 AMP		
782XDX2M4L-24A	24 VAC, 50/60Hz	72 Ω
782XDX2M4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XDX2M4L-240A	240 VAC, 50/60HZ	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 10 AMP		
782XDX2M4L-12D	12 VDC	120 Ω
782XDX2M4L-24D	24 VDC	470 Ω
782XDX2M4L-110D	110 VDC	10,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
782XDX3M4L-24A	24 VAC, 50/60Hz	72 Ω
782XDX3M4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XDX3M4L-240A	240 VAC, 50/60HZ	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
782XDX3M4L-12D	12 VDC	120 Ω
782XDX3M4L-24D	24 VDC	470 Ω
782XDX3M4L-110D	110 VDC	10,000 Ω

RETROFITS SCHRACK PT.
SEE END OF SECTION 1 FOR CROSS REFERENCE

DPDT, 15 AMPS


NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**QUICK CONNECT
SOLDER / PLUG-IN
TERMINALS**

**PRINTED CIRCUIT
MOUNTING HOLE LAYOUT**
(BOTTOM VIEW)

**PUSH BUTTON WITH
LOCK-DOWN DOOR**



AVAILABLE WITHOUT
LOCK-DOWN DOOR: CODE "M"



**BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS**

ORDERING CODE FOR RELAYS

CLASS: 782

CONTACT CONFIGURATION: XBX
DPDT: XBX

TERMINAL STYLE: M4L
QUICK CONNECTSOLDER/
PLUG-IN TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

OPTIONAL PLAIN COVER: -120A
CODE C


STANDARD COVER FEATURES:
PUSH BUTTON & LOCK-DOWN DOOR: **CODE M4**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

OPTIONAL STANDARD COVER DELETION:
PUSH BUTTON AND BI - POLAR L.E.D. WITHOUT
LOCK-DOWN DOOR: **CODE ML**

OPTIONAL PLAIN COVER FEATURES:
PUSH BUTTON WITHOUT LOCK-DOWN DOOR: **CODE M**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

COIL VOLTAGE:
6, 12, 24, 120, 220/230, 240 **ADD "A" FOR AC COILS**
6, 12, 24, 48, 110 **ADD "D" FOR DC COILS**

WIRING DIAGRAM (VIEWED FROM PIN END)



STANDARD PART NUMBERS DPDT	COIL MEASURED @ 25°C	
	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP		
782XBXM4L-24A	24 VAC, 50/60Hz	72 Ω
782XBXM4L-120A	120 VAC, 50/60Hz	1,700 Ω
782XBXM4L-240A	240 VAC, 50/60HZ	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP		
782XBXM4L-12D	12 VDC	120 Ω
782XBXM4L-24D	24 VDC	470 Ω
782XBXM4L-110D	110 VDC	10,000 Ω

RETROFITS SCHRACK PT.
SEE END OF SECTION 1 FOR CROSS REFERENCE

FEATURES**BENEFITS****FLAG INDICATOR:**

SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.

BI - POLAR

SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.

L.E.D. STATUS LAMP:

ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER. IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.

PUSH BUTTON:

WHEN ACTIVATED, HOLDS PUSH BUTTON AND CONTACTS IN THE OPERATE POSITION. EXCELLENT FOR ANALYZING CIRCUIT PROBLEMS.

LOCK-DOWN DOOR:

ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE EASILY THAN CONVENTIONAL RELAYS.

FINGER-GRIP COVER:

USED FOR IDENTIFICATION OF RELAYS IN MULTI-RELAY CIRCUITS.

I.D. TAG/WRITE LABEL:**COVER ADAPTERS:**

DIN RAIL FLANGE ADAPTER OR TOP/BOTTOM FLANGE ADAPTER, ALLOWS THE 783 RELAY TO BE DIRECT MOUNTED TO A DIN RAIL OR PANEL.

3PDT, 15 AMPS

 UL Recognized
 File No. E43641


 LR40787


 LISTED 367G
 IND. CONT. EQ.
 C US
 WHEN USED WITH
 SOCKETS 70-783D-1,
CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	75% of nominal voltage or less for DC coils, 80% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%, AC- 30% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±15% measured @ 25°C
Coil Power:	1.5 watts DC, 1.7 VA (60Hz) AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation:	3.0 watts DC, 3.4 VA (60Hz) AC. @ 25°C
Duty:	Continuous

CONTACTS

Contact Material:	Solid silver alloy, gold flashed
Contact Rating:	15 amps @110/120 VAC 50/60Hz (30 amps max.) 12 amps @ 28 VDC (30 amps max.) 12 amps @ 220/277 VAC 50/60Hz (20 amps max.) 1/2Hp @ 120 VAC, 3/4 Hp @ 250 VAC, B300 pilot duty
Contact Resistance:	50 milliohms maximum initial resistance

DIELECTRIC STRENGTH

Contacts to Coil:	2500 V rms
Across open Contacts:	1000 V rms
Pole to Pole:	2500 V rms
Contacts to Frame:	2500 V rms
Insulation Resistance:	100 megohms min. @ 500 VDC

TEMPERATURE

Operating:	-30°C to +70°C
Storage:	-30°C to +105°C

VIBRATION RESISTANCE

Functional:	6 g's, 10 to 55 Hz (0.6 mm double amplitude)
-------------	--

SHOCK RESISTANCE

Functional:	10 g's
-------------	--------

LIFE EXPECTANCY

Electrical:	150,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Weight:	60 grams approx.




**STANDARD COVER****STANDARD COVER WITH
FLANGE ADAPTER 16-783C1
ON TOP****TOP OR BOTTOM FLANGE
ADAPTER ORDERED AND
SHIPPED SEPARATELY****STANDARD COVER WITH
FLANGE ADAPTER 16-783C1
ON BOTTOM****TOP OR BOTTOM FLANGE
ADAPTER ORDERED AND
SHIPPED SEPARATELY****STANDARD COVER
WITH DIN ADAPTER
16-783C****DIN ADAPTER ORDERED AND
SHIPPED SEPARATELY**
Mating Sockets
70-783D-1: SCREW/DIN
 See section 8, page 21


3PDT, 15 AMPS


NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**PRINTED CIRCUIT MOUNTING HOLE LAYOUT (BOTTOM VIEW)****PRINTED CIRCUIT TERMINALS****QUICK CONNECT SOLDER / PLUG-IN TERMINALS**

AVAILABLE WITHOUT
LOCK-DOWN DOOR: CODE "M"

WIRING DIAGRAM (VIEWED FROM PIN END)**ORDERING CODE FOR RELAYS**

CLASS: 783

CONTACT CONFIGURATION: XCX
3PDT: XCX

TERMINAL STYLE: M4L
QUICK CONNECT SOLDER / PLUG-IN TERMINALS: NO CODE
PRINTED CIRCUIT TERMINALS: CODE T

OPTIONAL PLAIN COVER: -120A
CODE C

STANDARD COVER FEATURES:
PUSH BUTTON & LOCK-DOWN DOOR: CODE M4
BI - POLAR L.E.D. STATUS LAMP: CODE L

OPTIONAL STANDARD COVER DELETION:
PUSH BUTTON AND BI - POLAR L.E.D. WITHOUT LOCK-DOWN DOOR: CODE ML

OPTIONAL PLAIN COVER FEATURES:
PUSH BUTTON WITHOUT LOCK-DOWN DOOR: CODE M
BI - POLAR L.E.D. STATUS LAMP: CODE L

COIL VOLTAGE: 120A
6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS

COIL MEASURED @ 25°C

STANDARD PART NUMBERS	PLAIN COVER	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP			
783XCXM4L-24A	783XCXC-24A	24 VAC, 50/60 Hz	84.5 Ω
783XCXM4L-120A	783XCXC-120A	120 VAC, 50/60 Hz	2220 Ω
783XCXM4L-240A		240 VAC, 50/60 Hz	9120 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP			
783XCXM4L-12D		12 VDC	96 Ω
783XCXM4L-24D	783XCXC-24D	24 VDC	380 Ω
783XCXM4L-110D		110 VDC	7340 Ω
AC OPERATED - PRINTED CIRCUIT, 15 AMP			
783XCXTM4L-120A		120 VAC, 50/60 Hz	2220 Ω
DC OPERATED - PRINTED CIRCUIT, 15 AMP			
783XCXTM4L-12D		12 VDC	96 Ω
783XCXTM4L-24D		24 VDC	388 Ω

FEATURES**BENEFITS****FLAG INDICATOR:**

SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.

BI - POLAR

SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.

L.E.D. STATUS LAMP:

ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER.

PUSH BUTTON:

IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.

LOCK-DOWN DOOR:

WHEN ACTIVATED, HOLDS PUSH BUTTON AND CONTACTS IN THE OPERATE POSITION.

EXCELLENT FOR ANALYZING CIRCUIT PROBLEMS.

FINGER-GRIP COVER:

ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE

EASILY THAN CONVENTIONAL RELAYS.

I.D. TAG/WRITE LABEL:

USED FOR IDENTIFICATION OF RELAYS IN MULTI-RELAY CIRCUITS.

COVER ADAPTERS:

DIN RAIL FLANGE ADAPTER OR TOP/BOTTOM FLANGE ADAPTER, ALLOWS THE 784 RELAY TO BE DIRECT MOUNTED TO A DIN RAIL OR PANEL.

4PDT, 15 AMPS

 UL Recognized
 File No. E43641

 LR40787

 LISTED 367G
 IND. CONT. EQ.

C US

WHEN USED WITH
 SOCKETS 70-784D-1,CURRENT LIMITED TO
 RATING OF RELAY OR
 SOCKET WHICHEVER
 IS LESS**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	75% of nominal voltage or less for DC coils, 80% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%, AC- 30% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±10% measured @ 25°C
Coil Power:	1.5 watts DC, 2.0 VA (60Hz) AC @ 25°C (4PDT)
Insulation System:	Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation:	3.0 watts DC, 3.4 VA (60Hz) AC. @ 25°C
Duty:	Continuous.

CONTACTS

Contact Material:	Solid silver alloy, gold flashed
Contact Rating:	15 amps @ 110/120 VAC 50/60Hz, (30 amps max.) 12 amps @ 28 VDC (30 amps max.) 12 amps @ 220/277 VAC 50/60Hz (20 amps max.) 1/2Hp @ 120 VAC, 3/4 Hp @ 250 VAC. B300 pilot duty
Contact Resistance:	50 milliohms maximum initial resistance

DIELECTRIC STRENGTH

Contacts to Coil:	2500 V rms
Across Open Contacts:	1000 V rms
Pole to Pole:	2500 V rms
Contacts to Frame:	2500 V rms
Insulation Resistance:	100 megohms min. @ 500 VDC

TEMPERATURE

Operating:	-30°C to +70°C
Storage:	-30°C to +105°C

VIBRATION RESISTANCE

Functional:	6 g's, 10 to 55 Hz (0.6 mm double amplitude)
-------------	--

SHOCK RESISTANCE

Functional:	10 g's
-------------	--------

LIFE EXPECTANCY

Electrical:	150,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Weight:	80 grams approx.


**STANDARD COVER****STANDARD COVER WITH
 FLANGE ADAPTER 16-784C1
 ON TOP 16-784C1****STANDARD COVER WITH
 FLANGE ADAPTER 16-784C1
 ON BOTTOM****STANDARD COVER
 WITH DIN ADAPTER
 16-784C****DIN ADAPTER ORDERED AND
 SHIPPED SEPARATELY**
Mating Sockets
70-784D-1: SCREW/DIN
 See section, 8 page 22


4PDT, 15 AMPS

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).


**PRINTED CIRCUIT
MOUNTING HOLE LAYOUT**
(BOTTOM VIEW)

NEW
From The Market
Leader in Industrial
Relays



AVAILABLE WITHOUT
LOCK-DOWN DOOR: CODE "M"

WIRING DIAGRAM
(VIEWED FROM PIN END)



ORDERING CODE FOR RELAYS

CLASS: **784**

CONTACT CONFIGURATION: **XDX**
4PDT: XDX

TERMINAL STYLE: **M4L**
QUICK CONNECT SOLDER / PLUG-IN
TERMINALS: NO CODE
PRINTED CIRCUIT TERMINALS: CODE T

OPTIONAL PLAIN COVER: **-120A**
CODE C

STANDARD COVER FEATURES:
PUSH BUTTON & LOCK-DOWN DOOR: CODE M4
L.E.D. STATUS LAMP: CODE L

OPTIONAL STANDARD COVER DELETION:
PUSH BUTTON AND L.E.D. WITHOUT
LOCK-DOWN DOOR: CODE ML

OPTIONAL PLAIN COVER FEATURES:
PUSH BUTTON WITHOUT LOCK-DOWN DOOR: CODE M
L.E.D. STATUS LAMP: CODE L

COIL VOLTAGE:
6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS

STANDARD PART NUMBERS	COIL MEASURED @ 25°C		
	PLAIN COVER	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP			
784XDXM4L-24A	784XDXC-24A	24 VAC, 50/60 Hz	84.5 Ω
784XDXM4L-120A	784XDXC-120A	120 VAC, 50/60 Hz	2220 Ω
784XDXM4L-240A		240 VAC, 50/60 Hz	9120 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP			
784XDXM4L-12D		12 VDC	96 Ω
784XDXM4L-24D	784XDXC-24D	24 VDC	380 Ω
784XDXM4L-110D		110 VDC	7340 Ω
AC OPERATED - PRINTED CIRCUIT, 15 AMP			
784XDXTM4L-120A		120 VAC, 50/60 Hz	2220 Ω
DC OPERATED - PRINTED CIRCUIT, 15 AMP			
784XDXTM4L-12D		12 VDC	96 Ω
784XDXTM4L-24D		24 VDC	388 Ω

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage :	75% of nominal voltage or less for DC coils, 80% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%. AC-30%. Of nominal voltage or more
Max. Voltage :	110%
Resistance:	±15% measured @ 25°C
Coil Power:	0.9 to 1.1 watts DC., 1.0 to 1.2 VA (60Hz) AC. @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation:	2.3 watts DC, 2.55 VA (60Hz) AC. 5 minutes max. @ 40°C
Duty:	Continuous

CONTACTS

Contact Material:	3 amps bifurcated silver gold plated, 3 amps silver gold flashed, 5 & 15 amps silver alloy, gold flashed
Contact Rating:	SPDT: 15 amps @ 120/240 VAC, 30 VDC. 1/3 Hp, 120 VAC. 1/2 Hp 240 VAC, B300 pilot duty DPDT: 15 amps @ 120/240 VAC, 10 amps @ 30 VDC, 10 amps @ 120/240 VAC, G.P. 1/3 Hp, 120 VAC. 1/2Hp 240 VAC, B300 pilot duty 4PDT: Bifurcated 3 amps @ 120/240 VAC, 30 VDC. 1/16 Hp (2.8 amps FLA), 120 VAC. Pilot duty - 5 amps make, 1/2 amps break, 3 amps continuous, 120 VAC. 4PDT: 3 amps @ 120 VAC, 30 VDC 1/10 Hp 120/240 VAC, C300 pilot duty 4PDT: 5 amps @ 120/240 VAC, 30 VDC 1/6 Hp 120/240 VAC, C300 pilot duty

DIELECTRIC STRENGTH

Coil to Frame:	1500 V rms
Across Open Contacts:	1000 V rms
Contacts to Frame:	1500 V rms
Insulation Resistance:	100 megohms @ 500 VDC

TEMPERATURE

Operating:	-40°C to +70°C
Storage:	-40°C to +105°C

VIBRATION RESISTANCE

Functional:	5 g, 10 to 55Hz; 1 mm (double amplitude)
-------------	--

SHOCK RESISTANCE

Functional:	20 g
Mechanical:	100 g

LIFE EXPECTANCY

Electrical:	200,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Weight:	SPDT & DPDT 35 grams approx.

**SPDT, DPDT & 4PDT,
3, 5 & 15 AMPS**

UL **us**
UL Recognized
File No. E52197



**LISTED 367G
IND. CONT. EQ.**
C US
WHEN USED WITH
SOCKETS
70-459-1 OR 70-461-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS



COMPLIES WITH REQUIREMENTS OF

- * IEC STANDARDS 947-4-1 AND 947-5-1 LOW VOLTAGE DIRECTIVE
- * IEC = INTERNATIONAL ELECTROTECHNICAL COMMISSION
- * CE TESTING AND EVALUATION PERFORMED BY THE UNDERWRITERS LABORATORIES AS A THIRD PARTY PARTICIPANT

**MANUFACTURED UNDER
ISO 9002 & QS 9000**



**4PDT, QUICK CONNECT
SOLDER/PLUG-IN
3 OR 5 AMP**



**4PDT, PRINTED CIRCUIT
3 OR 5 AMP**



**SPDT, DPDT, QUICK CONNECT
SOLDER/PLUG-IN 15 AMP**



**SPDT, DPDT, PRINTED CIRCUIT
15 AMP**

Mating Sockets

**70-782D-1, 70-459-1, 70-461-1:
SCREW/DIN
70-401-1, 70-378-1: SOLDER
70-402-1, 70-379-1:
PRINTED CIRCUIT**

See section 8, page 13, 14, 15, 20




SPDT, 15 AMPS

OUTLINE DIMENSIONS


DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

QUICK CONNECT SOLDER / PLUG-IN TERMINALS



PRINTED CIRCUIT TERMINALS

PRINTED CIRCUIT MOUNTING HOLE LAYOUT (BOTTOM VIEW)



DIN ADAPTER 16-782C



FLANGE ADAPTER 16-782C1




NEW SLOTTED PLAIN COVER, ALLOWS FOR INSTALLATION OF THE OPTIONAL TOP MOUNT DIN OR TOP/BOTTOM MOUNT FLANGE ADAPTERS. ADAPTERS SOLD SEPARATELY



OBSERVE POLARITY
WHEN L.E.D. STATUS LAMP
IS INSTALLED ACROSS COIL
(DC STYLES TYPICAL)




WIRING DIAGRAMS

(VIEWED FROM PIN END)




COIL MEASURED @ 25°C

STANDARD PART NUMBERS SPDT	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP		
W78ARCSX-108	12 VAC, 50/60 Hz	46 Ω
W78ARCSX-109	24VAC, 50/60 Hz	180 Ω
W78ARCSX-111	120 VAC, 50/60 Hz	4430 Ω
W78ARCSX-112	240 VAC, 50/60 Hz	15,700 Ω
AC OPERATED - SOLDER/PLUG-IN WITH INDICATOR LAMP, 15 AMP		
W78ARNCSX-8	24 VAC, 50/60 Hz	180 Ω
W78ARNCSX-9	120VAC, 50/60 Hz	4430 Ω
W78ARNCSX-10	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP		
W78RCSX-96	6 VDC	40 Ω
W78RCSX-97	12 VDC	160 Ω
W78RCSX-98	24VDC	650 Ω
W78RCSX-100	110 VDC	11,000 Ω
DC OPERATED - SOLDER/PLUG-IN WITH INDICATOR LAMP, 15 AMP		
W78RNCX-10	24 VDC	650 Ω
AC OPERATED - PRINTED CIRCUIT TERMINAL, 15 AMP		
W78ARPCX-81	12 VAC	46 Ω
W78ARPCX-82	24 VAC	180 Ω
W78ARPCX-84	120 VAC	4430 Ω
DC OPERATED - PRINTED CIRCUIT TERMINAL, 15 AMP		
W78RPCX-79	12 VDC	160 Ω
W78RPCX-83	24 VDC	650 Ω
W78RPCX-85	110 VDC	11,000 Ω

DPDT, 15 AMPS**OUTLINE DIMENSIONS**
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).**QUICK CONNECT
SOLDER / PLUG-IN TERMINALS****PRINTED CIRCUIT
MOUNTING HOLE LAYOUT
(BOTTOM VIEW)****PRINTED CIRCUIT
TERMINALS****DIN ADAPTER
16-782C****FLANGE ADAPTER
16-782C1**

NEW SLOTTED PLAIN COVER, ALLOWS FOR INSTALLATION OF THE OPTIONAL TOP MOUNT DIN OR TOP/BOTTOM MOUNT FLANGE ADAPTERS. ADAPTERS SOLD SEPARATELY

**WIRING DIAGRAM
(VIEWED FROM PIN END)**


SEE CLASS 782XBX FOR
PART NUMBERS WITH
L.E.D. STATUS LAMP
AND PUSH BUTTON

COIL MEASURED @ 25°C

STANDARD PART NUMBERS DPDT	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 15 AMP		
W78ARCSX-7	6 VAC, 50/60 Hz	12.2 Ω
W78ARCSX-9	24VAC, 50/60 Hz	180 Ω
W78ARCSX-11	120 VAC, 50/60 Hz	4430 Ω
W78ARCSX-12	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - SOLDER/PLUG-IN, 15 AMP		
W78RCSX-6	6 VDC	40 Ω
W78RCSX-7	12 VDC	160 Ω
W78RCSX-8	24VDC	650 Ω
W78RCSX-9	48 VDC	2,600 Ω
W78RCSX-10	110 VDC	11,000 Ω
AC OPERATED - PRINTED CIRCUIT TERMINAL, 15 AMP		
W78ARPCX-5	120 VAC, 50/60 Hz	4430 Ω
W78ARPCX-6	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - PRINTED CIRCUIT TERMINAL, 15 AMP		
W78RPCX-1	6VDC	40 Ω
W78RPCX-2	12 VDC	160 Ω
W78RPCX-3	24 VDC	650 Ω

RETROFITS POTTER & BRUMFIELD K10.
SEE END OF SECTION 1 FOR CROSS REFERENCE

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



PRINTED CIRCUIT MOUNTING HOLE LAYOUT
(BOTTOM VIEW)

4PDT, 3 & 5 AMPS



DIN ADAPTER
16-782C

FLANGE ADAPTER
16-782C1



NEW SLOTTED PLAIN COVER, ALLOWS FOR INSTALLATION OF THE OPTIONAL TOP MOUNT DIN OR TOP/BOTTOM MOUNT FLANGE ADAPTERS. ADAPTERS SOLD SEPARATELY



SEE CLASS 782XDX FOR PART NUMBERS WITH L.E.D. STATUS LAMP AND PUSH BUTTON

ALL 4 POLE RELAYS HAVE OPPOSITE POLARITY ARC BARRIERS AS A STANDARD FEATURE TO PROVIDE GREATER VOLTAGE PROTECTION BETWEEN ADJACENT POLES

WIRING DIAGRAM
(VIEWED FROM PIN END)



COIL MEASURED @ 25°C

STANDARD PART NUMBERS 4PDT	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
W78ATCSX-2	12 VAC, 50/60 Hz	46 Ω
W78ATCSX-3	24 VAC, 50/60 Hz	180 Ω
W78ATCSX-5	120 VAC, 50/60 Hz	4430 Ω
W78ATCSX-6	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - SOLDER/PLUG-IN, 3 AMP, BIFURCATED		
W78TCSX-1	6 VDC	40 Ω
W78TCSX-2	12 VDC	160 Ω
W78TCSX-3	24 VDC	650 Ω
W78TCSX-5	110 VDC	11,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 3 AMP		
W78ACSX-2	12 VAC, 50/60 Hz	46 Ω
W78ACSX-3	24 VAC, 50/60 Hz	180 Ω
W78ACSX-5	120 VAC, 50/60 Hz	4430 Ω
W78ACSX-6	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - SOLDER/PLUG-IN, 3 AMP		
W78CSX-1	6 VDC	40 Ω
W78CSX-2	12 VDC	160 Ω
W78CSX-3	24 VDC	650 Ω
W78CSX-6	110 VDC	11,000 Ω
AC OPERATED PRINTED CIRCUIT, 3 AMP		
W78APCX-3	24 VAC, 50/60 Hz	180 Ω
W78APCX-5	120 VAC, 50/60 Hz	4430 Ω
DC OPERATED PRINTED CIRCUIT, 3 AMP		
W78PCX-2	12 VDC	160 Ω
W78PCX-3	24 VDC	650 Ω
W78PCX-6	110 VDC	11,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 5 AMP		
W78KACSX-15	24 VAC, 50/60 Hz	180 Ω
W78KACSX-17	120 VAC, 50/60 Hz	4430 Ω
W78KACSX-18	240 VAC, 50/60 Hz	15,700 Ω
DC OPERATED - SOLDER/PLUG-IN, 5 AMP		
W78KCSX-12	12 VDC	160 Ω
W78KCSX-13	24 VDC	650 Ω

FEATURES**BENEFITS****FLAG INDICATOR:**

SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.

**BI - POLAR
L.E.D. STATUS LAMP:**

SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.

PUSH BUTTON:

ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER. IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.

LOCK-DOWN DOOR:

WHEN ACTIVATED, HOLDS PUSH BUTTON AND CONTACTS IN THE OPERATE POSITION. EXCELLENT FOR ANALYZING CIRCUIT PROBLEMS.

FINGER-GRIP COVER:

ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE EASILY THAN CONVENTIONAL RELAYS.

I.D. TAG/WRITE LABEL:

USED FOR IDENTIFICATION OF RELAYS IN MULTI - RELAY CIRCUITS.

DPDT & 3PDT, 12 AMPSUL Recognized
File No. E43641LISTED 367G
IND. CONT. EQ.

C US

WHEN USED WITH
SOCKETS
70-464-1, 70-465-1,
70-750D8-1 OR
70-750D11-1CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	80% of nominal voltage or less for DC coils, 85% of nominal voltage or less for AC coils
Dropout Voltage:	DC-10%, AC-30% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±10% measured @ 25°C
Coil Power:	1.4 watts DC. 2 VA to 3.55 VA (60Hz) AC. @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Max. Coil Dissipation:	3.0 watts DC. 3.4 VA (60Hz) AC. @ 25°C
Duty:	Continuous

CONTACTS

Contact Material:	Silver alloy, gold flashed
Contact Rating:	12 amps, 120 / 240 VAC 50/60Hz, 12 amps, 28 VDC 1/3Hp 120 VAC, 1/2Hp 240 VAC
Contact Resistance:	50 milliohms max. @ 10 amps, 120 VAC or 24 VDC contacts conditioned for 50 make and break, operations @ 1 second "ON" & 1 second "OFF"

DIELECTRIC STRENGTH

Contacts to Coil:	2500 V rms
Across open Contacts:	1500 V rms
Pole to Pole:	2500 V rms
Contacts to Frame:	2500 V rms
Insulation Resistance:	100 megohms @ 500 VDC

TEMPERATURE

Operating:	-40°C to +50°C. (AC), -40°C +65°C. (DC)
Storage:	-40°C to +100°C

LIFE EXPECTANCY

Electrical:	200,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Weight:	79 grams approx.

MANUFACTURED UNDER
ISO 9002 & QS 9000**Mating Sockets**70-750D8-1, 70-750D11-1,
70-464-1, 70-465-1: SCREW/DIN
70-169-1, 70-170-1: SCREW/PANEL


See section 8, page 7 - 12




NEW
From The Market
Leader in Industrial
Relays

DPDT & 3PDT, 12 AMPS

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



WIRING DIAGRAMS
(VIEWED FROM PIN END)



BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS

ORDERING CODE FOR RELAYS

750 **XBX** **M4L-120A**

CLASS: _____

CONTACT CONFIGURATION: _____
DPDT: XBX
3PDT: XCX

STANDARD FEATURES: _____
PUSH BUTTON &
LOCK DOWN DOOR: **CODE M4**
BI - POLAR L.E.D. STATUS LAMP: **CODE L**

OPTIONAL FEATURES: _____
PUSH BUTTON WITHOUT
LOCK DOWN DOOR: **CODE M**

COIL VOLTAGE: _____
6, 12, 24, 120, 220/230, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - 8 PIN OCTAL, 12 AMP			
750XBM4L-24A	DPDT	24 VAC, 50/60Hz	72 Ω
750XBM4L-120A	DPDT	120 VAC, 50/60Hz	1,700 Ω
750XBM4L-240A	DPDT	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - 8 PIN OCTAL, 12 AMP			
750XBM4L-12D	DPDT	12 VDC	120 Ω
750XBM4L-24D	DPDT	24 VDC	470 Ω
750XBM4L-110D	DPDT	110 VDC	10,000 Ω
AC OPERATED - 11 PIN OCTAL, 12 AMP			
750XXM4L-24A	3PDT	24 VAC, 50/60Hz	72 Ω
750XXM4L-120A	3PDT	120 VAC, 50/60Hz	1,700 Ω
750XXM4L-240A	3PDT	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - 11 PIN OCTAL, 12 AMP			
750XXM4L-12D	3PDT	12 VDC	120 Ω
750XXM4L-24D	3PDT	24 VDC	470 Ω
750XXM4L-110D	3PDT	110 VDC	10,000 Ω

CADMIUM-FREE CONTACTS AVAILABLE,
CONTACT FACTORY FOR DETAILS

UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
2 POLES	12 AMP	120 VAC	DC	RESISTIVE
	10 AMP	240 VAC	50/60 Hz	RESISTIVE
	10 AMP	28 VDC	DC	RESISTIVE
3 POLES	10 AMP	120/240 VAC	50/60 Hz	RESISTIVE
	10 AMP	28 VDC	DC	RESISTIVE
2 & 3 POLES	1/3 HP	120 VAC	50/60 Hz	MOTOR
	1/2 HP	240 VAC	50/60 Hz	MOTOR

CONTACT RATINGS WITH BLOW-OUT MAGNET FOR DC SWITCHING (NOT UL)

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
2 POLES	3 AMP	150 VDC	DC	RESISTIVE

**DPDT & 3PDT
3, 10 & 12 AMPS**

UL us
UL Recognized
File No. E 43641

SP 168986

CE

UL LISTED 367G
IND. CONT. EQ.
C US

WHEN USED WITH
SOCKETS
70-464-1 OR 70-465-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE

* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION

* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage: 80% of nominal voltage or less for DC coils,
85% of nominal voltage or less for AC coils

Dropout Voltage: DC-10%, AC-30% of nominal voltage or more

Max. Voltage: 110%

Resistance: $\pm 10\%$ measured @ 25°C

Coil Power: 1.2 watts DC. 2 VA to 2.75 (60Hz) AC. @ 25°C

Insulation System: Class "B" (130°C per UL standard 1446)

Max. Coil Dissipation: 3.0 watts DC. @ 25°C.

Duty: Continuous.

CONTACTS

Contact Material: Silver alloy, gold flashed standard., gold diffused contacts available

Contact Rating: See "UL CONTACT LOAD RATINGS TABLE"

Contact Resistance: 50 milliohms max. @ 10 amps, 120 VAC or 24 VDC contacts conditioned for 50 make and break operations @ 1 second "ON" & 1 second "OFF"

DIELECTRIC STRENGTH

Contacts to Coil: 1500 V rms

Coil to Frame: 1500 V rms

Across Open Contacts: 500 V rms

Pole to Pole: 1500 V rms

Contacts to Frame: 1500 V rms

Insulation Resistance: 1000 megohms @ 500 VDC

TEMPERATURE

Operating: -45°C to +55°C (AC), -45°C to +70°C (DC).

Storage: -40°C to +105°C

VIBRATION RESISTANCE

Functional: 10 to 55Hz; 1 mm (double amplitude)

SHOCK RESISTANCE

Functional: 10 g's

Mechanical: 100 g's

LIFE EXPECTANCY

Electrical: 100,000 operations @ rated resistive load

Mechanical: 5,000,000 operations @ no load

MISCELLANEOUS

Operating Position: Any

Insulation Material: Molded plastic

Enclosure: Polycarbonate dust cover

Terminals: 8 or 11 pin octal plug-in

Weight: 99.2 grams approx.

**MANUFACTURED UNDER
ISO 9002 & QS 9000**




Mating Sockets
70-750D8-1, 70-750D11-1,
70-464-1, 70-465-1: SCREW/DIN
70-169-1, 70-170-1: SCREW/PANEL
See section 8, page 7 - 12





OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**DPDT & 3PDT
3, 10 & 12 AMPS**

SEE CLASS 750 FOR
PART NUMBERS WITH
L.E.D. STATUS LAMP
AND PUSH BUTTON

WIRING DIAGRAMS
(VIEWED FROM PIN END)

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED, 12 AMP			
A314XBX48P-24A	DPDT	24 VAC, 50/60Hz	85 Ω
A314XBX48P-120A	DPDT	120VAC, 50/60Hz	2250 Ω
A314XBX48P-240A	DPDT	220/240 VAC, 50/60Hz	9110 Ω
AC OPERATED, 10 AMP			
A314XCX48P-24A	3PDT	24 VAC, 50/60Hz	85 Ω
A314XCX48P-120A	3PDT	120 VAC, 50/60Hz	1700 Ω
A314XCX48P-240A	3PDT	220/240 VAC, 50/60Hz	9110 Ω
DC OPERATED, 12 AMP			
A314XBX48P-12D	DPDT	12VDC	120 Ω
A314XBX48P-24D	DPDT	24 VDC	472 Ω
DC OPERATED, 10 AMP			
A314XCX48P-12D	3PDT	12 VDC	120 Ω
A314XCX48P-24D	3PDT	24 VDC	472 Ω
AC OPERATED WITH BLOW - OUT MAGNET, 3 AMP FOR DC SWITCHING			
A314XBX48P69-24A	DPDT	24 VAC	85 Ω
A314XBX48P69-120A	DPDT	120VAC	1700 Ω
DC OPERATED WITH BLOW - OUT MAGNET, 3 AMP FOR DC SWITCHING			
A314XBX48P69-12D	DPDT	12 VDC	120 Ω
A314XBX48P69-24D	DPDT	24 VDC	472 Ω
A314XBX48P69-110D	DPDT	110 VDC	10,000 Ω

RETROFITS POTTER & BRUMFIELD KRPA.
SEE END OF SECTION 1 FOR CROSS REFERENCE

FEATURES**FLAG INDICATOR:** SHOWS RELAY STATUS IN MANUAL OR POWERED CONDITION.**BI - POLAR
L.E.D. STATUS LAMP:** SHOWS COIL "ON" OR "OFF" STATUS. IDEAL IN LOW LIGHT CONDITIONS.**PUSHBUTTON:** ALLOWS FOR MANUAL OPERATION OF RELAY WITHOUT THE NEED FOR COIL POWER. IDEAL FOR FIELD SERVICE PERSONNEL TO TEST CONTROL CIRCUITS.**LOCK-DOWN DOOR:** WHEN ACTIVATED, HOLDS PUSH BUTTON AND CONTACTS IN THE OPERATE POSITION. EXCELLENT FOR ANALYZING CIRCUIT PROBLEMS.**FINGER-GRIP COVER:** ALLOWS OPERATOR TO REMOVE RELAYS FROM SOCKETS MORE EASILY THAN CONVENTIONAL RELAYS.**I.D. TAG/WRITE LABEL:** USED FOR IDENTIFICATION OF RELAYS IN MULTI - RELAY CIRCUITS.**BENEFITS****DPDT & 3PDT, 12 AMPS****cULus**
UL Recognized
File No. E43641**SP** LR40787**UL** LISTED 367G
IND. CONT. EQ.
C USWHEN USED WITH
SOCKET 70-463-1CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS**CE**
COMPLIES WITH REQUIREMENTS OF* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage: 80% of nominal voltage or less for DC coils,
85% of nominal voltage or less for AC coils

Dropout Voltage: DC-10%, AC-30% of nominal voltage or more

Max. Voltage: 110%

Resistance: $\pm 10\%$ measured @ 25°C

Coil Power: 1.4 watts DC., 2 VA to 3.55 VA (60Hz) AC @ 25°C

Insulation System: Class "B" (130°C per UL standard 1446)

Max. Coil Dissipation: 3.0 watts DC. 3.4 VA (60Hz) AC. @ 25°C

Duty: Continuous

CONTACTS

Contact Material: Silver alloy, gold flashed

Contact Rating: 12 amps, 120/240 VAC 50/60Hz, 12 amps, 28 VDC
1/3Hp 120 VAC, 1/2Hp 240 VAC.

Contact Resistance: 50 milliohms max. @ 10 amps, 120 VAC or 24 VDC
contacts conditioned for 50 make and break
operations @ 1 second "ON" & 1 second "OFF"

DIELECTRIC STRENGTH

Contacts to Coil: 2500 V rms

Across Open Contacts: 1500 V rms

Pole to Pole: 2500 V rms

Contacts to Frame: 2500 V rms

Insulation Resistance: 100 megohms @ 500 VDC

TEMPERATURE

Operating: -40°C to +50°C. (AC), -40°C +65°C. (DC)

Storage: -40°C to +100°C

LIFE EXPECTANCY

Electrical: 200,000 operations @ rated resistive load

Mechanical: 5,000,000 operations @ no load

MISCELLANEOUS

Operating Position: Any


Insulation Material: Molded plastic

Enclosure: Polycarbonate dust cover

Weight: 88 grams approx.

**Mating Sockets****70-463-1: SCREW/DIN****70-124-1: SOLDER****70-178-1, 70-178-2: PRINTED CIRCUIT****70-124-2: QUICK CONNECT**


See section 8, page 16, 17





NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**DPDT & 3PDT, 12 AMPS****WIRING DIAGRAMS**

(VIEWED FROM PIN END)



BI - POLAR
L.E.D. STATUS LAMP
ALLOWS FOR REVERSE
POLARITY APPLICATIONS

ORDERING CODE FOR RELAYS

CLASS: 788 XBX M4L - 120A

CONTACT CONFIGURATION:

DPDT: XBX

3PDT: XCX

TERMINAL STYLE:

SOLDER PLUG-IN TERMINALS: NO CODE

PRINTED CIRCUIT TERMINALS: CODE T

STANDARD FEATURES:

PUSH BUTTON &
LOCK DOWN DOOR: CODE M4

BI - POLAR L.E.D. STATUS LAMP: CODE L

OPTIONAL FEATURES:

PUSH BUTTON WITHOUT LOCK DOWN DOOR: CODE M

COIL VOLTAGE:

6, 12, 24, 120, 220 / 230, 240 **ADD "A" FOR AC COILS**

6, 12, 24, 48, 110 **ADD "D" FOR DC COILS**

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - SOLDER/PLUG-IN, 12 AMP			
788XBXM4L-24A	DPDT	24 VAC, 50/60Hz	72 Ω
788XBXM4L-120A	DPDT	120 VAC, 50/60Hz	1,700 Ω
788XBXM4L-240A	DPDT	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 12 AMP			
788XBXM4L-12D	DPDT	12 VDC	120 Ω
788XBXM4L-24D	DPDT	24 VDC	470 Ω
788XBXM4L-110D	DPDT	110 VDC	10,000 Ω
AC OPERATED - SOLDER/PLUG-IN, 12 AMP			
788XCXM4L-24A	3PDT	24 VAC, 50/60Hz	72 Ω
788XCXM4L-120A	3PDT	120 VAC, 50/60Hz	1,700 Ω
788XCXM4L-240A	3PDT	240 VAC, 50/60Hz	9,100 Ω
DC OPERATED - SOLDER/PLUG-IN, 12 AMP			
788XCXM4L-12D	3PDT	12 VDC	120 Ω
788XCXM4L-24D	3PDT	24 VDC	470 Ω
788XCXM4L-110D	3PDT	110 VDC	10,000 Ω

CADMIUM-FREE CONTACTS AVAILABLE,
CONTACT FACTORY FOR DETAILS

UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
1 POLE THRU 3 POLES	15 AMP	120/240 VAC	50/60 Hz	RESISTIVE
	10 AMP	28 VDC	DC	RESISTIVE
	1/3 HP	120 VAC	50/60 Hz	MOTOR
	1/2 HP	240 VAC	50/60 Hz	MOTOR
	3 AMP	600 VAC	50/60 Hz	RESISTIVE

SPDT, DPDT & 3PDT, 15 AMPS

UL **us**
UL Recognized
File No. E13224

SP 168986

UL LISTED 367G
IND. CONT. EQ.
C **US**
WHEN USED WITH
SOCKETS 70-463-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

CE

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND 947-5-1 LOW VOLTAGE DIRECTIVE

* IEC = INTERNATIONAL ELECTROTECHNICAL COMMISSION

* CE TESTING AND EVALUATION PERFORMED BY THE UNDERWRITERS LABORATORIES AS A THIRD PARTY PARTICIPANT

**MANUFACTURED UNDER
ISO 9002 & QS 9000****GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	80% of nominal voltage or less for DC coils 85% of nominal voltage or less for AC coils
Dropout Voltage:	10% of nominal voltage or more
Max. Voltage:	110%
Resistance:	± 10 % measured at 25°C
Coil Power:	1.2 watts for DC coils, 2 VA to 2.75 VA for AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Maximum Coil Dissipation:	3.0 watts max. DC
Duty:	Continuous

CONTACTS

Contact Material:	0.187 silver alloy, gold flashed
Contact Resistance:	50 milliohms maximum initial resistance at rated current
Contact Ratings:	See "UL CONTACT LOAD RATINGS TABLE"

DIELECTRIC STRENGTH

Contacts to Coil:	2000 V rms
Across Open Contacts:	500 V rms
Pole to Pole	2000 V rms
Contacts to Frame:	2000 V rms
Insulation Resistance:	1000 megohms @ 500 VDC

TEMPERATURE


Operating:	-30°C to +50°C. (AC), -30°C to +65°C. (DC)
Storage	-30°C to +100°C

LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Terminals:	0.187 x 0.032 quick connect flange or 0.187 x 0.020 solder/plug-in. Optional printed circuit terminals available
Weight:	88 grams approx.

**PLUG-IN****FLANGE MOUNT****OPTIONAL PRINTED CIRCUIT
TERMINAL CONSULT FACTORY.****OPTIONAL TOP FLANGE
COVER CONSULT FACTORY.****OPTIONAL DIN COVER
CONSULT FACTORY.****Mating Sockets**

70-463-1: SCREW/DIN
70-124-1: SOLDER
70-178-1, 70-178-2: PRINTED CIRCUIT
70-124-2: QUICK CONNECT


See section 8, page 16, 17



SPDT, DPDT & 3PDT, 15 AMPS

OUTLINE DIMENSIONS




DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



SEE CLASS 788 FOR
PART NUMBERS WITH
L.E.D. STATUS LAMP
AND PUSH BUTTON

WIRING DIAGRAMS

(VIEWED FROM PIN END)





STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED SOLDER/PLUG-IN, 15 AMP			
A283XAXC-120A	SPDT	120 VAC, 50/60Hz	2250 Ω
A283XAXC-240A	SPDT	220/240 VAC, 50/60Hz	9100 Ω
A283XBXC-24A	DPDT	24 VAC, 50/60Hz	75 Ω
A283XBXC-120A	DPDT	120 VAC, 50/60Hz	2250 Ω
A283XBXC-240A	DPDT	220/240 VAC, 50/60Hz	9100 Ω
A283XCXC-24A	3PDT	24 VAC, 50/60Hz	72 Ω
A283XCXC-120A	3PDT	120 VAC, 50/60Hz	1700 Ω
A283XCXC-240A	3PDT	220/240 VAC, 50/60Hz	7200 Ω
DC OPERATED SOLDER/PLUG-IN, 15 AMP			
A283XAXC-12D	SPDT	12 VDC	120 Ω
A283XAXC-24D	SPDT	24 VDC	472 Ω
A283XBXC-12D	DPDT	12 VDC	120 Ω
A283XBXC-24D	DPDT	24 VDC	472 Ω
A283XBXC-110D	DPDT	110 VDC	10,000 Ω
A283XCXC-12D	3PDT	12 VDC	120 Ω
A283XCXC-24D	3PDT	24VDC	472 Ω

RETROFITS POTTER & BRUMFIELD KUP.
SEE END OF SECTION 1 FOR CROSS REFERENCE

SPDT, DPDT & 3PDT, 15 AMPS


OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).




SEE CLASS 388J FOR
PART NUMBERS WITH
L.E.D. STATUS LAMP
AND PUSH BUTTON

WIRING DIAGRAMS


(VIEWED FROM PIN END)



DPDT



SPDT




3PDT

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED, 15 AMP			
A283XAXC1-120A	SPDT	120 VAC, 50/60Hz	2250 Ω
A283XAXC1-240A	SPDT	220/240 VAC, 50/60Hz	9100 Ω
A283XBXC1-120A	DPDT	120 VAC, 50/60Hz	2250 Ω
A283XBXC1-240A	DPDT	220/240 VAC, 50/60Hz	9100 Ω
A283XCXC1-120A	3PDT	120 VAC, 50/60Hz	1700 Ω
A283XCXC1-240A	3PDT	220/240 VAC, 50/60Hz	7200 Ω
DC OPERATED, 15 AMP			
A283XAXC1-12D	SPDT	12 VDC	120 Ω
A283XAXC1-24D	SPDT	24 VDC	472 Ω
A283XBXC1-12D	DPDT	12 VDC	120 Ω
A283XBXC1-24D	DPDT	24 VDC	472 Ω
A283XCXC1-24D	3PDT	24 VDC	472 Ω

RETROFITS POTTER & BRUMFIELD KUP.
SEE END OF SECTION 1 FOR CROSS REFERENCE

**DPDT , DPST-NO, SPST-NO-DM,
SPDT-NO-DM-DB & SPST-NO-DM,
3 & 10 AMPS, 150 VDC SWITCHING**

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).




UL CONTACT LOAD RATINGS TABLE FOR DC SWITCHING

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	TYPE OF LOAD
DPDT	3 AMP	150 VDC	RESISTIVE
SPST (DM and/or DB)	10 AMP	150 VDC	RESISTIVE
SPST (N.O or N.C)	10 AMP	150 VDC	RESISTIVE

**THE BLOWOUT MAGNET
STYLES HAVE THE SAME
LOAD SPECIFICATIONS
AS THE A283 ENCLOSED
PLUG-IN RELAYS, PLUS
THE ADDITIONAL LOAD
RATINGS CHARTED IN
TABLE ABOVE.
SEE A283 GENERAL
SPECIFICATIONS.**

WIRING DIAGRAMS
(VIEWED FROM PIN END)



DPDT



SPST-NO-DM

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED WITH BLOWOUT MAGNET, 3 AMP			
A283XBX69C-120A	DPDT	120 VAC, 50/60 Hz	2250 Ω
DC OPERATED WITH BLOWOUT MAGNET, 3 AMP			
A283XBX69C-12D	DPDT	12 VDC	120 Ω
A283XBX69C-24D	DPDT	24 VDC	472 Ω
A283XBX69C-110D	DPDT	110 VDC	10,000 Ω
AC OPERATED WITH BLOWOUT MAGNET, 10 AMP			
A283HXX69C-120A	SPST-NO (DM)	120 VAC, 50/60 Hz	2250 Ω
DC OPERATED WITH BLOWOUT MAGNET, 10 AMP			
A283HXX69C-48D	SPDT-NO (DM-DB)	48 VDC	1800 Ω
DC OPERATED WITH BLOWOUT MAGNET, 5 AMP			
A283BXX69C-24D	DPST-NO	24 VDC	472 Ω
A283BXX69C-48D	DPST-NO	48 VDC	1800 Ω
DC OPERATED WITH BLOWOUT MAGNET, 10 AMP			
A283HXX69C-12D	SPST-NO (DM)	12 VDC	120 Ω
A283HXX69C-24D	SPST-NO (DM)	24 VDC	472 Ω
A283HXX69C-48D	SPST-NO (DM)	48 VDC	1800 Ω
A283HXX69C-110D	SPST-NO (DM)	110 VDC	10,000 Ω

RETROFITS POTTER & BRUMFIELD KUEP.
SEE END OF SECTION 1 FOR CROSS REFERENCE

DPDT & 3PDT, 16 & 20 AMPS**UL CONTACT LOAD RATINGS TABLE**

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
2 POLES	20 AMP	300 VAC	50/60 Hz	RESISTIVE
	20 AMP	28 VDC	DC	RESISTIVE
3 POLES	16 AMP	277 VAC	50/60 Hz	RESISTIVE
	16 AMP	28 VDC	DC	RESISTIVE
2 & 3 POLES	3/4 HP	120 VAC	50/60 Hz	MOTOR
	1 HP	208-600 VAC	50/60 Hz	MOTOR

UP TO 20 AMP SWITCHING

cULus
UL Recognized
File No. E43641



LISTED 367G
IND. CONT. EQ.

C US

WHEN USED WITH
SOCKET 70-463-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS



COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND
947-5-1 LOW VOLTAGE DIRECTIVE

* IEC = INTERNATIONAL
ELECTROTECHNICAL COMMISSION

* CE TESTING AND EVALUATION
PERFORMED BY THE UNDERWRITERS
LABORATORIES AS A THIRD PARTY
PARTICIPANT

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage:	80% of nominal voltage or less for DC coils 85% of nominal voltage or less for AC coils
Dropout Voltage:	10% of nominal voltage or more
Resistance:	±10% measured at 25°C
Coil Power:	1.2 watts for DC coils, 2 VA to 2.75 VA for AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Maximum Coil Dissipation:	3.0 watts max. DC
Duty:	Continuous

CONTACTS

Contact material:	0.187 silver alloy, gold flashed
Contact Resistance:	50 milliohms maximum initial resistance at rated current
Contact Ratings:	See "UL CONTACT RATINGS TABLE"

DIELECTRIC STRENGTH

Contacts to Coil:	2000 V rms
Across Open Contacts:	1500 V rms
Pole to Pole:	2000 V rms
Contacts to Frame:	2000 V rms
Insulation Resistance:	1000 megohms @ 500 VDC

TEMPERATURE

Operating:	-30°C to +50°C. (AC), -30°C to +65°C. (DC)
Storage:	-30°C to +100°C




LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Terminals:	0.187 x 0.032 quick connect flange or 0.187 x 0.20 plug-in. Optional printed circuit terminals available
Weight:	94 grams approx.


**MANUFACTURED UNDER
ISO 9002 & QS 9000**

**PLUG-IN****FLANGE MOUNT****OPTIONAL DIN MOUNT COVER**


Mating Sockets
70-463-1: SCREW/DIN
70-124-1: SOLDER
70-178-1, 70-178-2: PRINTED CIRCUIT
70-124-2: QUICK CONNECT
See section 8, page 16, 17



NEW
From The Market
Leader in Industrial
Relays




OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).




**FLAG INDICATOR &
PUSH BUTTON STANDARD
ON 388J RELAYS.**

FLANGE COVER



WIRING DIAGRAMS
(VIEWED FROM PIN END)



ORDERING CODE FOR RELAYS

CLASS: 388J XCX C1 M- 240A
FLAG INDICATOR STANDARD FEATURE

CONTACT CONFIGURATION: DPDT: XBX, 3PDT: XCX

CONSTRUCTION STYLE: C1
* ENCLOSED, PLAIN COVER: **CODE C**
ENCLOSED, FLANGE COVER: **CODE C1**
ENCLOSED, 6-32 TAPPED CORE &
ANTI-ROTATION TAB: **CODE C2**
ENCLOSED 6-32 STUD & ANTI-ROTATION TAB: **CODE CS2**
ENCLOSED TOP FLANGE MOUNT: **CODE C3**
ENCLOSED DIN MOUNT: **CODE C4**

TERMINAL STYLE: M- 240A
† QUICK CONNECT SOLDER TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

OPTIONS: C1
BI - POLAR L.E.D. STATUS LAMP: **CODE L**
PUSH BUTTON: **CODE M**
MAGNETIC BLOWOUT: **CODE 69**
DC COIL SUPPRESSION: **CODE V**
AC COIL SUPPRESSION: **CODE V1**
RECTIFIED COIL: **CODE V2**

COIL VOLTAGE: 240A
6, 12, 24, 120, 240 ADD "A" FOR AC COILS
6, 12, 24, 48, 110 ADD "D" FOR DC COILS

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 16 AMP			
388JXCXC1M-240A	3PDT	240 VAC,50/60Hz	7200 Ω
388JXCXC1M-120A	3PDT	120 VAC,50/60Hz	1700 Ω
DC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 16 AMP			
388JXCXC1M-12D	3PDT	12 VDC	120 Ω
388JXCXC1M-24D	3PDT	24 VDC	470 Ω
AC OPERATED PLUG-IN WITH PUSH BUTTON, 16 AMP			
388JXCXCM-240A	3PDT	240 VAC,50/60Hz	7200 Ω
388JXCXCM-120A	3PDT	120 VAC,50/60Hz	1700 Ω
DC OPERATED PLUG-IN WITH PUSH BUTTON, 16 AMP			
388JXCXCM-12D	3PDT	12 VDC	120 Ω
388JXCXCM-24D	3PDT	24 VDC	470 Ω
AC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 20 AMP			
388JXBXC1M-240A	DPDT	240 VAC,50/60Hz	9100 Ω
388JXBXC1M-120A	DPDT	120 VAC,50/60Hz	2250 Ω
DC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 20 AMP			
388JXBXC1M-12D	DPDT	12 VDC	120 Ω
388JXBXC1M-24D	DPDT	24 VDC	470 Ω
AC OPERATED PLUG-IN WITH PUSH BUTTON, 20 AMP			
388JXBXCM-240A	DPDT	240 VAC,50/60Hz	9100 Ω
388JXBXCM-120A	DPDT	120 VAC,50/60Hz	2250 Ω
DC OPERATED PLUG-IN WITH PUSH BUTTON, 20 AMP			
388JXBXCM-12D	DPDT	12 VDC	120 Ω
388JXBXCM-24D	DPDT	24 VDC	470 Ω

RETROFITS SCHRACK RM. SEE END OF SECTION 1 FOR CROSS REFERENCE
CADMIUM-FREE CONTACTS AVAILABLE, CONTACT FACTORY FOR DETAILS

* Note: Code C recommended to be used with printed circuit terminals or Plug-in applications only.
† 0.187 Quick connect or Solder terminals are socket Compatible.

UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
1 POLE THRU 3 POLES	15 AMP	120/240 VAC	50/60 Hz	RESISTIVE
	15 AMP	28 VDC	DC	RESISTIVE
	1/3 HP	120 VAC	50/60 Hz	MOTOR
	1/2 HP	240 VAC	50/60 Hz	MOTOR

BENEFITS OF 3mm CONTACT GAP DESIGN:

1. HIGH DIELECTRIC STRENGTH ACROSS CONTACTS.
2. IMPROVED ARC QUENCHING WHEN BREAKING HIGH CURRENT LOADS.
3. MEETS EUROPEAN SPACING REQUIREMENTS OF 8mm ACROSS SURFACES

DPST-NO, 3PST-NO, 15 AMPS

UL Recognized
File No. E43641



LISTED 367G
IND. CONT. EQ.

C US

WHEN USED WITH
SOCKET 70-463-1

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND 947-5-1 LOW VOLTAGE DIRECTIVE

* IEC = INTERNATIONAL ELECTROTECHNICAL COMMISSION

* CE TESTING AND EVALUATION PERFORMED BY THE UNDERWRITERS LABORATORIES AS A THIRD PARTY PARTICIPANT

**MANUFACTURED UNDER
ISO 9002 & QS 9000**

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage:	80% of nominal voltage or less for DC coils 85% of nominal voltage or less for AC coils
Dropout Voltage:	10% of nominal voltage or more
Resistance:	±10% measured at 25°C
Coil Power:	1.2 watts for DC coils, 2 VA to 2.75 VA for AC @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446)
Maximum Coil Dissipation:	3.0 watts max. DC
Duty:	Continuous

CONTACTS

Contact material:	Silver alloy, gold flashed
Contact Resistance:	50 milliohms maximum initial resistance at rated current
Contact Ratings:	See "UL CONTACT LOAD RATINGS TABLE"

DIELECTRIC STRENGTH

Contacts to Coil:	3 mm gap, 4000 V rms
Across Open Contacts:	3 mm gap, 1000 V rms
Pole to Pole:	2000 V rms
Contacts to Frame:	2000 V rms
Insulation Resistance:	1000 megohms @ 500 VDC

TEMPERATURE

Operating:	-30°C to +50°C. (AC), -30°C to +65°C. (DC)
Storage:	-30°C to +100°C

LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Insulation material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Terminals:	0.187 x 0.032 quick connect flange or 0.187 x 0.020 solder/plug-in. Optional printed circuit terminals available
Weight:	88 grams approx.

**PLUG-IN****OPTIONAL FLANGE MOUNT COVER****OPTIONAL DIN MOUNT COVER****Mating Sockets**


70-463-1: SCREW/DIN

70-124-1: SOLDER

70-178-1, 70-178-2: PRINTED CIRCUIT




70-124-2: QUICK CONNECT

See section 8, page 16, 17



DPST-NO, 3PST-NO, 15 AMPS**OUTLINE DIMENSIONS**

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

PLUG-IN**QUICK CONNECT SOLDER /
PLUG-IN TERMINALS****FLANGE COVER****ORDERING CODE FOR RELAYS**

CLASS: **388V CXX C1 M 24A**

CONTACT CONFIGURATION:

BXX - (DPST-NO) 3 MM CONTACT GAP,
CXX - (3PST-NO) 3 MM CONTACT GAP,

CONSTRUCTION STYLE:

* ENCLOSED, PLAIN COVER: **CODE C**
ENCLOSED, FLANGE COVER: **CODE C1**
ENCLOSED, 6-32 TAPPED CORE &
ANTI-ROTATION TAB: **CODE C2**
ENCLOSED 6-32 STUD
& ANTI-ROTATION TAB: **CODE CS2**
ENCLOSED TOP FLANGE MOUNT: **CODE C3**
ENCLOSED DIN MOUNT: **CODE C4**

TERMINAL STYLE:

† QUICK CONNECT SOLDER/PLUG-IN
TERMINALS: **NO CODE**
PRINTED CIRCUIT TERMINALS: **CODE T**

OPTIONS:

BI - POLAR L.E.D. STATUS LAMP: **CODE L**
PUSH BUTTON: **CODE M**
MAGNETIC BLOWOUT: **CODE 69**
DC COIL SUPPRESSION: **CODE V**
AC COIL SUPPRESSION: **CODE V1**
RECTIFIED COIL: **CODE V2**

COIL VOLTAGE:

6, 12, 24, 120, 240 **ADD "A" FOR AC COILS**
6, 12, 24, 48, 110 **ADD "D" FOR DC COILS**



* Note: Code C recommended to be used with printed circuit terminals or Plug-in applications only.

† 0.187 Quick connect or solder terminals are socket compatible.

**3 MILLIMETER
CONTACT GAP.
PUSH BUTTON
STANDARD.**

WIRING DIAGRAMS

(VIEWED FROM PIN END)



		COIL MEASURED @ 25°C	
STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED PLUG-IN WITH PUSH BUTTON 3mm GAP, 15 AMP			
388VCXXCM-220/240A	3PST-NO	220/240 VAC,50/60Hz	9100 Ω
388VCXXCM-120A	3PST-NO	120 VAC,50/60Hz	1100 Ω
388VCXXCM-24A	3PST-NO	24 VAC,50/60Hz	75 Ω
388VBXXCM-220/240A	DPST-NO	220/240 VAC,50/60Hz	9100 Ω
388VBXXCM-120A	DPST-NO	120 VAC,50/60Hz	1100 Ω
388VBXXCM-24A	DPST-NO	24 VAC,50/60 Hz	75 Ω
DC OPERATED PLUG-IN WITH PUSH BUTTON 3mm GAP, 15 AMP			
388VCXXCM-24D	3PST-NO	24 VDC	240 Ω
388VCXXCM-12D	3PST-NO	12 VDC	120 Ω
388VBXXCM-24D	DPST-NO	24 VDC	240 Ω
388VBXXCM-12D	DPST-NO	12 VDC	120 Ω

RETROFITS POTTER & BRUMFIELD KUGP.
SEE END OF SECTION 1 FOR CROSS REFERENCE

DIELECTRIC STRENGTH CHART (V rms)

	SPDT	DPDT	3PDT	SPDT-DM,DB,DM-DB
COIL TO FRAME	1600	1600	1600	1600
ACROSS OPEN CONTACTS	1000	1000	1000	1500
CONTACT TO FRAME	1600	1600	1600	1600
COIL TO CONTACTS	2200	2200	1600	2200
POLE TO POLE	-	2200	1600	-
CONTACTS TO METAL MOUNTING PLATE (COVER INSTALLED)	2200	2200	1600	2200
COIL TO METAL MOUNTING PLATE (COVER INSTALLED)	2200	2200	2200	2200

20, 25 & 30 AMPS

UL **us**
UL Recognized
File No. E 43641

SP 168986



COMPLIES WITH REQUIREMENTS OF

* IEC STANDARDS 947-4-1 AND 947-5-1 LOW VOLTAGE DIRECTIVE

* IEC = INTERNATIONAL ELECTROTECHNICAL COMMISSION

* CE TESTING AND EVALUATION PERFORMED BY THE UNDERWRITERS LABORATORIES AS A THIRD PARTY PARTICIPANT

MANUFACTURED UNDER
ISO 9002 & QS 9000

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage:	80% of nominal voltage or less for DC coils 85% of nominal voltage or less for AC coils
Dropout Voltage:	10% of nominal voltage or more
Resistance:	±10% measured @ 25°C
Coil Power:	1.44 watts for DC coils, 2 VA to 3.5 VA for AC coils
Insulation System:	Class "B" Coil system. (130°C per UL standard 1446)
Max. Coil Dissipation:	2.5 watts max. DC
Duty:	Continuous

CONTACTS

Contact Material:	0.250 silver alloy, gold flashed
Contact Rating:	See next page
Contact Resistance:	50 milliohms maximum initial resistance at rated current

TIMING

Operate Time:	20 mS max. @ nominal voltage
Release Time:	20 mS max. @ nominal voltage

DIELECTRIC STRENGTH

Dielectric Strength	See "DIELECTRIC STRENGTH CHART"
Insulation Resistance:	1,000 megohms min. @ 500 VDC

TEMPERATURE


Operating:	-30°C to +50°C. (AC), -30°C to +65°C. (DC)
Storage:	-30°C to +100°C

LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS


Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Polycarbonate dust cover
Terminals:	0.250 x 0.032 quick connect/solder terminals Optional printed circuit terminals. (0.090 x 0.032) available
Weight:	94 grams approx with cover



**STANDARD SIDE
FLANGE COVER**



**OPTIONAL PRINTED
CIRCUIT TERMINAL
CONSULT FACTORY.**



**OPTIONAL TOP FLANGE COVER
CONSULT FACTORY.**



**OPTIONAL DIN COVER
CONSULT FACTORY.**



CLASS 389 LOAD RATINGS

POLES	ENCLOSED STYLE 1, 2 AND 3 POLE			
	CURRENT OR HORSEPOWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
1 POLE	13A	28	DC	RESISTIVE
	20A	15	DC	RESISTIVE
	25A	300	50/60 Hz	RESISTIVE
	5A	600	50/60 Hz	RESISTIVE
	20A	277	50/60 Hz	BALLAST
	1HP	120	50/60 Hz	MOTOR
	1-1/2HP	208/240	50/60 Hz	MOTOR
	1HP	480/600	50/60 Hz	MOTOR
	660VA	120	50/60 Hz	PILOT DUTY
	915VA	208	50/60 Hz	PILOT DUTY
	960VA	240	50/60 Hz	PILOT DUTY
	765VA	480/600	50/60Hz	PILOT DUTY
	•B600		50/60Hz	PILOT DUTY
2 POLES	13A	28	DC	RESISTIVE
	20A	15	DC	RESISTIVE
	25A	300	50/60 Hz	RESISTIVE
	5A	600	50/60 Hz	RESISTIVE
	20A	277	50/60 Hz	BALLAST
	1HP	120	50/60 Hz	MOTOR
	1-1/2HP	208/240	50/60 Hz	MOTOR
	1HP	480/600	50/60 Hz	MOTOR
	660VA	120	50/60 Hz	PILOT DUTY
	915VA	208	50/60 Hz	PILOT DUTY
	960VA	240	50/60 Hz	PILOT DUTY
	765VA	460/600	50/60Hz	PILOT DUTY
	B600		50/60Hz	PILOT DUTY
3 POLES	13A	28	DC	RESISTIVE
	15A	28	DC (NO)	RESISTIVE
	20A	15	DC	RESISTIVE
	20A	150	50/60 Hz	RESISTIVE
	††15A	250	50/60 Hz	RESISTIVE
	†10A	300	50/60 Hz	RESISTIVE
	20A	150	50/60 Hz	BALLAST
	6-2/3HP	277	50/60 Hz	BALLAST
	1/2HP	120	50/60Hz	MOTOR
	1/2HP	208/240	50/60 Hz	MOTOR
	1HP	240	50/60 Hz	MOTOR
	3/4HP	120	50/60Hz	MOTOR
	470VA	120/240	50/60Hz	PILOT DUTY
	445VA	208	50/60Hz	PILOT DUTY
	B300		50/60Hz	PILOT DUTY

CLASS 389D LOAD RATINGS

POLE	ENCLOSED STYLE 1, 2 AND 3 POLE			
	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
1 POLE	30A	28	DC	RESISTIVE
	30A	300	50/60 Hz	RESISTIVE
	10A	600	50/60 Hz	RESISTIVE
	1HP	120	50/60 Hz	MOTOR
	1-1/2HP	200 thru 600	50/60 Hz	MOTOR
	765VA	120	50/60 Hz	PILOT DUTY
	915VA	208	50/60 Hz	PILOT DUTY
	960VA	240,480,600	50/60 Hz	PILOT DUTY
	A600		50/60 Hz	PILOT DUTY

CLASS 389 BALLAST LOAD RATINGS

POLES	ENCLOSED STYLE			
SPDT	20 AMP	277 VAC	50/60Hz	
DPDT	20 AMP	277 VAC	50/60Hz	
3PDT	20 AMP	150 VAC	50/60Hz	
	6 2/3 AMP	277 VAC	50/60Hz	
DOUBLE BREAK DOUBLE MAKE (1 FORM "X" & "Z")				
SPDT	25 AMP	277 VAC	50/60Hz	



†† UL APPLIANCE RATED. ALL OTHER RATINGS NOT SO MARKED ARE INDUSTRIAL RATED
 † CSA RATING ONLY, NOT UL

**1, 2 & 3 POLE NEMA PILOT DUTY CONTACT RATINGS**

NEMA CONTACT CODE DESIGNATION	THERMAL CONTINUOUS TEST CURRENT AMPERES	MAXIMUM CURRENT, AMPERES									
		120 VOLTS 50/60Hz		240 VOLTS 50/60Hz		480 VOLTS 50/60Hz		600 VOLTS 50/60Hz		MAXIMUM VOLT-AMPERES	
		MAKE	BREAK	MAKE	BREAK	MAKE	BREAK	MAKE	BREAK	MAKE	BREAK
A600	10	60	6.00	30	3.00	15	1.50	12	1.20	7200	720
B300	5	30	3.00	15	1.50					3600	360
B600	5	30	3.00	15	1.50	0.75	0.75	0.6	0.6	3600	360

DPDT, 3PDT, 20 & 25 AMPS**NEW**
From The Market
Leader in Industrial
Relays**OUTLINE DIMENSIONS**

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**ORDERING CODE FOR RELAYS**

389F XCX C1 M - 120A

CLASS: _____
FLAG INDICATOR STANDARD FEATURE

CONTACT CONFIGURATION: _____
DPDT: XBX, 3PDT: XCX

CONSTRUCTION STYLE: _____

- * ENCLOSED, PLAIN COVER: **CODE C**
- ENCLOSED, FLANGE COVER: **CODE C1**
- ENCLOSED, 6-32 TAPPED CORE & ANTI-ROTATION TAB: **CODE C2**
- ENCLOSED 6-32 STUD & ANTI-ROTATION TAB: **CODE CS2**
- ENCLOSED TOP FLANGE MOUNT: **CODE C3**
- ENCLOSED DIN MOUNT: **CODE C4**

TERMINAL STYLE: _____

- 0.250 QUICK CONNECT SOLDER TERMINALS: **NO CODE**
- PRINTED CIRCUIT TERMINALS: **CODE T**

OPTIONS: _____


- BI - POLAR L.E.D. STATUS LAMP: **CODE L**
- PUSH BUTTON: **CODE M**
- MAGNETIC BLOWOUT: **CODE 69**
- DC COIL SUPPRESSION: **CODE V**
- AC COIL SUPPRESSION: **CODE V1**
- RECTIFIED COIL: **CODE V2**

COIL VOLTAGE: _____

6, 12, 24, 120, 240 **ADD "A" FOR AC COILS**
6, 12, 24, 48, 110 / 125, 220 / 250 **ADD "D" FOR DC COILS**

* Note: Code C recommended to be used with printed circuit terminals only.

**FLAG INDICATOR
& PUSH BUTTON
STANDARD ON
389F RELAYS.**


WIRING DIAGRAMS
(VIEWED FROM PIN END)

STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 20 AMP			
389FXCXC1M-240A	3PDT	240 VAC, 50/60Hz	4600 Ω
389FXCXC1M-120A	3PDT	120 VAC, 50/60Hz	1200 Ω
AC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 25 AMP			
389FXBXC1M-240A	DPDT	240 VAC, 50/60Hz	7200 Ω
389FXBXC1M-120A	DPDT	120 VAC, 50/60Hz	1700 Ω
DC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 20 AMP			
389FXCXC1M-12D	3PDT	12 VDC	100 Ω
389FXCXC1M-24D	3PDT	24 VDC	400 Ω
DC OPERATED FLANGE MOUNT WITH PUSH BUTTON, 25 AMP			
389FXBXC1M-12D	DPDT	12 VDC	100 Ω
389FXBXC1M-24D	DPDT	24 VDC	400 Ω


RETROFITS SCHRACK RM.
SEE END OF SECTION 1 FOR CROSS REFERENCE

20, 25 & 30 AMPS**OUTLINE DIMENSIONS**

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**WIRING DIAGRAMS**

(VIEWED FROM PIN END)

**COIL MEASURED @ 25°C**

STANDARD PART NUMBERS	CONTACT CONFIGURATION	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED FLANGE MOUNT, 30 AMP			
W389ADCX-4	SPST-NO (DM)	120 VAC, 50/60Hz	1100 Ω
W389ADCX-5	SPST-NO (DM)	220/240 VAC, 50/60Hz	4300 Ω
W389ADZCX-3	SPDT-NO-NC (DM-DB)	24 VAC, 50/60Hz	44 Ω
W389ADZCX-4	SPDT-NO-NC (DM-DB)	120 VAC, 50/60Hz	1100 Ω
DC OPERATED FLANGE MOUNT, 30 AMP			
W389DCX-2	SPST-NO (DM)	12 VDC	100 Ω
W389DCX-3	SPST-NO (DM)	24 VDC	400 Ω
W389DZCX-2	SPST-NO-NC (DM-DB)	12 VDC	100 Ω
W389DZCX-3	SPST-NO-NC (DM-DB)	24VDC	400 Ω
AC OPERATED FLANGE MOUNT, 25 AMP			
W389ACX-4	SPDT	120 VAC, 50/60Hz	1700 Ω
W389ACX-8	DPDT	24 VAC, 50/60Hz	72 Ω
W389ACX-9	DPDT	120 VAC, 50/60Hz	1700 Ω
W389ACX-10	DPDT	220/240 VAC, 50/60Hz	7200 Ω
AC OPERATED FLANGE MOUNT, 20 AMP			
W389ACX-14	3PDT	120 VAC, 50/60Hz	1200 Ω
W389ACX-15	3PDT	220/240 VAC, 50/60Hz	4600 Ω
DC OPERATED FLANGE MOUNT, 25 AMP			
W389CX-2	SPDT	12 VDC	100 Ω
W389CX-3	SPDT	24VDC	400 Ω
W389CX-7	DPDT	12 VDC	100 Ω
W389CX-8	DPDT	24VDC	400 Ω
DC OPERATED FLANGE MOUNT, 20 AMP			
W389CX-12	3PDT	12 VDC	100 Ω
W389CX-13	3PDT	24VDC	400 Ω

RETROFITS POTTER & BRUMFIELD KUMP & KUHP.
SEE END OF SECTION 1 FOR CROSS REFERENCE

FEATURES

OPTIONAL BLOWOUT MAGNET
WIDE SPACING BETWEEN
STATIONARY CONTACT TERMINALS

ARC BARRIERS BETWEEN
CONTACTS

2 MILLIMETER CONTACT GAPS

IMPROVED DIELECTRIC
STRENGTH BETWEEN CONTACT

WIDE SELECTION OF
MOUNTING OPTIONS

HIGH VOLTAGE DC SWITCHING

CLEARANCE FOR FULLY BOOTED QUICK CONNECT
TERMINALS

IMPROVED DIELECTRIC STRENGTH BETWEEN
CONTACT SETS.

8 MILLIMETER CREEPAGE AND CLEARANCE TO
MEET INTERNATIONAL REQUIREMENTS.

4000 Vrms DIELECTRIC BETWEEN MUTUALLY
INSULATED CONDUCTIVE ELEMENTS AND FRAME.

ALLOWS INSTALLATIONS TO BE "CUSTOMIZED"

• **BENEFITS** •

**DPDT, UP TO 30 AMPS
UP TO 600 VAC OR 150 VDC**



UL Recognized
File No. E13224



50758

**MANUFACTURED UNDER
ISO 9002 & QS 9000**

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage:	85% of nominal voltage or less for AC coils, 80% of nominal voltage or less for DC coils
Dropout Voltage:	10% min. of nominal voltage or more
Max. Voltage:	110%
Resistance:	±10% measured @ 25°C
Coil Power:	2.0 watts DC, 3.0 VA (60Hz) AC. @ 25°C
Insulation System:	Class "B" (130°C per UL standard 1446), Class "F" (155°C available)
Max. Coil Dissipation:	3.0 watts DC., 3.4 VA (60Hz) AC
Duty:	Continuous

CONTACTS

Contact Material:	Silver alloy, gold flashed
Contact Rating:	30 amps @ 120/240/277 VAC. 20 amps @ 480 VAC (general purpose) 15 amps @ 600 VAC (resistive load). 30 amps @ 28 VDC (resistive load). 1Hp @ 120 VAC 50/60 Hz. 2 Hp @ 208, 240, 480, 600 VAC. 50/60 Hz (motor load). Code 69 - DPDT: 5 amps @ 150 VDC; SPDT-DM-DB: 10 amps @ 150 VDC; 20 amps @ 72 VDC; DPTS-NO: 3 amps @ 220 VDC

TIMING

Operate Time:	20 mS max. @ nominal voltage
Release Time:	15 mS max. @ nominal voltage

DIELECTRIC STRENGTH

Contacts to Coil:	4000 V rms; (8mm creepage)
Coil to Frame:	4000 V rms
Across Open Contacts:	1000 V rms
Contact To Frame:	4000 V rms

TEMPERATURE

Operation:	-30°C to +50°C. (AC), -30°C to +60°C. (DC)
Storage:	-40°C to +105°C

LIFE EXPECTANCY


Electrical:	100,000 operations @ rated resistive load
Mechanical:	10,000,000 operations @ no load

MISCELLANEOUS

Operating Position:	Any
Enclosure:	Polycarbonate dust cover
Weight:	85 grams approx.



**STANDARD SIDE
FLANGE COVER**



**OPTIONAL TOP FLANGE
MOUNT COVER**



OPTIONAL DIN MOUNT COVER




NEW
From The Market
Leader in Industrial
Relays


**DPDT, UP TO 30 AMPS
UP TO 600 VAC OR 150 VDC**

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**QUICK CONNECT
SOLDER TERMINALS**




**PRINTED CIRCUIT
MOUNTING HOLE LAYOUT
(BOTTOM VIEW)**





**PRINTED CIRCUIT
TERMINALS**

OPTIONAL PUSH BUTTON



ENCLOSED FLANGE MOUNT



ORDERING CODE FOR RELAYS

TEMPERATURE RATING: ☐ F 300 XBX C1 LM -24D
 †† 130°C COIL: CODE B
 155°C COIL: CODE F

CLASS: _____

CONTACT CONFIGURATION: _____
 DPDT: XBX

CONSTRUCTION STYLE: _____
 * ENCLOSED, PLAIN COVER: CODE C
 ENCLOSED, FLANGE COVER: CODE C1
 ENCLOSED, 6-32 TAPPED CORE &
 ANTI-ROTATION TAB: CODE C2
 ENCLOSED 6-32 STUD & ANTI-ROTATION TAB: CODE CS2
 ENCLOSED TOP FLANGE MOUNT: CODE C3
 ENCLOSED DIN MOUNT: CODE C4

TERMINAL STYLE: _____
 † QUICK CONNECT SOLDER TERMINALS: NO CODE
 PRINTED CIRCUIT TERMINALS: CODE T


OPTIONS: _____
 BI - POLAR L.E.D. STATUS LAMP: CODE L
 PUSH BUTTON: CODE M
 MAGNETIC BLOWOUT: CODE 69
 DC COIL SUPPRESSION: CODE V
 AC COIL SUPPRESSION: CODE V1
 RECTIFIED COIL: CODE V2

COIL VOLTAGE: _____
 6, 12, 24, 120, 240 ADD "A" FOR AC COILS
 6, 12, 24, 48, 110-125, 220-250 ADD "D" FOR DC COILS

* Note: Code C recommended to be used with printed circuit terminals only.
 †† Standard coil temperature Rating. Code letter not required in part number.
 Add code letter required in part number when a higher nonstandard coil temperature rating is required.

**OPTIONAL 6-32
STUD OR TAPPED
CORE WITH
ANTI-ROTATION TAB.**

WIRING DIAGRAM
(VIEWED FROM PIN END)



STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED, 30 AMP			
300XBTC1-240A	DPDT	240 VAC, 50/60Hz	7200 Ω
300XBTC1-120A	DPDT	120 VAC, 50/60Hz	1700 Ω
300XBTC1-24A	DPDT	24 VAC, 50/60Hz	72 Ω
300XBTC1-12A	DPDT	12 VAC, 50/60Hz	18 Ω
DC OPERATED, 30 AMP			
300XBTC1-110D	DPDT	110 VDC	10,000 Ω
300XBTC1-24D	DPDT	24 VDC	470 Ω
300XBTC1-12D	DPDT	12 VDC	51 Ω
DC OPERATED, 30 AMP WITH MAGNETIC BLOWOUT			
300XB69C1-125D	DPDT	110 VDC	10,000 Ω
300XB69C1-24D	DPDT	24 VDC	470 Ω
300XB69C1-12D	DPDT	12 VDC	51 Ω

UL CONTACT LOAD RATINGS TABLE

LOAD	LOAD VOLTAGE	SPST	SPDT		OPERATIONS
		N.O. LOAD	N.O. LOAD	N.C. LOAD	
GENERAL PURPOSE	240 VAC	30 AMP	30 AMP	15 AMP	100,000
RESISTIVE	28 VDC	30 AMP	30 AMP	10 AMP	100,000
MOTOR	125 VAC	1 HP	1 HP	1/4 HP	1,000
	240 VAC	2 HP	2 HP	1/2 HP	6,000
FLA/LRA ‡	120 VAC	22/98 AMP	22/98 AMP	-	100,000
	240 VAC	30/80 AMP	30/80 AMP	12/30 AMP	30,000
TUNGSTEN	240 VAC	TV - 5	TV - 5	-	25,000
BALLAST	277 VAC	10 AMP	10 AMP	3 AMP	6,000
PILOT DUTY	240 VAC	470 VA	470 VA	275 VA	6,000

‡ FLA = Full load amps, LRA = Locked rotor amps.

SPST-N.O. & SPDT, 30 AMPS

cULus
UL Recognized
File No. E43641

CLASS "F" INSULATION 155 °C.
FLANGE MOUNTED. EPOXY SEALED
WITH REMOVABLE TAPE SEAL OVER
VENT HOLE (REMOVED AFTER CLEANING)

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage: 80% of nominal voltage or less for AC coils,
75% of nominal voltage or less for DC coils
Dropout Voltage: 10% of nominal voltage or more
Max. Coil Voltage: 120% max.
Power Consumption: 2.8 watts max.
Insulation System: Class "F" (155°C)
Coil Resistance: ±10% measured @ 25°C
Duty: Continuous

CONTACT

Contact Material: Silver alloy
Switching Voltage: 277 VAC, 28 VDC max.
Contact Resistance: 75 milliohms @ 1 amp rated current
Minimum Load: 1 amp, 5 VDC, 12 VAC

TIMING

Operate Time: DC: 15 mS typ. Including bounce
Release Time: DC: 15 mS typ. Including bounce

DIELECTRIC STRENGTH

Contacts to Coil: 2500 V rms
Between Open Contacts: 1500 V rms
Insulation Resistance: 1000 mΩ min. @ 500 VDC, 25°C 50% RH

TEMPERATURE

Operating: -55°C to +85°C
Storage: -55°C to +155°C

VIBRATION RESISTANCE

Functional: 10 to 55Hz 1.65 mm max.
No contact opening > 100 uS

SHOCK RESISTANCE

Functional: 10 g's for 11 mS, no contact opening > 100 μS
Mechanical: 100 g's


LIFE EXPECTANCY

Electrical: 100,000 operations @ rated resistive load
Mechanical: 10,000,000 operations @ no load

MISCELLANEOUS


Operating Position: Any
Enclosure: Epoxy sealed immersion cleanable suitable for automatic circuit board processing, max. Exposure soldering temperature is 4 sec. @ 500°F
94V-O flammability rating
Enclosure: 0.25" quick connect & safety wells accept insulated female quick connect terminals
Terminals: 33 grams approx.
Weight:

MEETS UL 508,
UL 873 AND
UL 1950 - 1/8"
THRU AIR - 1/4"
OVER SURFACE


STANDARD FLANGE COVER**OPTIONAL DIN ADAPTER 16-9A DIN-1**

OUTLINE DIMENSIONS


DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



A1 = 0.250 X 0.032 (6.35 X 0.81) Quick Connect Terminal
B1 = 0.187 x 0.020 (4.78 x 0.508) Quick Connect Terminal



WIRING DIAGRAM (BOTTOM VIEW)



STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25 °C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
FLANGE MOUNT, 30 AMP			
W9AS1D52-5	SPST-NO	5 VDC	25 Ω
W9AS1D52-12	SPST-NO	12 VDC	144 Ω
W9AS1D52-24	SPST-NO	24 VDC	576 Ω
W9AS1D52-110	SPST-NO	110 VDC	12100 Ω
FLANGE MOUNT, 20 AMP			
W9AS5D52-5	SPDT	5 VDC	25 Ω
W9AS5D52-12	SPDT	12 VDC	144 Ω
W9AS5D52-24	SPDT	24 VDC	576 Ω
W9AS5D52-110	SPDT	110 VDC	12100 Ω
FLANGE MOUNT, 30 AMP			
W9AS1A52-24	SPST-NO	24 VAC	
W9AS1A52-120	SPST-NO	120 VAC	
W9AS1A52-240	SPST-NO	240 VAC	
FLANGE MOUNT, 20 AMP			
W9AS5A52-24	SPDT	24 VAC	
W9AS5A52-120	SPDT	120 VAC	
W9AS5A52-240	SPDT	240 VAC	

UL CONTACT LOAD RATINGS TABLE

RATING	LOAD VOLTAGE	DPST-N.O. & DPDT	DPDT	OPERATIONS
		N.O. LOAD	N.C. LOAD	
RESISTIVE LOAD	120/277 VAC	30 AMP	3 A MP	6,000
	28 VDC	20 AMP	3 A MP	100,000
MOTOR	120 VAC	1 HP	-	1000
	240 VAC	3 HP	-	1000
TUNGSTEN	120 VAC	TV-10	-	25,000
LRA/FLA†	240 VAC	96/22	-	30,000
		110/25.3	-	
PILOT DUTY	240 VAC	3 AMP	-	6,000

DPST-N.O. & DPDT 30 AMPS

cULus
UL Recognized
File No. E43641

Note:

† FLA = full load amps, LRA = Locked rotor amps.

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage: 80% of nominal voltage or less for AC coils,
75% of nominal voltage or less for DC coils

Dropout Voltage: 10% of nominal voltage or more

Max. Operating Frequency: 14 operations per minute

Nominal Power: AC coil: 4.0 VA, DC coil: 1.7W

Insulation System: Class "F" (155°C)

Coil Resistance: ±10% measured @ 25°C

Duty: Continuous

CONTACT

Contact Material: Silver alloy

Contact Load Ratings: See: "UL CONTACT LOAD RATINGS TABLE"

Contact Resistance: 100, 000, 000 @ initial rated current (switched)

Minimum Load: N.O. 500 mA @ 12 VAC/VDC
N.C. 100 mA @ 6 VAC/VDC

TIMING

Operate Time: DC: 15 mS typ. 25ms W/ Bounce

Release Time: DC: 10 mS typ. 25 ms W/ Bounce

DIELECTRIC STRENGTH

Between Open Contacts: 1500 V rms

Contacts to Coil: 4000V rms

Insulation Resistance: 10³ meg Ω min. @ 500 VDC, 25°C 50% RH

TEMPERATURE

Operating: AC coil rectified: -40°C to +85°C, DC: -40°C to +85°C

Storage: -55°C to +155°C

VIBRATION RESISTANCE

Functional: 0.065 (1.65 mm) double
Amplitude -10 thru 55 Hz

SHOCK RESISTANCE

Functional: 10 g's for 11 mS, 1/2 sign wave pulse with no contact opening > 100µs

Mechanical: 100 g's for 11 mS, 1/2 sine wave pulse

LIFE EXPECTANCY

Electrical: 100,000 operations @ rated resistive load

Mechanical: 5,000,000 operations @ no load

MISCELLANEOUS


Operating Position: Any

Enclosure: Epoxy sealed immersion cleanable tape sealed plastic cover


Flammability: 94V-O flammability rating

Weight: 86 grams approx.

CLASS "F" INSULATION 155 °C.
EPOXY SEALED WITH REMOVABLE
TAPE SEAL OVER VENT HOLE
(REMOVED AFTER CLEANING)



OPTIONAL DIN ADAPTER
16-92 DIN-1




MEETS UL 873
AND UL 508
SPACING - (8MM)
THRU AIR, (9.5 MM)
OVER SURFACE



DPST-N.O. & DPDT 30 AMPS


OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).




WIRING DIAGRAM

(VIEWED FROM PIN END)



DPST-N.O.



DPDT

STANDARD PART NUMBERS	COIL MEASURED @ 25°C		
	CONTACT CONFIGU- RATION	NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED COIL FLANGE MOUNT, 30 AMP			
W92S7A22-24	DPST-NO	24 VAC	-
W92S7A22-120	DPST-NO	120 VAC	-
W92S7A22-240	DPST-NO	240 VAC	-
W92S11A22-24	DPDT	24 VAC	-
W92S11A22-120	DPDT	120 VAC	-
W92S11A22-240	DPDT	240 VAC	-
DC OPERATED COIL FLANGE MOUNT, 30 AMP			
W92S7D22-12	DPST-NO	12 VDC	86 Ω
W92S7D22-24	DPST-NO	24 VDC	350 Ω
W92S7D22-110	DPST-NO	110 VDC	7,255 Ω
W92S11D22-12	DPDT	12 VDC	86 Ω
W92S11D22-24	DPDT	24 VDC	350 Ω
W92S11D22-110	DPDT	110 VDC	7,255 Ω

UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD	MINIMUM LOAD
1 POLE THRU 6 POLES	5 AMP	120 VAC	50/60 Hz	RESISTIVE	
	5 AMP	28 VDC	DC	RESISTIVE	50 mA, 6 VDC
	3 AMP	120 VAC	50/60 Hz	RESISTIVE	
	3 AMP	28 VDC	DC	RESISTIVE	10 mA, 6 VDC

**DPDT THRU 6PDT,
3 & 5 AMPS**

cUL us
UL Recognized
File No. E52197

168986

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage : 80% of nominal voltage or less
 Dropout Voltage: DC-10% of nominal voltage or more
 Max. Voltage : 110%
 Resistance: $\pm 10\%$ measured @ 25°C
 Coil Power: 0.5 to 1.5 watts DC, 1.5 VA to 2 VA (60 Hz) AC @ 25°C.
 Max. Coil Dissipation: 2.2 watts @ 25°C.
 Duty: Continuous

CONTACTS

Contact Material: Silver gold overlay
 Coil Resistance: 50 megohms max.
 Contact Rating: See "UL CONTACT LOAD RATING TABLE"

CAPACITANCE

Between Contacts: 2 pf, typ.
 Contacts to Coil: 2 pf, typ.
 Contacts to Frame: 30 pf, typ.

TIMING

Operate Time: DPDT=12 mS, 4PDT=14 mS, 6PDT=16 mS,
 Release Time: 8 mS

DIELECTRIC STRENGTH

Contacts to Coil: 1500 V rms
 Coil to Frame: 1000 V rms
 Across Open Contacts: 500 V rms
 Contacts to Frame: 1500 V rms
 Insulation Resistance: 1000 megohms @ 500 VDC

TEMPERATURE

Operating: -55°C to +70°C
 Storage: -55°C to +105°C



LIFE EXPECTANCY

Electrical: 200,000 operations @ rated resistive load
 Mechanical: 1,000,000 operations @ no load

MISCELLANEOUS

Operating Position: Any
 Insulation Material: Molded plastic
 Enclosure: Polycarbonate dust cover
 Weight: 22 to 40 grams approx.



Standard **Class 67** miniature industrial relays are designed for applications requiring DPDT to 6PDT contacts where space and weight are of prime importance. Shatter resistant, see-thru plastic covers are utilized to protect against dust, tampering and electrical shock. The 67T models have Bifurcated Contacts and are designed for low level switching applications.

**BIFURCATED CONTACTS
(LOW LEVEL APPLICATIONS)****STANDARD CONTACTS
(5 AMP CROSS BAR)****Mating Sockets**

70-303-1, 70-305-1, 70-307-1: SOLDER
70-304-1, 70-306-1, 70-308-1:
PRINTED CIRCUIT
 See section 8, page 23, 24



DPDT THRU 6PDT, 3 & 5 AMPS

OUTLINE DIMENSIONS
DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).WIRING DIAGRAM
(VIEWED FROM PIN END)

DIMENSIONS

CONTACT CONFIGURATION	"A" DIM
6PDT	1.374 (34.9)
4PDT	1.156 (29.4)
DPDT	0.978 (24.8)

STANDARD PART NUMBERS

CONTACT CONFIGURATION

COIL MEASURED @ 25°C

NOMINAL INPUT VOLTAGE OR

NOMINAL RESISTANCE (OHMS)

DC OPERATED COIL - SOLDER/PLUG-IN, 5 AMP

W67RCSX-1	DPDT	5 VDC	52 Ω
W67RCSX-2	DPDT	12 VDC	185 Ω
W67RCSX-3	DPDT	24 VDC	700 Ω
W67RCSX-4	DPDT	48 VDC	2,500 Ω
W67RCSX-5	DPDT	110 VDC	15,000 Ω
W67RCSX-6	4PDT	5 VDC	52 Ω
W67RCSX-7	4PDT	12 VDC	185 Ω
W67RCSX-8	4PDT	24 VDC	700 Ω
W67RCSX-9	4PDT	48 VDC	2,500 Ω
W67RCSX-10	4PDT	110 VDC	15,000 Ω
W67RCSX-12	6PDT	12 VDC	90 Ω
W67RCSX-13	6PDT	24 VDC	430 Ω

DC OPERATED COIL-BIFURCATED CONTACTS, 3 AMP

W67TRCSX-2	DPDT	12 VDC	185 Ω
W67TRCSX-3	DPDT	24 VDC	700 Ω
W67TRCSX-7	4PDT	12 VDC	185 Ω
W67TRCSX-8	4PDT	24 VDC	700 Ω
W67TRCSX-12	6PDT	12 VDC	90 Ω
W67TRCSX-13	6PDT	24 VDC	430 Ω

DC OPERATED PRINTED CIRCUIT, 5 AMP

W67RPCX-2	DPDT	12 VDC	185 Ω
W67RPCX-3	DPDT	24 VDC	700 Ω
W67RPCX-7	4PDT	12 VDC	185 Ω
W67RPCX-8	4PDT	24 VDC	700 Ω
W67RPCX-12	6PDT	12 VDC	90 Ω
W67RPCX-13	6PDT	24 VDC	430 Ω

AC OPERATED COIL - SOLDER/PLUG-IN, 5 AMP

W67ARCSX-5	DPDT	120 VAC, 50/60Hz	9000 Ω
W67ARCSX-10	4PDT	120 VAC, 50/60Hz	8000 Ω
W67ARCSX-15	6PDT	120 VAC, 50/60Hz	8000 Ω

DC OPERATED COIL ULTRA SENSITIVE - SOLDER/PLUG-IN, 3 AMP

W67SCSX-1	DPDT	9.4 MADC	1,000 Ω
W67SCSX-2	DPDT	6.4 MADC	2,500 Ω
W67SCSX-3	DPDT	4.5 MADC	5,000 Ω
W67SCSX-6	4PDT	13.7 MADC	1,000 Ω
W67SCSX-7	4PDT	9.1 MADC	2,500 Ω
W67SCSX-8	4PDT	6.5 MADC	5,000 Ω

RETROFITS POTTER & BRUMFIELD R10.
SEE END OF SECTION 1 FOR CROSS REFERENCE

UL CONTACT LOAD RATINGS TABLE

POLES	CURRENT OR HORSE POWER	LOAD VOLTAGE	LOAD VOLTAGE FREQUENCY	TYPE OF LOAD
ALL STYLES	10 AMP	120 VAC	50/60 Hz	RESISTIVE
	5 AMP	240 VAC	50/60 Hz	RESISTIVE
	10 AMP	28 VDC	DC	RESISTIVE
	0.5 AMP	125 VDC	DC	RESISTIVE
	3 AMP	120 VAC	50/60 Hz	INDUCTIVE
	1 AMP	240 VAC	50/60 Hz	INDUCTIVE
	3 AMP	28 VDC	DC	INDUCTIVE
	0.1 AMP	125 VDC	DC	INDUCTIVE
SUFFIX "69" WITH BLOWOUT MAGNET FOR DC SWITCHING (NOT UL OR CSA)				
SPST-NO	1.5 AMP	125 VDC	DC	RESISTIVE
SPST-NO-DM	4 AMP	125 VDC	DC	RESISTIVE
SPST-NO	0.5 AMP	250 VDC	DC	RESISTIVE
SPST-NO-DM	1.5 AMP	250 VDC	DC	RESISTIVE
SPST-NO	0.5 AMP	125 VDC	DC	INDUCTIVE
SPST-NO-DM	1.5 AMP	125 VDC	DC	INDUCTIVE
SPST-NO	150 mA	250 VDC	DC	INDUCTIVE
SPST-NO-DM	0.5 AMP	250 VDC	DC	INDUCTIVE

COIL SPECIFICATIONS @ 25°C

AC RELAYS 50/60 HZ (COIL DATA @ 60HZ VOLTAGE)					DC RELAYS, 1.8 WATTS (2.5 W @ 125 VDC)			
Nominal Voltage	Resistance Ohms ±10%	Milliamperes		Impedance Ohms	Nominal Voltage	Resistance Ohms ±10%	Milliamperes	
		Inrush (Open)	Sealed (Pull-in)				Cold	Hot
6	1.1	1500	840	7.2	6	15.5	385	304
12	4.2	750	410	27	12	63.5	189	147
24	15.5	375	200	120	24 (28)*	250	96	77
120	540	75	40	2700	32	375	86	62
240	2100	32	17	13,400	115/125*	6200	20	16

12 & 14 PIN, 10 AMPS

cULus
UL Recognized
File No. E13224

SP 168986

UL LISTED 225G
IND. CONT. EQ.
C US

WHEN USED WITH
SOCKETS
27390 OR 33377

CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS

**CONTACTS CAN
CLOSE ON 30 AMP
LOADS AND CARRY
10 AMPS
CONTINUOUSLY AT
VOLTAGES SHOWN
IN UL CONTACT LOAD
RATINGS TABLE.**

*** 24 VDC AND 115 VDC RELAYS HAVE NAME
PLATES STAMPED 24-28 AND 115-125 VDC
RESPECTIVELY. THESE RELAYS OPERATE AT
80% OF THE LOWER VOLTAGES AND OPERATE
WITHIN ALLOWABLE TEMPERATURE RISES AT
110% OF HIGHER VOLTAGES.
250 VDC: USE 125 VDC RELAY AND SERIES
RESISTOR (6000 Ω, 5 W) NOT SUPPLIED.**

GENERAL SPECIFICATIONS

COIL
Pull-in Voltage: 85% of nominal voltage or less for AC coils,
80% of nominal voltage or less for DC coils
Max. Voltage: 110%
Insulation System: Class "B" (130°C per UL standard 1446)

CONTACTS
Contact Material: Silver alloy, gold diffused


TIMING
Operate Time: 25 mS max. @ nominal voltage
Release Time: 20 mS max. @ nominal voltage

DIELECTRIC STRENGTH
All Mutually Insulated Points: 1500 V rms

TEMPERATURE
Operation: -40°C to +60°C
Storage: -40°C to +130°C

LIFE EXPECTANCY
Electrical: 100,000 operations @ rated resistive load
Mechanical: 10,000,000 operations @ no load

MISCELLANEOUS
Operating Position: Vertical, contacts up
Enclosure: Polycarbonate dust cover
Weight: 241 grams approx.











Mating Sockets
27390D, 33377D: SCREW/PANEL/DIN
See section 8, page 25



12 & 14 PIN, 10 AMPS**OUTLINE DIMENSIONS**

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).

**WIRING DIAGRAMS**
(VIEWED FROM PIN END)**219XBX**
DPDT**219BBXP**
DPDT+2 NO**219ABAP**
DPDT+1NO & 1NC**219FXXP**
6P-NO**219DXDP**
4PDT**219DXBP**
4P-NO+2P-NC**ORDERING CODE FOR RELAYS****219 XBX P L -24D****CLASS:****CONTACT CONFIGURATION:**

DPDT: **XBX**
 DPDT +1 POLE: NO & 1 POLE NC: **ABA**
 2 POLE: NO & DPDT: **BBX**
 4 PDT: **XXD**
 6 POLE: NO: **FXX**
 4 POLE: NO & 2 POLE: NC: **DXB**

STANDARD FEATURES:POLYCARBONATE COVER: **CODE P****OPTIONAL FEATURES:**

STATUS LAMP: **CODE L**
 MANUAL ACTUATOR: **CODE M**
 BIFURCATED CONTACTS: **CODE 33**
 PERM. MAGNET BLOWOUT: **CODE 69**

COIL VOLTAGE:

6, 12, 24, 120, 240 **ADD "A" FOR AC COILS**
 6, 12, (24-28), 32, 115/125 **ADD "D" FOR DC COILS**

COIL VOLTAGES & FREQUENCIES MUST BE SPECIFIED.

Make before break and other contact configurations available
 limited only by the number of terminal pins. Contact factory.

THE SERIES 219
GENERAL PURPOSE
INDUSTRIAL
PLUG-IN RELAYS
FEATURE 12 PIN
AND 14 PIN
BASES. THE COIL
IS ENCAPSULATED
FOR PROTECTION.
NUCLEAR
QUALIFIED
VERSIONS ARE
AVAILABLE.
CONSULT FACTORY.

12 PIN MODELS	CONTACT CONFIGU- RATION	14 PIN MODELS	CONTACT CONFIGU- RATION
219BBXP	DPDT + 2 NO	219DXDP	4PDT
219XBX	DPDT	219FXXP	6P-NO
219ABAP	DPDT + 1 NO & 1 NC	219DXBP	4P-NO + 2P-NC

FEATURES**VACUUM BAKED & DRY
NITROGEN FILLED****HERMETICALLY SEALED
METAL ENCLOSURE****PLUG-IN STYLE
MOUNTING****BENEFITS**REMOVES CONTAMINANTS AND PROVIDES A CLEAN & DRY
ATMOSPHERE FOR CONTACTS.IDEAL FOR USE IN HAZARDOUS LOCATIONS. UL CERTIFIED FOR
CLASS 1 DIVISION 2 GROUP A, B, C & D HAZARDS.WHEN USED WITH 70-464-1 OR 70-465-1 SOCKETS, THE 750H CAN BE
DIN RAIL MOUNTED OR PANEL MOUNTED.**DPDT, 12 AMPS
3PDT, 10 AMPS****cULus**
UL Recognized
File No. E43641**UL** LISTED 367G
IND. CONT. EQ.
C USWHEN USED WITH
SOCKETS
70-464-1 OR 70-465-1CURRENT LIMITED TO
RATING OF RELAY OR
SOCKET WHICHEVER
IS LESS**GENERAL SPECIFICATIONS****COIL**

Pull-in Voltage:	85% of nominal voltage or less for AC coils, 80% of nominal voltage or less for DC coils
Dropout Voltage:	10% of nominal voltage or more
Max. Voltage:	110%
Resistance:	±10% measured @ 25°C
Coil Power:	1.2 watts DC, 2 VA to 2.75 VA (60Hz) AC @ 25°C.
Max. Coil Dissipation:	3.0 watts DC @ 25°C.
Duty:	Continuous

CONTACTS

Contact Material:	Silver alloy, gold flashed
Contact Rating:	10 amps, 120 VAC. 6 amps, 240 VAC 50/60Hz for 3 pole 12 amps, 120 VAC. 8 amps, 240 VAC 50/60Hz for 2 pole 1/3Hp 120 VAC, 1/2Hp 240 VAC. 10 amps, 30 VDC
Contact Resistance:	50 milliohms max. Initial at rated current

TIMING

Operate Time:	15 mS max @ nominal voltage
Release Time:	10 mS max @ nominal voltage

DIELECTRIC STRENGTH

Contacts to Coil:	1250 V rms
Across open Contacts:	500 V rms
Pole to Pole:	1250 V rms
Contacts to Frame:	1250 V rms
Insulation Resistance:	1000 megohms min. @ 500 VDC

TEMPERATURE

Operating:	-45°C to +55°C. (AC) -45°C +70°C. (DC)
Storage:	-45°C to +105°C

VIBRATION RESISTANCE

Functional:	6 g's, 10 to 55Hz (double amplitude)
-------------	--------------------------------------

SHOCK RESISTANCE

Functional:	5 g's
Mechanical:	20 g's

LIFE EXPECTANCY

Electrical:	100,000 operations @ rated resistive load
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS


Operating Position:	Any
Insulation Material:	Molded plastic
Enclosure:	Grey metal case, hermetically sealed
Weigh:	130 grams approx.

**UL GROUPS A, B, C & D CERTIFIED
CLASS 1 DIVISION 2 FOR
HAZARDOUS LOCATIONS****Mating Sockets****70-750D8-1, 70-750D11-1,
70-464-1, 70-465-1: SCREW/DIN
70-169-1, 70-170-1: SCREW/PANEL
See Section 8, page 7 - 12**

NEW
From The Market
Leader in Industrial
Relays

OUTLINE DIMENSIONS



DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



DPDT, 12 AMPS
3PDT, 10 AMPS

**WIRING DIAGRAMS**

(VIEWED FROM PIN END)



STANDARD PART NUMBERS	CONTACT CONFIGU- RATION	COIL MEASURED @ 25°C	
		NOMINAL INPUT VOLTAGE	NOMINAL RESISTANCE (OHMS)
AC OPERATED - 8 PIN OCTAL, 12 AMP			
750XBXH-12A	DPDT	12 VAC, 50/60Hz	72 Ω
750XBXH-24A	DPDT	24 VAC, 50/60Hz	1,700 Ω
750XBXH-120A	DPDT	120 VAC, 50/60Hz	9,100 Ω
DC OPERATED - 8 PIN OCTAL, 12 AMP			
750XBXH-12D	DPDT	12 VDC	120 Ω
750XBXH-24D	DPDT	24 VDC	470 Ω
750XBXH-110D	DPDT	110 VDC	10,000 Ω
AC OPERATED - 11 PIN OCTAL, 10 AMP			
750XCXH-12A	3PDT	12 VAC, 50/60Hz	72 Ω
750XCXH-24A	3PDT	24 VAC, 50/60Hz	1,700 Ω
750XCXH-120A	3PDT	120 VAC, 50/60Hz	9,100 Ω
DC OPERATED - 11 PIN OCTAL, 10 AMP			
750XCXH-12D	3PDT	12 VDC	120 Ω
750XCXH-24D	3PDT	24 VDC	470 Ω
750XCXH-110D	3PDT	110 VDC	10,000 Ω

BENEFITS

CURRENT RATING:	30 AMPS @ 120/240 VAC, 20 AMPS @ 28 VDC	15 AMPS @ 120 VAC, 15 AMPS @ 28 VDC
HORSEPOWER RATING:	1-1/2 HP @ 120 VAC, 2 HP @ 240 VAC	1/4HP @ 120 VAC, NOT UL RATED
TUNGSTEN LOAD RATING:	2.4 KW @ 240 VAC	1 KW @ 120/240 VAC
ELECTRICAL LIFE @ RATED LOAD:	200,000 OPERATIONS	100,000 OPERATIONS

MAGNECRAFT: W21ACPX-2**MIDTEX: TYPE 136****DPDT, 30 AMPS**


UL **us**
UL Recognized
File No. E43641

SP 168986

**MANUFACTURED UNDER
ISO 9002**

OUTLINE DIMENSIONS

DIMENSIONS SHOWN IN INCHES & (MILLIMETERS).



**EXCEEDS NEMA STD. TS
2- 1992 APPROVED BY
D.O.T FOR:**
 California Minnesota
 Georgia New York
 Illinois Texas
 Oregon Colorado
 Maryland Missouri
 North Carolina

**BENEFITS OF RECTIFIED COIL DESIGN:**

1. Chatter Free Operation in Brownout Conditions Down to 85 VAC and Will not Overheat up to 140 VAC.
2. Less Power Consumption and Less Heating.

GENERAL SPECIFICATIONS**COIL**

Pull-in Voltage:	65% of nominal voltage @ 20°C or less for AC coils
Dropout Voltage:	10% of nominal voltage or more
Coil Insulation:	Class "B" system (130°C per UL standard 1446)
Nominal Power:	4.0 VA

CONTACTS

Contact Material:	Silver alloy
Contact Rating:	30 amps, 120/240 VAC (resistive) 25 amps, 120/240 VAC (CSA) 20 amps, 28 VDC (resistive) 1-1/2Hp, 120 VAC, 2Hp, 240 VAC 20 amps, 120 VAC (tungsten lamp) 10 amps, 240 VAC (tungsten lamp)

DIELECTRIC STRENGTH

Across Open Contacts:	500 V rms
Contact to Coil:	1500 V rms
Contact to Frame:	1500 V rms

TEMPERATURE

Operating:	-40°C to +84°C
Storage:	-40°C to +105°C


LIFE EXPECTANCY

Electrical:	200,000 operations @ 20 amps tungsten, 120 VAC
Mechanical:	5,000,000 operations @ no load

MISCELLANEOUS

Enclosure:	Clear polycarbonate
Operating Position:	Vertical, contacts up or horizontal
Weight:	204.7 grams approx.

MOUNTING:
FITS STANDARD
8 PIN JONES PLUG

WIRING DIAGRAM
(VIEWED FROM PIN END)

**SWITCHES
TUNGSTEN LAMP
LOADS UP TO
20 AMPS**

RECTIFIED COIL**COIL MEASURED @ 25°C**

STANDARD PART NUMBER	CONTACT CONFIGU- RATION	NOMINAL INPUT VOLTAGE	NOMINAL POWER
AC RECTIFIED - PLUG-IN, 30 AMP			
W21ACPX-2	DPDT	120 VAC, 50/60Hz	4.0 VA



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	IDEC			
781XAXML-24A	RH1B-L-AC24			
781XAXML-120A	RH1B-L-AC120			
781XAXML-240A	RH1B-L-AC240			
781XAXML-12D	RH1B-L-DC12			
781XAXML-24D	RH1B-L-DC24			
781XAXML-110D	RH1B-L-DC110			
781XAXTML-120A	RH1V2-L-AC120			
781XAXTML-12D	RH1V2-L-DC12			
781XAXTML-24D	RH1V2-L-DC24			
MAGNECRAFT & STRUTHERS-DUNN	IDEC			
781XAXC-24A	RH1B-U-AC24			
781XAXC-120A	RH1B-U-AC120			
781XAXC-24D	RH1B-U-DC24			
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	OMRON		
782DXH10-24A	KHS17A11-24	MY4H-US-24VAC		
782DXH10-120A	KHS17A11-120	MY4H-US-120VAC		
782DXH10-12D	KHS17D11-12	MY4H-US-12VDC		
782DXH10-24D	KHS17D11-24	MY4H-US-24VDC		
782DXH10-110D	KHS17D11-110	-		
782DXH21-120A	KHS17A12-120	-		
782DXH21-12D	KHS17D12-12	-		
782DXH21-24D	KHS17D12-24	-		
MAGNECRAFT & STRUTHERS-DUNN	FINDER	TYCO / SCHRACK (PT REPLACES ZT)		ALLEN-BRADLEY
782DX2M4L-24A	55.34.8024.20.54	PT570524	ZT570524	700-HC24A24-1-4
782DX2M4L-120A	55.34.8120.20.54	PT570615	ZT570615	700-HC24A1-1-4
782DX2M4L-240A	55.34.8240.20.54	PT570730	ZT570730	700-HC24A2-1-4
782DX2M4L-12D	55.34.9012.20.54	PT570012	ZT570012	700-HC24Z12-1-4
782DX2M4L-24D	55.34.9024.20.54	PT570024	ZT570024	700-HC24Z24-1-4
782DX2M4L-110D	55.34.9110.20.54	PT570110	ZT570110	700-HC24Z1-1-4
782XB2M4L-24A	56.32.8024.20.54	PT270524	ZT270524	
782XB2M4L-120A	56.32.8120.20.54	PT270615	ZT270615	
782XB2M4L-240A	56.32.8240.20.54	PT270730	ZT270730	
782XB2M4L-12D	56.32.9012.20.54	PT270012	ZT270012	
782XB2M4L-24D	56.32.9024.20.54	PT270024	ZT270024	
782XB2M4L-110D	56.32.9110.20.54	PT270110	ZT270110	
782XBXM4L-24A	55.32.8024.20.54	PT270524	ZT270524	
782XBXM4L-120A	55.32.8120.20.54	PT270615	ZT270615	
782XBXM4L-240A	55.32.8240.20.54	PT270730	ZT270730	
782XBXM4L-12D	55.32.9012.20.54	PT270012	ZT270012	
782XBXM4L-24D	55.32.9024.20.54	PT270024	ZT270024	
782XBXM4L-110D	55.32.9110.20.54	PT270110	ZT270110	
MAGNECRAFT & STRUTHERS-DUNN	IDEC	OMRON		
782XB2C-24A	RY2S-U-AC24V	MY2-AC24		
782XB2C-120A	RY2S-U-AC110/120V	MY2-AC120		

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS. CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	IDEC	OMRON			
782XBX2C-24D	RY2S-U-DC24V	MY2-DC24			
MAGNECRAFT & STRUTHERS-DUNN	IDEC				
782XBX3C-24A	RY22S-U-AC24V				
782XBX3C-120A	RY22S-U-AC110/120V				
782XBXC3-24D	RY22S-U-DC24V				
MAGNECRAFT & STRUTHERS-DUNN	IDEC				
783XCXM4L-24A	RH3B-ULC-AC24				
783XCXM4L-120A	RH3B-ULC-AC120				
783XCXM4L-240A	RH3B-ULC-AC240				
783XCXM4L-12D	RH3B-ULC-DC12				
783XCXM4L-24D	RH3B-ULC-DC24				
783XCXM4L-110D	RH3B-ULC-DC110				
783XCXTM4L-120A	RH3V2-ULC-AC120				
783XCXTM4L-12D	RH3V2-ULC-DC12				
783XCXTM4L-24D	RH3V2-ULC-DC24				
MAGNECRAFT & STRUTHERS-DUNN	IDEC	OMRON			
783XCXC-24A	RH3B-U-AC24	LY3-AC24			
783XCXC-120A	RH3B-U-AC120	LY3-AC120			
783XCXC-24D	RH3B-U-DC24	LY3-DC24			
MAGNECRAFT & STRUTHERS-DUNN	IDEC	OMRON			
784DXM4L-24A	RH4B-ULC-AC24	LY414N-AC24			
784DXM4L-120A	RH4B-ULC-AC120	LY414N-AC120			
784DXM4L-240A	RH4B-ULC-AC240	LY414N-AC240			
784DXM4L-12D	RH4B-ULC-DC12	LY414N-DC12			
784DXM4L-24D	RH4B-ULC-DC24	LY414N-DC24			
784DXM4L-110D	RH4B-ULC-DC110	LY414N-DC110			
784XDXTM4L-120A	RH4V2-ULC-AC120	-			
784XDXTM4L-12D	RH4V2-ULC-DC12	-			
784XDXTM4L-24D	RH4V2-ULC-DC24	-			
MAGNECRAFT & STRUTHERS-DUNN	IDEC	OMRON			
784DXDC-24A	RH4B-U-AC24	LY4-AC24			
784DXDC-120A	RH4B-U-AC120	LY4-AC120			
784DXDC-24D	RH4B-U-DC24	LY4-DC24			
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	IDEC	OMRON	AROMAT	ALLEN - BRADLEY
W78ATCSX-2	KHAU17A96-12	RY42S-U-AC12V	MY4Z-AC12	HC4D-AC12	700-HC54A24
W78ATCSX-3	KHAU17A96-24	RY42S-U-AC24V	MY4Z-AC24	HC4D-AC24	700-HC54A1
W78ATCSX-5	KHAU17A96-120	RY42S-U-AC110/120V	MY4Z-AC120	HC4D-AC120	
W78ATCSX-6	KHAU17A96-240	RY42S-U-AC220/240V	MY4Z-AC240	HC4D-AC240	
W78TCSX-1	KHAU17D96-6	RY42S-U-DC6V	MY4Z-DC6	HC4D-DC6	700-HC54Z12
W78TCSX-2	KHAU17D96-12	RY42S-U-DC12V	MY4Z-DC12	HC4D-DC12	700-HC54Z24
W78TCSX-3	KHAU17D96-24	RY42S-U-DC24V	MY4Z-DC24	HC4D-DC24	

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS.
CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	IDEC	OMRON	AROMAT	ALLEN - BRADLEY
W78TCSX-5	* KHAU17D16-110	RY42S-U-DC100/110V	MY4Z-DC110	HC4D-DC110	700-HC14A12
W78ACSX-2	* KHAU17A11-12	RY4S-U-AC12V	MY4-AC12		700-HC14A24
W78ACSX-3	* KHAU17A11-24	RY4S-U-AC24V	MY4-AC24		700-HC14A1
W78ACSX-5	* KHAU17A11-120	RY4S-U-AC110/120V	MY4-AC120		700-HC14A2
W78ACSX-6	* KHAU17A11-240	RY4S-U-AC220/240V	MY4-AC240		700-HC14Z06
W78CSX-1	* KHAU17D11-6	RY4S-U-DC6V	MY4-DC6		700-HC14Z12
W78CSX-2	* KHAU17D11-12	RY4S-U-DC12V	MY4-DC12		700-HC14Z24
W78CSX-3	* KHAU17D11-24	RY4S-U-DC24V	MY4-DC24		700-HC14Z1
W78CSX-6	* KHAU17D11-110	RY4S-U-DC100/110V	MY4-DC110		
W78APCX-3	KHAE17A11-24	RY4V-U-AC24V	MY4-02-AC24		
W78APCX-5	KHAE17A11-120	RY4V-U-AC110/120V	MY4-02-AC120		
W78PCX-2	KHAE17D11-12	RY4V-U-DC12V	MY4-02-DC12		
W78PCX-3	KHAE17D11-24	RY4V-U-DC24V	MY4-02-DC24		
W78PCX-6	KHAE17D11-110	RY4V-U-DC100/110V	MY4-02-DC110		
W78KACXSX-15	KHAU17A12-24	RY4S-U-AC24V		HC4-AC24	700-HC24A24
W78KACXSX-17	KHAU17A12-120	RY4S-U-AC110/120V		HC4-AC120	700-HC24A1
W78KACXSX-18	KHAU17A12-240	RY4S-U-AC220/240V		HC4-AC240	700-HC24A2
W78KCSX-12	KHAU17D12-12	RY4S-U-DC12V		HC4-DC12	700-HC24Z12
W78KCSX-13	KHAU17D12-24	RY4S-U-DC24V		HC4-DC24	700-HC24Z24
W78ARCSX-7	K10P11A15-6	RH2B-U-AC6V	LY2-AC6		700-HF32A06
W78ARCSX-9	K10P11A15-24	RH2B-U-AC24V	LY2-AC24		700-HF32A24
W78ARCSX-11	K10P11A15-120	RH2B-U-AC110/120V	LY2-AC120		700-HF32A1
W78ARCSX-12	K10P11A15-240	RH2B-U-AC220/240V	LY2-AC240		700-HF32A2
W78RCSX-6	K10P11D15-6	RH2B-U-DC6V	LY2-DC6		700-HF32Z06
W78RCSX-7	K10P11D15-12	RH2B-U-DC12V	LY2-DC12		700-HF32Z12
W78RCSX-8	K10P11D15-24	RH2B-U-DC24V	LY2-DC24		700-HF32Z24
W78RCSX-9	K10P11D15-48	RH2B-U-DC48V	LY2-DC48		700-HF32Z48
W78RCSX-10	K10P11D15-110	RH2B-UL-DC100/110V	LY2-DC110		700-HF32Z1
W78ARPCX-5	K10P11A55-120	RH2V2-U-AC110/120V	LY2-0-AC120		
W78ARPCX-6	K10P11A55-240	RH2V2-U-AC220/240V	LY2-0-AC240		
W78RPCX-1	K10P11D55-6	RH2V2-U-DC6V	LY2-0-DC6		
W78RPCX-2	K10P11D55-12	RH2V2-U-DC12V	LY2-0-DC12		
W78RPCX-3	K10P11D55-24	RH2V2-U-DC24V	LY2-0-DC24		
W78ARCSX-108			LY1-AC12		
W78ARCSX-109			LY1-AC24		
W78ARCSX-111			LY1-AC120		
W78ARCSX-112			LY1-AC240		
W78ARNCSX-8			LY1N-AC24		
W78ARNCSX-9			LY1N-AC120		
W78ARNCSX-10			LY1N-AC240		
W78RCSX-96			LY1-DC6		
W78RCSX-97			LY1-DC12		
W78RCSX-98			LY1-DC24		
W78RCSX-100			LY1-DC110		
W78RNCSX-10			LY1N-DC24		
W78ARPCX-81			LY1-0-AC12		
W78ARPCX-82			LY1-0-AC24		

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS.
CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.
* 91 STYLE SAME AS 11 STYLE EXCEPT NO STUD



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	OMRON			
W78ARPCX-84	LY1-0-AC120			
W78RPCX-79	LY1-0-DC12			
W78RPCX-83	LY1-0-DC24			
W78RPCX-85	LY1-0-DC110			
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	OMRON	ALLEN - BRADLEY
750XBXM4L-24A	KRPA-11ANFP-24	MT228024	MK2PN-S-AC24	700HA32A24-1-4
750XBXM4L-120A	KRPA-11ANFP-120	MT228115	MK2PN-S-AC120	700HA32A1-1-4
750XBXM4L-240A	KRPA-11ANFP-240	MT228230	MK2PN-S-AC240	700HA32A2-1-4L
750XBXM4L-12D	KRPA-11DNFP-12	MT223012	MK2PN-S-DC12	700HA32Z12-1-4
750XBXM4L-24D	KRPA-11DNFP-24	MT223024	MK2PN-S-DC24	700HA32Z24-1-4
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	OMRON	ALLEN - BRADLEY
750XBXM4L-110D	KRPA-11DNFP-110	MT223110	MK2PN-S-DC110	700HA32Z1-1-4
750XCXM4L-24A	KRPA-14ANFP-24	MT328024	MK3PN-S-AC24	700HA33A24-1-4
750XCXM4L-120A	KRPA-14ANFP120	MT328115	MK3PN-S-AC120	700HA33A1-1-4
750XCXM4L-240A	KRPA-14ANFP-240	MT328230	MK3PN-S-AC240	700HA33A2-1-4L
750XCXM4L-12D	KRPA-14DNFP-12	MT323012	MK3PN-S-DC12	700HA33Z12-1-4
750XCXM4L-24D	KRPA-14DNFP-24	MT323024	MK3PN-S-DC24	700HA33Z24-1-4
750XCXM4L-110D	KRPA-14DNFP-110	MT323110	MK3PN-S-DC110	700HA33Z1-1-4
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	IDEC		DELTRON
A314XBX48P-24A	KRPA-11AG (or GF) -24	RR2P-U-AC24V		20108-82
A314XBX48P-120A	KRPA-11AG (or GF) -120	RR2P-U-AC120V		20108-84
A314XBX48P-240A	KRPA-11AG (or GF) -240	RR2P-U-AC240V		20108-85
A314XCX48P-24A	KRPA-14AG (or GF) -24	RR3PA-U-AC24V		20110-82
A314XCX48P-120A	KRPA-14AG (or GF) -120	RR3PA-U-AC120V		20110-84
A314XCX48P-240A	KRPA-14AG (or GF) -240	RR3PA-U-AC240V		20110-85
A314XBX48P-12D	KRPA-11DG (or GF) -12	RR2P-U-DC12V		20114-81
A314XBX48P-24D	KRPA-11DG (or GF) -24	RR2P-U-DC24V		20114-82
A314XCX48P-12D	KRPA-14DG (or GF) -12	RR3PA-U-DC12V		20116-81
A314XCX48P-24D	KRPA-14DG (or GF) -24	RR3PA-U-DC24V		20116-82
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	ALLEN - BRADLEY		
788XBXM4L-24A	KUP-11A45 (or F) -24	700HB32A24-1-4		
788XBXM4L-120A	KUP-11A45- (or F) 120	700HB32A1-1-4		
788XBXM4L-240A	KUP-11A45- (or F) 240	700HB32A2-1-4L		
788XBXM4L-12D	KUP-11D45- (or F) 12	700HB32Z12-1-4		
788XBXM4L-24D	KUP-11D45- (or F) 24	700HB32Z24-1-4		
788XBXM4L-110D	KUP-11D45- (or F) 110	700HB32Z1-1-4		
788XCXM4L-24A	KUP-14A45- (or F) 24	700HB33A24-1-4		
788XCXM4L-120A	KUP-14A45- (or F) 120	700HB33A1-1-4		
788XCXM4L-240A	KUP-14A45- (or F) 240	700HB33A2-1-4L		
788XCXM4L-12D	KUP-14D45- (or F) 12	700HB33Z12-1-4		
788XCXM4L-24D	KUP-14D45- (or F) 24	700HB33Z24-1-4		
788XCXM4L-110D	KUP-14D45- (or F) 110	700HB33Z1-1-4		

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS. CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	IDEC	OMRON	DELTRON
A283XAXC-24A	KUP5A15 (or F) - 24	RR1BA-U-AC24V	MJN1C-AC24	20306-82
A283XAXC-120A	KUP5A15 (or F) - 120	RR1BA-U-AC120V	MJN1C-AC120	20306-84
A283XAXC-240A	KUP5A15 (or F) - 240	RR1BA-U-AC240V	MJN1C-AC240	20306-85
A283XBXC-24A	KUP11A15 (or F) - 24	RR2BA-U-AC24V	MJN2C-AC24	20307-82
A283XBXC-120A	KUP11A15 (or F) - 120	RR2BA-U-AC120V	MJN2C-AC120	20307-84
A283XBXC-240A	KUP11A15 (or F) - 240	RR2BA-U-AC240V	MJN2C-AC240	20307-85
A283XCXC-24A	KUP14A15 (or F) - 24	RR3B-U-AC24V	MJN3C-AC24	20308-82
A283XCXC-120A	KUP14A15 (or F) - 120	RR3B-U-AC120V	MJN3C-AC120	20308-84
A283XCXC-240A	KUP14A15 (or F) - 240	RR3B-U-AC240V	MJN3C-AC240	20308-85
A283XAXC-12D	KUP5D15 (or F) - 12	RR1BA-U-DC12V	MJN1C-DC12	20309-81
A283XAXC-24D	KUP5D15 (or F) - 24	RR1BA-U-DC24V	MJN1C-DC24	20309-82
A283XBXC-12D	KUP11D15 (or F) - 12	RR2BA-U-DC12V	MJN2C-DC12	20310-81
A283XBXC-24D	KUP11D15 (or F) - 24	RR2BA-U-DC24V	MJN2C-DC24	20310-82
A283XBXC-110D	KUP11D15 (or F) - 110	RR2B-U-DC110V	MJN2C-DC110	20310-84
A283XCXC-12D	KUP14D15 (or F) - 12	RR3B-U-DC12V	MJN3C-DC12	20311-81
A283XCXC-24D	KUP14D15 (or F) - 24	RR3B-U-DC24V	MJN3C-DC24	20311-82
A283XAXC1-120A	KUP5A55 (or F) - 120	RR1BA-US-AC120V	MJN1CF-AC120	20545-84
A283XAXC1-240A	KUP5A55 (or F) - 240	RR1BA-US-AC240V	MJN1CF-AC240	20545-85
A283XBXC1-120A	KUP11A55 (or F) - 120	RR2BA-US-AC120V	MJN2CF-AC120	20546-84
A283XBXC1-240A	KUP11A55 (or F) - 240	RR2BA-US-AC240V	MJN2CF-AC240	20546-85
A283XCXC1-120A	KUP14A55 (or F) - 120	RR3B-US-AC120V	MJN3CF-AC120	20547-84
A283XCXC1-240A	KUP14A55 (or F) - 240	RR1BA-US-DC240V	MJN3CF-AC240	20547-85
A283XAXC1-12D	KUP5D55 (or F) - 12	RR1BA-US-DC12V	MJN1CF-DC12	20551-81
A283XAXC1-24D	KUP11D55 (or F) - 24	RR2BA-US-DC24V	MJN1CF-DC24	20551-82
A283XBXC1-12D	KUP11D55 (or F) - 12	RR2BA-US-DC12V	MJN2CF-DC12	20552-81
A283XBXC1-24D	KUP11D55 (or F) - 24	RR2B-US-DC24V	MJN2CF-DC24	20552-82
A283XCXC1-24D	KUP14D55 (or F) - 24	RR3B-US-DC24V	MJN3CF-DC24	20553-82
A283XB69C-120A	KUEP-11A15-120			
A283XB69C-12D	KUEP-11D15-12			
A283XB69C-24D	KUEP-11D15-24			
A283BXX69C-24D	KUEP-7D15-24			
A283BXX69C-48D	KUEP-7D15-48			
A283XB69C-110D	KUEP-11D15-110			
A283HXX69C-120A	KUEP-3A15-120			
A283HXX69C-12D	KUEP-3D15-12			
A283HXX69C-24D	KUEP-3D15-24			
A283HXX69C-48D	KUEP-3D15-48			
A283HXX69C-110D	KUEP-3D15-110			
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	FINDER	
388JXCXC1M-240A	KUMP-14A68-240	RM333740		
388JXCXC1M-120A	KUMP-14A68-120	RM333615		
388JXCXC1M-12D	KUMP-14D68-12	RM333012		
388JXCXC1M-24D	KUMP-14D68-24	RM333024		
388JXCXCM-240A	KUMP-14A28-240	RM332740	6233 8240 0040	
388JXCXCM-120A	KUMP-14A28-120	RM332615	6233 8120 0040	
388JXCXCM-12D	KUMP-14D28-12	RM332012	6233 9012 0040	
388JXCXCM-24D	KUMP-14D28-24	RM332024	6233 9024 0040	

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS.
CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	FINDER
388JXBXC1M-240A	KUMP-11A68-240	RM233740	
388JXBXC1M-120A	KUMP-11A68-120	RM233615	
388JXBXC1M-12D	KUMP-11D68-12	RM233012	
388JXBXC1M-24D	KUMP-11D68-24	RM233024	
388JXBXC1M-240A	KUMP-11A28-240	RM232740	6232 8240 0040
388JXBXC1M-120A	KUMP-11A28-120	RM232615	6232 8120 0040
388JXBXC1M-12D	KUMP-11D28-12	RM232012	6232 9012 0040
388JXBXC1M-24D	KUMP-11D28-24	RM232024	6232 9024 0040
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	FINDER
388VCXXCM-220/240A	KUGP-12A15-240	RM632740	62.33 8240.0310
388VCXXCM-120A	KUGP-12A15-120	RM632615	62.33 8120.0310
388VCXXCM-24A	KUGP-12A15-24	RM632524	62.32 8024.0310
388VBXXCM-220/240A	KUGP-7A15-240	RM532740	62.22 8240.0310
388VBXXCM-120A	KUGP-7A15-120	RM532615	62.23 8120.0310
388VBXXCM-24A	KUGP-7A15-24	RM532524	62.23 8024.0310
388VCXXCM-24D	KUGP-12D15-24	RM632024	62.32 9024.0310
388VCXXCM-12D	KUGP-12D15-12	RM632012	62.32 9012.0310
388VBXXCM-24D	KUGP-7D15-24	RM532024	62.32 9024.0310
388VBXXCM-12D	KUGP-7D15-12	RM532012	62.33 9012.0310
MAGNECRAFT & STRUTHERS-DUNN		TYCO / SCHRACK	FINDER
389FXCXC1M-240A		RM735740	6283 8240 0040
389FXCXC1M-120A		RM735615	6283 8120 0040
389FXBXC1M-240A		RM835740	6282 8240 0040
389FXBXC1M-120A		RM83561	6282 8240 0040
389FXCXC1M-12D		RM735024	6283 9024 0040
389FXCXC1M-24D		RM735012	6283 9012 0040
389FXBXC1M-12D		RM835024	6282 9024 0040
389FXBXC1M-24D		RM835012	6282 9012 0040
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	TYCO / SCHRACK	DELTROL
W389ADCX-4	KUMP-3A5G-120	RMD 05 615	0840-84
W389ADCX-5	KUMP-3A5G-240	RMD 05 740	20840-85
W389ADZCX-3	KUMP-6A5G-24	RMC 05 524	
W389ADZCX-4	KUMP-6A5G-120	RMC 05 615	
W389DCX-2	KUMP-3D5G-12	RMD 05 012	20848-81
W389DCX-3	KUMP-3D5G-24	RMD 05 024	20848-82
W389DZCX-2	KUMP-6D5G-12	RMC 05 012	
W389DZCX-3	KUMP-6D5G-24	RMC 05 024	
W389ACX-4	KUHP-5A51-120		
W389ACX-8	KUHP11A51-24		
W389ACX-9	KUHP11A51-120		
W389ACX-10	KUHP11A51-240		
W389ACX-14	-		
W389ACX-15	-		
W389CX-2	KUHP5D51-12		
W389CX-3	KUHP5D51-24		

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS. CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD			
W389CX-7				
W389CX-8				
W389CX-12				
W389CX-13				
MAGNECRAFT & STRUTHERS-DUNN	DELTRON			
300XBC1-240A	20844-85			
300XBC1-120A	20844-84			
300XBC1-24A	20844-82			
300XBC1-12A	20844-81			
300XBC1-110D	20852-84			
300XBC1-24D	20852-82			
300XBC1-12D	20852-81			
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	AMERICAN ZETTLER		
W9AS1D52-5	T9AS1D52-5	AZ2280-1A-5DEF		
W9AS1D52-12	T9AS1D52-12	AZ2280-1A-12DEF		
W9AS1D52-24	T9AS1D52-24	AZ2280-1A-24DEF		
W9AS1D52-48	T9AS1D52-48	AZ2280-1A-48DEF		
W9AS1D52-110	T9AS1D52-110	AZ2280-1A-110DEF		
W9AS5D52-5	T9AS5D52-5	AZ2280-1C-5DEF		
W9AS5D52-12	T9AS5D52-12	AZ2280-1C-12DEF		
W9AS5D52-24	T9AS5D52-24	AZ2280-1C-24DEF		
W9AS5D52-48	T9AS5D52-48	AZ2280-1C-48DEF		
W9AS5D52-110	T9AS5D52-110	AZ2280-1C-110DEF		
W9AS1A52-24		AZ2280-1A-24AEF		
W9AS1A52-120		AZ2280-1A-120AEF		
W9AS1A52-240		AZ2280-1A-240AEF		
W9AS5A52-24		AZ2280-1C-24AEF		
W9AS5A52-120		AZ2280-1C-120AEF		
W9AS5A52-240		AZ2280-1C-240AEF		
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD	AMERICAN ZETTLER	OMRON	AROMAT
W92S7D22-12	T92P7D22-12	AZ2800-2A-12D	G7L-2A-TUB-CB-DC24	HE2aN-Q-DC24V
W92S7D22-24	T92P7D22-24	AZ2800-2A-24D	G7L-2A-TUB-CB-DC110	HE2aN-Q-DC110V
W92S7D22-110	T92P7D22-110	AZ2800-2A-110D		
W92S11D22-12	T92P11D22-12	AZ2800-2C-12D		
W92S11D22-24	T92P11D22-24	AZ2800-2C-24D		
W92S11D22-110	T92P11D22-110	AZ2800-2C-110D	G7L-2A-TUB-CB-AC24	HE2aN-Q-AC24V
W92S7A22-24	T92P7A22-24	AZ2800-2A-24AE	G7L-2A-TUB-CB-AC120	HE2aN-Q-AC120V
W92S7A22-120	T92P7A22-120	AZ2800-2A-120AE	G7L-2A-TUB-CB-AC240	HE2aN-Q-AC240V
W92S7A22-240	T92P7A22-240	AZ2800-2A-240AE		
W92S11A22-24	T92P11A22-24	AZ2800-2C-24AE		
W92S11A22-120	T92P11A22-120	AZ2800-2C-120AE		
W92S11A22-240	T92P11A22-240	AZ2800-2C-240AE		
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD			
W67RCSX-1	R10E1(X or Y)2-V28			
W67RCSX-2	R10E1(X or Y)2-V185			

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT, INTERNAL WIRING, AND CONTACT LOAD RATINGS. CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.



SECTION 1 CROSS REFERENCE GUIDE

MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD
W67RCSX-3	R10E1(X or Y)2-V700
W67RCSX-4	R10E1(X or Y)2-V2.5K
W67RCSX-5	R10E1(X or Y)2-V15.0K
W67RCSX-6	R10E1(X or Y)4-V28
W67RCSX-7	R10E1(X or Y)4-V185
W67RCSX-8	R10E1(X or Y)4-V700
W67RCSX-9	R10E1(X or Y)4-V2.5K
W67RCSX-10	R10E1(X or Y)4-V15.0K
W67RCSX-12	R10E1(X or Y)6-V90
W67RCSX-13	R10E1(X or Y)6-V430
W67TRCSX-2	R10E1(P or Z)2-V185
W67TRCSX-3	R10E1(P or Z)2-V700
W67TRCSX-7	R10E1(P or Z)4-V185
W67TRCSX-8	R10E1(P or Z)4-V700
W67TRCSX-12	R10E1(P or Z)6-V90
W67TRCSX-13	R10E1(P or Z)6-V430
W67RPCX-2	R10E2(X or Y)2-V185
W67RPCX-3	R10E2(X or Y)2-V700
W67RPCX-7	R10E2(X or Y)4-V185
W67RPCX-8	R10E2(X or Y)4-V700
W67RPCX-12	R10E2(X or Y)6-V90
W67RPCX-13	R10E2(X or Y)6-V430
W67ARCSX-5	R10E1(X or Y)2-120V
W67ARCSX-10	R10E1(X or Y)4-120V
W67ARCSX-15	R10E1(X or Y)6-120V
W67SCSX-1	R10SE1(X or Y)2-J1.0K
W67SCSX-2	R10SE1(X or Y)2-J2.5K
W67SCSX-3	R10SE1(X or Y)2-J5.0K
W67SCSX-6	R10SE1(X or Y)4-J1.0K
W67SCSX-7	R10SE1(X or Y)4-J2.5K
W67SCSX-8	R10SE1(X or Y)4-J5.0K
MAGNECRAFT & STRUTHERS-DUNN	TYCO / POTTER & BRUMFIELD
750XBXH-12A	KR11AGE (or GF) 12
750XBXH-24A	KR11AGE (or GF) 24
750XBXH-120A	KR11AGE (or GF) 120
750XBXH-12D	KR11DGE (or GF) 12
750XBXH-24D	KR11DGE (or GF) 24
750XBXH-110D	KR11DGE (or GF) 110
750XCXH-12A	KR14AGE (or GF) 12
750XCXH-24A	KR14AGE (or GF) 24
750XCXH-120A	KR14AGE (or GF) 120
750XCXH-12D	KR14DGE (or GF) 12
750XCXH-24D	KR14DGE (or GF) 24
750XCXH-110D	KR14DGE (or GF) 110
MAGNECRAFT & STRUTHERS-DUNN	MIDTEX
W21ACPX-2	136-62T3A1

THE CROSS REFERENCE IS INTENDED TO MATCH FOOT PRINT,
INTERNAL WIRING, AND CONTACT LOAD RATINGS.
CONSTRUCTION FEATURES AND GENERAL SPECIFICATIONS
SHOULD BE COMPARED IF EXACT REPLACEMENT IS REQUIRED.

U. S. A.

TELEPHONE: (843)393-5778

FAX: (843)393-4123

WEBSITE: www.magnecraft.com

EMAIL: info@magnecraft.com

EUROPE

TELEPHONE: 4989 / 75080310

FAX: 4989 / 7559344

WEBSITE: www.magnecraft.com

EMAIL: renatesteinback@magnecraft.de

FOR SOCKET COMPATIBLE AND FLANGE MOUNTED RELAYS APPLICATION ENGINEERING ASSISTANCE

Chuck Johnson, PRODUCT MANAGER

FAX: (847) 441-2522

EMAIL: cjohnson@magnecraft.com

Tom Mahaffey, PRODUCT MANAGER

FAX: (843) 395-8530

EMAIL: tmahaffey@magnecraft.com

FAX ON DEMAND: 1-800-891-2957

DOCUMENT: 500