




Part Number

ERA.1S.275.CTL **Size/Series** 1S / S **Request a quote**

MECHANICAL DETAILS

Shell Style/Model ERA*: Fixed receptacle, nut fixing
Keying Circular (can rotate), plug has male contact(s)
Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Cable Fixing J : 0 - 0 mm
Variant :

	A	B	E	L	L1	M	S1	S3	e
mm.	14	16	7.5	20.2	20.5	1.5	10.5	14	M12x1.0
in.	0.55	0.63	0.30	0.80	0.81	0.06	0.41	0.55	



PERFORMANCE DETAILS

Insert Configuration 1S.275 : 1 Coax (75 Ohm)
Insulator T: PTFE
Specifications
Contact Type: Coaxial 75 Ohm (Solder)
Max. Matings: 1000
Contact Dia.: 1.3 mm (0.0512in)
Bucket Dia.: 1.1 mm (0.0432in)
Vtest: 2400 V (AC), 3300 V (DC)
Rated Current: 10 A (AC/DC)
Impedance: 75 Ohm
VSWR: 1.02 + 0.08 * f/GHz
Cable type: RG 179 B/U, RG 187 A/U, RG 58 C/U, RG 302 /U, RG 400 /U, 2YCCY, RG 59 B/U, RG 223 /U, HF-5408

OTHER CHARACTERISTICS

Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Salt Spray Corrosion: >144 hr
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
IP Rating 50
Catalog

