

Series 15600 ATC® Blade-Type Fuse Panels



The 15600 ATC® fuse panel is a compact, yet rugged, power distribution module. It is available in a single or dual internal buss electrical configuration featuring an optional ground pad terminal strip. The 15600 fuse panel is surface mounted, uses convenient quick-connect terminals, and is recommended as a supplemental power distribution module. It can be used to accompany main PDMs such as the Cooper Bussmann 31000/32000 Series VEC/DVEC, 15710 Series RTA, and the 1540X Series RFRM.


Specifications

- Input Terminal Rating:** #10-32 Threaded studs (100A max).
- Output Terminal Rating:** 30A Max per circuit.
- Temperature Rating:** -20°F (0°C) to 150°F (65°C).
- Materials:** Black thermoplastic.
- Termination:** .250" x .032" quick-connect terminals. Ground terminal pad option available. Input wire size: #4-6 AWG. Output wire size: #12-16 AWG.
- Torque Rating:** 20 in-lbs (2.25N•m) max.
- Mounting Torque Rating:** 8 in-lbs (0.9N•m) max.

Options

- Positions:** 4-20 circuits available.
- Split Power:** Single or dual buss options.

Dimensions - mm(in)



Part Numbering System

Series	No. of Fuses &/or Circuit Breaker Positions	Hardware Options	Ground Terminal Base
0	04-20	0	0
1560	Left Side Right Side	1	1
2	(max. combination of 20)	2	
0 - Single Stud, Single Supply Circuit		0 - W/O nuts	0 - None
2 - Double Stud, Split Supply Circuits		1 - Nuts shipped bulk	1 - Include Ground Pad
		2 - Nuts assembled	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cooper Bussmann:

[15600-04-20](#) [15600-04-21](#) [15600-06-10](#) [15600-08-10](#) [15600-10-10](#) [15600-14-20](#) [15600-14-21](#) [15600-16-20](#)
[15600-16-21](#) [15600-18-10](#) [15600-18-20](#) [15600-18-21](#) [15602-04/16-20](#) [15602-04/06-21](#) [15600-06-11](#) [15602-04/06-20](#) [15600-10-00](#)