


[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

You Searched For: **MDMV-9PH003B-A174**

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS.

ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.

[Sales Support](#)
[Product Overview](#)
[Stock Check](#)

Our Descriptive Part Number: MDMV-9PH003B-A174

Our Global Manufacturing Part Number: 096660-0029

Export Compliance

	Country of Compliance	United States
	Export Compliance Notes	Commercial Shipments "C" Controlled by the US Department of Commerce.

Product Datasheet	
Product Group	Microminiature
Product Sub-Group	MDM
Market Application	Commercial
Contact Arrangement	9
Contact Type	Pin
Termination Type	Harness-insulated wire.
Termination Code	18", 7/34 strand, #26 AWG. MIL-W-16878/4, Type E Teflon, color coded to MIL-STD-681 System I
Hardware	.091 (2.31) diameter hole.
Shell Finish	Electroless Nickel
Insulator Material	Polyester
Contact Material	Copper alloy, Gold plate
Mounting Hardware	300 Series stainless steel, passivated
Washer Material	400 Series stainless steel, passivated
Coupling - Mechanical Feature	Friction / Jackscrews
Polarization	Keystone - shaped shells
Coaxial Cable	RG-178 / U
Contact Termination	Multiple indent crimp
Insulation Resistance	Method: 3003, Criteria of Acceptance: 5,000 Mega ohms minimum