

Power Relay 430 3mm

- 1 pole 16A, 1 form A (NO) contact
- Safety mains isolation
- Contact gap >3mm
- DC and AC coil
- 4kV/8mm coil-contact, reinforced insulation (VDE 0700)
- PCB mounting or quick connect terminals
- Mounting brackets or snap mounting
- Version with arc blow magnet for high DC loads
- WG version: product in accordance to IEC 60335-1

Typical applications

Domestic appliances, industrial appliances, industrial controls.

Approvals

VDE REG.-Nr. C820, UL E214024

Technical data of approved types on request.

Contact Data

Contact arrangement	1 form A (NO)
Contact gap	>3mm
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	16A
Limiting making current, max 4 s, duty factor 10%	25A
Breaking capacity max.	4000VA
Contact material	AgCu3
Contact style	bifurcated contact
Frequency of operation, with/without load	900/18000h ⁻¹

Contact ratings

Type	Contact	Load	Cycles
IEC 61810			
0430 .4 .. 0	A (NO)	16A, 250VAC, cosφ=1, 70°C	50x10 ³

Mechanical endurance

DC coil	>250x10 ³ operations
AC coil	>250x10 ³ operations



F0256-B

Coil Data

Coil voltage range	
DC coil	6 to 110VDC
AC coil	6 to 240VAC
Operative range, IEC 61810	2

Coil versions, DC coil

Coil code	Rated voltage VDC	Operate voltage VDC	Release voltage VDC	Coil resistance Ω±10%	Rated coil power mW
09	12	7.8	0.6	145	993
10	24	15.6	1.2	580	993
11	48	31.2	2.4	2200	1047
13	110	71.5	5.5	13000	931

All figures are given for coil without pre-energization, at ambient temperature +23°C.

Other coil voltages on request.



Coil versions, AC coil, 50Hz

Coil code	Rated voltage VAC	Operate voltage VAC	Release voltage VAC	Coil resistance Ω±10%	Rated coil power VA
23	24	18	3.6	145	1.8
25	60	45	9	950	1.8
26	110	83	16	3100	1.8
27	230	175	35	11400	1.8
28	240	185	36	13000	1.8

All figures are given for coil without pre-energization, at ambient temperature +23°C, 50Hz. Other coil voltages on request.

Insulation Data

Initial dielectric strength	
between open contacts	2000V _{ms}
between contact and coil	4000V _{ms}
Clearance/creepage	
between contact and coil	≥8/8mm
Material group of insulation parts	IIla
Tracking index of relay base	PTI250



Power Relay 430 3mm (Continued)

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customer-support/rohssupportcenter

Resistance to heat and fire according EN60335, par.30

Ambient temperature -20 to +70°C

Category of environmental protection

IEC 61810

RTI - dust protected

Shock resistance (destructive)

100g

Terminal type

PCB-THT, quick connect

Mounting

PCB, mounting brackets,
snap mounting, DIN rail

Weight

32g

Resistance to soldering heat THT

IEC 60068-2-20


270°C/10s

Packaging unit


50 pcs.

PCB layout / terminal assignment

Bottom view on solder pins



S0448-AE




S0448-AF



Dimensions

Snap mounting

PCB mounting



S0449-CH





S0449-CB

Power Relay 430 3mm (Continued)

Dimensions

Mounting brackets

DIN-rail mount



S0449-CK

Product code structure

Typical product code **0430 2 5 09 0 100**

Type

0430 Power relay 430 3mm

Mounting

0 PCB version **2** Snap mounting
1 Mounting brackets **5** DIN-rail mounting

Contact design

4 Arc blowing magnet
5 Standard

Coil

Coil code: please refer to coil versions table

Contact material

0 AgCu 3

Version

100 Standard

100WG Product in accordance with IEC 60335-1 (domestic appliances) only available on request

Other types on request.

Product code	Mounting	Cont. material	Cont. arrangement	Coil	Part Number
0430 04 0901 00	PCB version	AgCu3	1 form A (NO)	DC coil	3-1415535-3
0430 04 1001 00					2-1415535-8
0430 15 1001 00	Mounting Bracket				2-1415535-9
0430 55 1001 00	DIN-rail mounting				3-1415404-9
0430 25 2701 00	Snap mounting			AC coil	5-1415543-2