






REQUIREMENTS

- 1- CLIP FOR T0218/T0220
- 2- FORCE MIN. AT S: 4.5 mm = 10 N
- 3- FORCE MIN. AT S: 5.0 mm = 12 N




SCALE 1 : 1

Important dimensions

Note:

THIS DOCUMENT CONTAINS AAVID THERMALLOY'S INTELLECTUAL PROPERTY WHICH IS SUPPLIED IN CONFIDENCE; IT MUST NOT BE USED FOR ANY PURPOSE OTHER THAN WHICH IT IS SUPPLIED; IT MUST NOT BE REPRODUCED WITHOUT WRITTEN PERMISSION FROM THE OWNERS



AAVID THERMALLOY
EUROPE www.aavidthermalloy.com

Via XXV Aprile, 32
40057 Cadrilano - Bologna ITALY
Tel. +39 051 764011
Fax +39 051 764090

Cheney Manor
SWINDON WILTS SN2 2QN UK
Tel. +44 1793 401400
Fax +44 1793 615396

COMPANY
WITH QUALITY SYSTEM
CERTIFIED BY LRQA
ISO 9001:2000



Format A4

Die n.

Factor

Perim.

Area

Weight

1
A 07Feb07

ORIGINAL (Was ZA4597-6)

Revision description

MATERIAL EN10132-4 C67S 0.4x14.5

GENERAL TOLERANCES

Machining ± 1 mm

FINISH Zn high resistance plated

RoHS Compliant

Corrosion resistance: 50 h Neutral salt

Vis. n.

Drawn

Check

R. Tassinari

DRAWING n.

439651

Description:

CLIP-STEEL-14.5x21x0.4-ZH
ROHS COMPLIANT- (4597G)

By