


[About Us](#)
[Products](#)
[Services](#)
[Support](#)
[Projects](#)
[Web Shop](#)

Products

[» Board Comparison Chart](#)
[» Developer's Kits](#)
[» OEM Boards](#)
[↓ QuickStart Boards](#)
[» LPC1343](#)
[» **LPC2106 RS232**](#)
[» LPC2129 CAN](#)
[» LPC2148 USB](#)
[» Prototype board](#)
[» Christmas Tree](#)
[» Color LCD Bluetooth Game](#)
[» Education Boards](#)
[» LPCXpresso & mbed](#)
[» Displays](#)
[» Tools](#)
[» Accessories](#)

LPC2106 RS232 QuickStart Board



Price Information

EUR

Art.no: **EA-QSB-002** [Buy](#)

Price Information

EUR

With a prototype board

Art.no: **EA-QSB-102** [Buy](#)

[Overview](#)
[Specification](#)
[MCU](#)
[Related Products](#)
[Resources](#)
[FAQ](#)

LPC2106 RS232 QuickStart Board

<i>Processor</i>	NXP's ARM7TDMI LPC2106 microcontroller
<i>Program Flash</i>	128 KB
<i>Data Memory</i>	64 KB
<i>Clock Crystals</i>	14.7456 MHz crystal for maximum execution speed (4x PLL = 58,9824 Mhz CPU clock)
<i>Dimensions</i>	27.9 x 65.3 mm
<i>Power</i>	On-board low-dropout voltage and reset generation - Generates +3.3V and +1.8V from a +5V supply +3.3V available for external circuits, up to 300 mA - Power supply: 4-6 VDC
<i>Connectors</i>	- All LPC2106 I/O pins are available on connectors - RS232, DSUB-9 (ESD/EMI protected)
<i>Other</i>	256 Kbit I2C E2PROM - Simple and automatic program download (ISP) via serial channel. Circuit that automatically controls the bootloader from RS232 channel - DIL40 form factor with 2x20 pins (15.24 mm, 0.60" between pin rows) - Four layer PCB (FR-4 material) for best noise immunity - Easy to connect to JTAG signals