





Alcoa Fastening
Systems


DATA SHEET



.88 in. = 22 mm
1.16 in. = 29 mm
2.24 in. = 56 mm
3.26 in. = 83 mm



For 100° Flush Head MAGNA-LOK
Fasteners, Use Anvil Inserts
#116179 For 3/16 Diameter
#116180 For 1/4 Diameter



See other side of this sheet for notes, assembly instructions
and how to attach nose assembly to installation tool.

Alcoa Fastening Systems

Commercial Products

1 Corporate Drive - Kingston, NY 12401

TYPE: Blind Rivet, Convertible
FOR: MAGNA-LOK -06 & -08
TOOL: 210; 211; 212; 2400 only

99-1451

NOSE ASSEMBLY

OTHER

PRODUCT REVISION: 1-84
REVISED: 9/19/01

REPLACE MENT PARTS

REF. PART NO.	REQ.	DESCRIPTION	REF. PART NO.	REQ.	DESCRIPTION
1	116156	Driving Anvil - MGL-06	7	504550	O-ring - AS 568-011
2	116158	Driving Anvil - MGL-08	8	505371	Spring - Lee #LC-045E-18
3	115429	Holder - Anvil	9	115427	Spindle Extension
4	115428	Coil	10	89794	Lock Collar
5	116299	Gripper Jaws	11	89140	Shim
6	115714	Follower & Pintail Tube Assem.	12	115432	Jam Nut