






⚠ MATERIAL: HOUSING - NYLON MOLDING COMPOUND, 94V-0, GLASS FILLED, BLACK.
TERMINALS - 0.25[.010] THICK BRASS PLATED WITH 0.254 MICRONS[.000010] MINIMUM THICK GOLD OVER 1.016 MICRONS [0.000040] MINIMUM THICK PALADIUM NICKEL OVER 0.05 MICRONS[.000002] MINIMUM THICK GOLD IN CONTACT AREAS AND 3.8 MICRONS[.000150] MINIMUM THICK TIN-LEAD ON SOLDER TINES OVER 2.54 MICRONS[.000100] MINIMUM THICK NICKEL UNDERPLATE.
SHIELD - STAINLESS STEEL, TIN-LEAD PLATED
STRIKER PLATE - STAINLESS STEEL.

OBSOLETE	TAPE & REEL	KEY 5-15	5-569331-5
	TAPE & REEL	KEY 4-15 LAN	5-569331-4
	TAPE & REEL	KEY 3-15 MODEM	5-569331-3
	TAPE & REEL	KEY 2-15 MULTI-FUNCTION	5-569331-2
	TAPE & REEL	KEY 1-15 CLOSED	5-569331-1
	PACKAGING	KEYING OPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST REVISION.		DWN R. BURCH/UTA 24 SEPT 96	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK N. JONES 11 OCT 96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. TRAMMEL 18 OCT 96	NAME	
0 PLC ±.0		PRODUCT SPEC	HEADER ASSEMBLY, SHIELDED, DUAL 15, TYPE II, SERIES III INFOPORT™	
1 PLC ±.01		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
2 PLC ±.02		—	A1 00779 C-569331	
3 PLC ±.03		WEIGHT	SCALE 10:1 SHEET 1 OF 2 REV C	
4 PLC ±.04		CUSTOMER DRAWING		
ANGLES FINISH				



LOC		DIST		REVISIONS			
AA		23		DATE	OWN	APVD	
				SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHALL BE CONTACTED FOR THE LATEST REVISION.				AMP Incorporated Harrisburg, PA 17105-3608			
DWN R. BURCH/UTA		24 SEPT 96		NAME HEADER ASSEMBLY, SHIELDED, DUAL 15, TYPE II, SERIES III INFOPORT™			
CHK N. JONES		11 OCT 96		SIZE A1		CAGE CODE 00779	
APVD J. TRAMMEL		18 OCT 96		DRAWING NO C-569331		SCALE 10:1	
PRODUCT SPEC		APPLICATION SPEC		WEIGHT		SHEET 2	
MATERIAL		FINISH		CUSTOMER DRAWING		OF 2	
						REV C	