






		1	2	3	4	5	6	7																																																																																				
A	     PCB Layout ② NOTES: MATERIAL: 1.1 Housing Material: 25%Glass filled PBT, UL94V-0,Black; 1.2 Contact Material: Phosphor Bronze, Tin plated over Nickel; ELECTRICAL: 2.1 Current Rating: 1AMP; 2.2 Insulation Resistance: 1000MΩ Min at 500V; 2.3 Contact Resistance: 30mΩ Max at DC 100mA; 2.4 Withstand Voltage: 500VAC For 1minute; 3. Operating Temperature: -55°C to +105°C. ②③ <table><thead><tr><th rowspan="2">WSW P/N</th><th rowspan="2">Position</th><th colspan="4">Dimension</th></tr><tr><th>A</th><th>B</th><th>C</th><th>D</th></tr></thead><tbody><tr><td>A 08-LC-TR</td><td>08</td><td>10.16</td><td>7.62</td><td>10.05</td><td>7.62</td></tr><tr><td>A 14-LC-TR</td><td>14</td><td>17.78</td><td>15.24</td><td>10.05</td><td>7.62</td></tr><tr><td>A 16-LC-TR</td><td>16</td><td>20.32</td><td>17.78</td><td>10.05</td><td>7.62</td></tr><tr><td>A 18-LC-TR</td><td>18</td><td>22.86</td><td>20.32</td><td>10.05</td><td>7.62</td></tr><tr><td>A 20-LC-TR</td><td>20</td><td>25.40</td><td>22.86</td><td>10.05</td><td>7.62</td></tr><tr><td>A 24-LC-TR</td><td>24</td><td>30.48</td><td>27.94</td><td>17.6</td><td>15.24</td></tr><tr><td>A 24-LC-TR01</td><td>24</td><td>30.48</td><td>27.94</td><td>10.05</td><td>7.62</td></tr><tr><td>A 28-LC-TR</td><td>28</td><td>35.56</td><td>33.02</td><td>17.6</td><td>15.24</td></tr><tr><td>A 28-LC-TR01</td><td>28</td><td>35.56</td><td>33.02</td><td>10.05</td><td>7.62</td></tr><tr><td>A 32-LC-TR</td><td>32</td><td>40.54</td><td>38.10</td><td>17.6</td><td>15.24</td></tr><tr><td>A 40-LC-TR</td><td>40</td><td>50.80</td><td>48.26</td><td>17.6</td><td>15.24</td></tr><tr><td>A 42-LC-TR</td><td>42</td><td>53.21</td><td>50.80</td><td>17.6</td><td>15.24</td></tr></tbody></table>									WSW P/N	Position	Dimension				A	B	C	D	A 08-LC-TR	08	10.16	7.62	10.05	7.62	A 14-LC-TR	14	17.78	15.24	10.05	7.62	A 16-LC-TR	16	20.32	17.78	10.05	7.62	A 18-LC-TR	18	22.86	20.32	10.05	7.62	A 20-LC-TR	20	25.40	22.86	10.05	7.62	A 24-LC-TR	24	30.48	27.94	17.6	15.24	A 24-LC-TR01	24	30.48	27.94	10.05	7.62	A 28-LC-TR	28	35.56	33.02	17.6	15.24	A 28-LC-TR01	28	35.56	33.02	10.05	7.62	A 32-LC-TR	32	40.54	38.10	17.6	15.24	A 40-LC-TR	40	50.80	48.26	17.6	15.24	A 42-LC-TR	42	53.21	50.80	17.6	15.24	A
WSW P/N	Position	Dimension																																																																																										
		A	B	C	D																																																																																							
A 08-LC-TR	08	10.16	7.62	10.05	7.62																																																																																							
A 14-LC-TR	14	17.78	15.24	10.05	7.62																																																																																							
A 16-LC-TR	16	20.32	17.78	10.05	7.62																																																																																							
A 18-LC-TR	18	22.86	20.32	10.05	7.62																																																																																							
A 20-LC-TR	20	25.40	22.86	10.05	7.62																																																																																							
A 24-LC-TR	24	30.48	27.94	17.6	15.24																																																																																							
A 24-LC-TR01	24	30.48	27.94	10.05	7.62																																																																																							
A 28-LC-TR	28	35.56	33.02	17.6	15.24																																																																																							
A 28-LC-TR01	28	35.56	33.02	10.05	7.62																																																																																							
A 32-LC-TR	32	40.54	38.10	17.6	15.24																																																																																							
A 40-LC-TR	40	50.80	48.26	17.6	15.24																																																																																							
A 42-LC-TR	42	53.21	50.80	17.6	15.24																																																																																							
B										B																																																																																		
C										C																																																																																		
D										D																																																																																		
E										E																																																																																		
F										F																																																																																		
G	RoHS compliant Unit:mm		Scale	Free				Date	Name	Description: IC Socket	G																																																																																	
TOLERANCE							Drawn	26.05.2014	Ray																																																																																			
X.			±0.38	③	The 48Pin version is EOL	19.06.2023	Peter	Approved	19.06.2023	Peter	ASSMANN WSW-No.																																																																																	
X.X			±0.25								A xx-LC-TR																																																																																	
X.XX			±0.13	②	Update the drawing	11.06.2021	Segal																																																																																					
DIM			TOL	①	Update the drawing	29.07.2014	Amy	ASSMANN WSW/ components		Drawing-No.	ASS 6449 CO	rev03																																																																																
				①	Drawn	26.05.2014	Ray			Customer-No.			SHEET																																																																															
H <td colspan="2"></td> <td>Angle</td> <td>±3°</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <th>H</th>			Angle	±3°							H																																																																																	
			Angle	TOL	Id.	Modification	Date	Name			1 / 1																																																																																	
		1	2	3	4	5	6	7																																																																																				