



Main

Range of product	TeSys GV2
Device short name	GV2LE
Product or component type	Circuit breaker
Circuit breaker application	Motor protection
Poles description	3P
Network type	AC
Utilisation category	Category A conforming to IEC 60947-2 AC-3 conforming to IEC 60947-4-1
Network frequency	50/60 Hz conforming to IEC 60947-2
Breaking capacity	Icu = 100 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 100 kA at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 3 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2 Icu = 10 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	100 % at 400/415 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 440 V AC 50/60 Hz conforming to IEC 60947-2 75 % at 690 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 230/240 V AC 50/60 Hz conforming to IEC 60947-2 100 % at 500 V AC 50/60 Hz conforming to IEC 60947-2
Trip unit rating	10 A
Trip unit technology	Magnetic
Magnetic tripping current	138 A

Complementary

Mounting mode	By clips By screws
Mounting support	Plate Rail
Mounting position	Horizontal Vertical
Motor power kW	5.5 kW at 500 V AC 50/60 Hz 7.5 kW at 690 V AC 50/60 Hz 5.5 kW at 690 V AC 50/60 Hz 4 kW at 500 V AC 50/60 Hz 4 kW at 400/415 V AC 50/60 Hz 3 kW at 400/415 V AC 50/60 Hz
Control type	Toggle
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Power dissipation per pole	1.8 W
Mechanical durability	100000 cycles
Electrical durability	100000 cycles for AC-3 at 415 V

Operating rate	40 cyc/h
Rated duty	Continuous conforming to IEC 60947-4-1
Connections - terminals	Screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness : flexible - with cable end Screw clamp terminals 2 cable(s) 1.5...6 mm ² - cable stiffness : flexible - without cable end Screw clamp terminals 2 cable(s) 1...6 mm ² - cable stiffness : solid
Tightening torque	1.7 N.m - on screw clamp terminals
Mechanical robustness	Vibrations 5 Gn, 5...150 Hz conforming to IEC 60068-2-6 Shocks 30 Gn conforming to IEC 60068-2-27
Suitability for isolation	Yes conforming to IEC 60947-1
Height	89 mm
Width	45 mm
Depth	78.5 mm
Product weight	0.33 kg

Environment

Standards	EN 60204 IEC 60947-1 IEC 60947-2 NF C 63-120 NF C 63-650 NF C 79-130 VDE 0113 VDE 0660
Product certifications	CCC CSA
Protective treatment	TH
IK degree of protection	IK04
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C
Fire resistance	960 °C conforming to IEC 60695-2-1
Operating altitude	2000 m