

74LVX14

Low Voltage Hex Inverter with Schmitt Trigger Input

General Description

The LVX14 contains six inverter gates each with a Schmitt trigger input. They are capable of transforming slowly changing input signals into sharply defined, jitter-free output signals. In addition, they have a greater noise margin than conventional inverters.


The LVX14 has hysteresis between the positive-going and negative-going input thresholds (typically 1.0V) which is determined internally by transistor ratios and is essentially insensitive to temperature and supply voltage variations.

The inputs tolerate voltages up to 7V allowing the interface of 5V systems to 3V systems.

Features


- Input voltage level translation from 5V to 3V
- Ideal for low power/low noise 3.3V applications
- Available in SOIC JEDEC, SOIC EIAJ and TSSOP packages
- Guaranteed simultaneous switching noise level and dynamic threshold performance

Logic Symbol



TL/F/11603-2

Connection Diagram



TL/F/11603-1

Pin Names	Description
I_n	Inputs
$\bar{O}_n$	Outputs

Truth Table

Input	Output
A	$\bar{O}$
L	H
H	L

	SOIC JEDEC	SOIC EIAJ	TSSOP
Order Number	74LVX14M 74LVX14MX	74LVX14SJ 74LVX14SJX	74LVX14MTC 74LVX14MTCX
See NS Package Number	M14A	M14D	MTC14

Absolute Maximum Ratings (Note)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

Supply Voltage (V_{CC})	−0.5V to +7.0V
DC Input Diode Current (I_{IK})	−20 mA
$V_I = -0.5V$	−20 mA
DC Input Voltage (V_I)	−0.5V to 7V
DC Output Diode Current (I_{OK})	−20 mA
$V_O = -0.5V$	−20 mA
$V_O = V_{CC} + 0.5V$	+20 mA
DC Output Voltage (V_O)	−0.5V to $V_{CC} + 0.5V$
DC Output Source or Sink Current (I_O)	±25 mA
DC V_{CC} or Ground Current (I_{CC} or I_{GND})	±50 mA
Storage Temperature (T_{STG})	−65°C to +150°C
Power Dissipation	180 mW

Note: The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.

Recommended Operating Conditions

Supply Voltage (V_{CC})	2.0V to 3.6V
Input Voltage (V_I)	0V to 5.5V
Output Voltage (V_O)	0V to V_{CC}
Operating Temperature (T_A)	−40°C to +85°C
Input Rise and Fall Time ($\Delta t/\Delta v$)	0 ns/V to 100 ns/V

DC Electrical Characteristics

Symbol	Parameter	V _{CC}	74LVX14			74LVX14		Units	Conditions	
			T _A = +25°C			T _A = −40°C to +85°C				
			Min	Typ	Max	Min	Max			
V _{t+}	Positive Threshold	3.0	2.2			2.2		V		
V _{t−}	Negative Threshold	3.0	0.9			0.9		V		
V _H	Hysteresis	3.0	0.3		1.2	0.3 1.2		V		
V _{OH}	High Level Output Voltage	2.0 3.0 3.0	1.9 2.9 2.58	2.0 3.0		1.9 2.9 2.48	V	V _{IN} = V _{IL} or V _{IH}	I _{OH} = −50 μA I _{OH} = −50 μA I _{OH} = −4 mA	
V _{OL}	Low Level Output Voltage	2.0 3.0 3.0		0.0 0.0	0.1 0.1 0.36	0.1 0.1 0.44	V	V _{IN} = V _{IL} or V _{IH}	I _{OL} = 50 μA I _{OL} = 50 μA I _{OL} = 4 mA	
I _{IN}	Input Leakage Current	3.6	±0.1			±1.0		μA	V _{IN} = 5.5V or GND	
I _{CC}	Quiescent Supply Current	3.6	2.0			20		μA	V _{IN} = V _{CC} or GND	

Noise Characteristics

Symbol	Parameter	V _{CC} (V)	74LVX14		Units	C _L (pF)
			T _A = 25°C			
			Typ	Limit		
V _{OLP}	Quiet Output Maximum Dynamic V _{OL}	3.3	0.3	0.5	V	50
V _{OLV}	Quiet Output Minimum Dynamic V _{OL}	3.3	−0.3	−0.5	V	50
V _{IHD}	Minimum High Level Dynamic Input Voltage	3.3	2.0		V	50
V _{ILD}	Maximum Low Level Dynamic Input Voltage	3.3	0.8		V	50

Note: Input t_r = t_f = 3 ns

AC Electrical Characteristics

Symbol	Parameter	V _{CC} (V)	74LVX14			74LVX14		Units	C _L (pF)
			T _A = + 25°C			T _A = − 40°C to + 85°C			
			Min	Typ	Max	Min	Max		
t _{PLH} , t _{PHL}	Propagation Delay Time	2.7	8.7	16.3		1.0	19.5	ns	15
			11.2	19.8		1.0	23.0		50
		3.3 ± 0.3	6.8	10.6		1.0	12.5		15
			9.3	14.1		1.0	16.0		50
t _{OSLH} , t _{OSHL}	Output to Output Skew (Note 1)	2.7		1.5		1.5	ns	50	

Note 1: Parameter guaranteed by design. t_{OSLH} = |t_{PLHm} − t_{PLHn}|, t_{OSHL} = |t_{PHLm} − t_{PHLn}|

Capacitance


Symbol	Parameter	74LVX14			74LVX14		Units
		T _A = +25°C			T _A = −40°C to +85°C		
		Min	Typ	Max	Min	Max	
C _{IN}	Input Capacitance		4	10		10	pF
C _{PD}	Power Dissipation Capacitance (Note 1)		21				pF

Note 1: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation: $I_{CC(opr.)} = \frac{C_{PD} \times V_{CC} \times f_{IN} + I_{CC}}{6 \text{ (per Gate)}}$


74LVX14 Ordering Information

The device number is used to form part of a simplified purchasing code where the package type and temperature range are defined as follows:




TL/F/11603-3

Physical Dimensions inches (millimeters) unless otherwise noted




14-Lead Molded Small Outline Package, JEDEC
Order Number 74LVX14M or 74LVX14MX
NS Package Number M14A

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



14-Lead Small Outline Package EIAJ (SJ)
Order Number 74LVX14SJ or 74LVX14SJX
NS Package Number M14D

Physical Dimensions millimeters (Continued)



LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation Americas
Tel: 1(800) 272-9959
Fax: 1(800) 737-7018
Email: support@nsc.com

<http://www.national.com>

National Semiconductor Europe
Fax: +49 (0) 180-530 85 86
Email: europe.support@nsc.com
Deutsch Tel: +49 (0) 180-530 85 85
English Tel: +49 (0) 180-532 78 32
Français Tel: +49 (0) 180-532 93 58
Italiano Tel: +49 (0) 180-534 16 80

National Semiconductor Southeast Asia
Fax: (852) 2376 3901
Email: sea.support@nsc.com

National Semiconductor Japan Ltd.
Tel: 81-3-5620-7561
Fax: 81-3-5620-6179