

10

9

8

7

6



5

4

3

2

19034



MATERIAL: COPPER
.031" NOM. THICKNESS
FINISH: ELECTRO-TIN PLATING

MWID= MAX. WIRE INSULATION DIA.

PART NUMBERS ARE FOR LOOSE PIECE TO ORDER PARTS ON TAPE ADD A "T" TO END OF PART NUMBER

MATERIAL NO.	ENGR NO.	WIRE RANGE AWG	DIAMETER "D"	MAX. "L"	±.01 "B"	MWID	MIN. I.D.				INSULATION
190340002	A-259X	22-18	.180	.950	.450	.145	.056				PVC
190340005	A-269X	22-18	.156	.890	.450	.145	.056				PVC
190340007	B-279X	16-14	.180	.950	.450	.175	.084				PVC
190340009	B-289X	16-14	.156	.890	.450	.175	.084				PVC

REMOVED TAPE PARTS

EC NO: 2005/04/27
DRWN: SHADECK
CHKDR: DEROSS
APPR: DEROSS
REV: 2005/05/04

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR	±---	±---

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY	DATE
EMF	07/30/93
CHECKED BY	DATE
JM	07/30/93
APPROVED BY	DATE
FP	07/30/93

MATERIAL NO.
SEE TABLE

SIZE
B

SCALE
5:1

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

INSULKRIMP
MALE BULLET SNAP PLUG

MOLEX INCORPORATED

DOCUMENT NO.
SD-19034-004

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

9

8

7

6

5

4

3

2

1