


EVEREADY 1235

C

SUPER HEAVY DUTY



Industry Standard Dimensions



Chemical System: Zinc-Manganese Dioxide (Zn/MnO₂)
(No Added Mercury or Cadmium)

Designation: ANSI-14D, IEC-R14

Battery Voltage: 1.5 Volts

Operating Temp: -18°C to 55°C (0°F to 130°F)

Average Weight: 45.0 grams (1.6 oz.)


Volume: 25 cubic centimeters (1.5 cubic inch)

Average Capacity: 3800 mAh to 0.8 volts
(Rated at 25 mA continuous at 21°C)


Cell: One No. 35 (size "C")

Jacket: Metal


TYPICAL TEMPERATURE EFFECT 3.9 ohm - 4 hours/day to 0.75 volts



CONSTANT RESISTANCE PERFORMANCE Typical Service



CONSTANT CURRENT DISCHARGE Typical Service



Important Notice





This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved

EVEREADY 1235

Industry Standard Tests (21° C)



Important Notice

This data sheet contains information specific to batteries manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright © Eveready Battery Co. - All rights reserved