samtec

E.L.P.™
EXTENDED LIFE PRODUCT
10 year Mixed Flowing Gas with 30µ" Gold
Call Samtec for maximum mated cycles


HTSW–115–05–L–Q

HTSW–116–11–G–S


TSW–209–09–F–S–RA

(2.54 mm) .100"

THROUGH-HOLE .025" SQ POST HEADER

Mates with:
SSW, SSQ, SSM, ESW, ESQ, BCS, BSW, CES, SLW, IDSD, IDSS, SMSD, SMSS

SPECIFICATIONS

For complete specifications see www.samtec.com?TSW or www.samtec.com?HTSW

Insulator Material:
TSW: Black Glass Filled Polyester
HTSW: Natural Liquid Crystal Polymer
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over 50µ" (1.27 µm) Ni
Operating Temp Range:
-55°C to +125°C with Gold
-55°C to +105°C with Tin
Voltage Rating:
550 VAC mated with SSW;
500 VAC mated with BCS or ESQ;
450 VAC -RA/-RE mated with BCS or SSM
400 VAC mated with CES
RoHS Compliant: Yes
Lead–Free Solderable:
HTSW: Yes
TSW: Wave Only

CURRENT RATING (PER PIN)						
TSW mated with						
ESW	SSW	SLW	SSQ	SSM	BCS	SNT
5.2 A	5.7 A	5.2 A	6.3 A	5.2 A	4.6 A	4.3 A
1 POSITION POWERED PER ROW						

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality

FILE NO. E111594
FILE NO: 090871_0_000

APPLICATIONS
BCS TSW
HORIZONTAL

ALSO AVAILABLE (MOQ Required)

- Other platings
  Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

TYPE STRIP

TSW = Standard Strip

HTSW = Hi-Temp Strip

PIN CENTERS

–1 = .100" (2.54 mm) Centers, All Positions Filled



–2 = .200" (5.08 mm) Centers, Every Other Position Filled



NO. PINS PER ROW

01 thru 50
= .100" (2.54 mm) Center Version

02 thru 25
= .200" (5.08 mm) Center Version

Straight Pin Versions



–S
–D
–T
–Q

Right Angle Versions



–S
–D
–T
–Q

Due to technical progress, all designs, specifications and components are subject to change without notice.



TSW–112–07–G–T

TSW–109–10–F–D–RA





HTSW–120–13–T–D



TSW–114–16–G–S–RE

TSW, HTSW SERIES

LEAD STYLE

PLATING OPTION

–F
= Gold flash on post, Matte Tin on tail

–L
= 10µ" (0.25 µm) Gold on post, Matte Tin on tail

–G
= 10µ" (0.25 µm) Gold on post, Gold flash on balance

–T
= Matte Tin

OTHER SOLUTIONS

- Elevated Right Angle option
- Shunts

Contact Samtec

ROW OPTION

–S
= Single Row

–D
= Double Row

–T
= Triple Row

–Q
= Double Row (5.08 mm) .200" row space

OTHER OPTIONS

– RA or –RE
= Right Angle

–NA
= Right Angle (using straight body for coplanar mating with SSW-RA series)



–LL
= Locking Lead

Two leads per strip crimped in opposite directions on or near centerline. See charts for available styles. N/A with single row 1 or 2 positions. Recommended hole size (1.02 mm ± 0.03 mm) .040" ± .001"

–LC
= Locking Clip (Styles –08 thru –13 & –22 only)



Requires 4 pin minimum (NA with -T,-Q,-RA or -RE)

–LA
= –RA Option with –LL Option

–"XXX"
= Polarized Position

Straight Pin Versions
(Specify "LEAD STYLE" from chart)

	STYLE	A	B	C
*	– 05	(3.30) .130	(8.51) .335	(2.67) .105
*	– 06	(2.41) .095	(7.62) .300	(2.67) .105
*	– 07	(2.54) .100	(10.92) .430	(5.84) .230
*	– 08	(5.08) .200	(13.46) .530	
	– 09	(10.16) .400	(18.54) .730	
	– 10	(12.70) .500	(21.08) .830	
	– 11	(15.24) .600	(23.62) .930	
	– 12	(17.78) .700	(26.16) 1.030	
	– 13	(22.86) .900	(31.24) 1.230	
	– 14	(2.79) .110	(13.46) .530	(8.13) .320
*	– 15		(18.54) .730	(13.21) .520
*	– 16	(7.87) .310		(8.13) .320
*	– 17	(2.79) .110	(21.08) .830	(15.74) .620

* Available with –LL (Locking Lead) Option

	STYLE	A	B	C
*	–18	(2.79) .110	(23.62) .930	(18.29) .720
*	–19		(26.16) 1.030	(20.83) .820
*	– 20		(31.24) 1.230	(25.91) 1.020
*	– 21		(36.32) 1.430	(30.99) 1.220
*	– 22	(7.62) .300	(16.00) .630	(5.84) .230
*	– 23	(2.92) .115	(11.30) .445	
*	– 24		(12.15) .480	(6.73) .265
*	– 25	(5.33) .210	(16.00) .630	(8.13) .320
▲	– 26	(3.20) .126	(11.58) .456	(5.84) .230
	– 27	(25.40) 1.000	(33.78) 1.330	
	– 28	(20.32) .800	(28.70) 1.130	
	– 29	(23.11) .910	(33.78) 1.330	(8.13) .320
	– 30	(18.03) .710	(28.70) 1.130	
+	– 41	(0.89) .035	(9.27) .365	(5.84) .230
+	– 42	(1.27) .050	(11.94) .470	(8.13) .320

\+ Style –41 & –42 available with HTSW only.

▲Except: Style –26 (0.46) .018 DIA Tail



Specify -07 for best mate with IDXX Series IDC Cable

Right Angle Versions
(Specify "LEAD STYLE" from chart and select –RA or –RE from other options)

–RA LEAD STYLE	SINGLE (–S) A	SINGLE (–S) C	DOUBLE (–D) A	TRIPLE (–T & –Q) A
– 08	(2.29) .090	(5.84) .230	(2.29) .090	(2.29) .090
– 09	(7.37) .290		(7.37) .290	(7.37) .290
–10	(9.91) .390		(9.91) .390	(9.91) .390
–11	(12.45) .490		(12.45) .490	(12.45) .490
–12	(14.99) .590		(14.99) .590	(14.99) .590
–13	(20.07) .790		(20.07) .790	N/A
* –16	(5.08) .200	(8.13) .320	(5.08) .200	(5.08) .200
– 21	(25.15) .990	(5.84) .230	N/A	N/A
* – 22	(4.83) .190		(4.83) .190	(4.83) .190
* – 25	(2.54) .100	(8.13) .320	(2.54) .100	(2.54) .100
– 27	(22.61) .890	(5.84) .230	N/A	N/A
– 28	(17.53) .690		(17.53) .690	
– 29	(20.32) .800	(8.13) .320	N/A	
– 30	(15.24) .600		(15.24) .600	

– RE LEAD STYLE	SINGLE A	C
– 09	(4.83) .190	(5.84) .230
–10	(7.37) .290	
–11	(9.91) .390	
–12	(12.45) .490	
–13	(17.53) .690	
–16	(2.54) .100	(8.13) .320
– 21	(22.61) .890	(5.84) .230
– 22	(2.29) .090	
– 27	(20.07) .790	
– 28	(14.99) .590	

*Available with –LA (Locking Lead) Option

LEAD STYLE	B
– RA	(1.52) .060
– RE	(4.06) .160



Due to technical progress, all designs, specifications and components are subject to change without notice.