



HONEYWELL PART NUMBER
1SM46-T
PRODUCT CODE TWA4660

REV	DOCUMENT	CHANGED BY	CHECK
12	0038442	SSK 31MAR08	BLR



- NOTES**
- 1- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX. DIA. ON .375 ±.002 CENTERS.
 - 2- TERMINALS ARE PLATED FOR SOLDERING.
 - 3- NORMALLY OPEN MATING CONTACT SURFACES ARE 24K SOLID GOLD OVERLAY

RELEASE NO.	-
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	VK	10 DEC 07	Honeywell			
OPERATING FORCE — — 3 - 5 OZ		CONTACT ARRANGEMENT SPDT					CHECK	RJ	10 DEC 07				
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .004 MAX													
		SEA LEVEL 50,000 FT											
		INDUCTIVE 1/2 AMP 1/2 AMP											
		RESISTIVE 1 AMP 1 AMP											
OVERTRAVEL — — — — — .005 MIN		MAXIMUM INRUSH 2 AMP			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
					RASTER				B	I	1SM46-T		12
									SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	