


LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			F2	REVISED PER ECO-11-002228	11FEB11	HMR DR



AMP WIRE RANGE	FILE E13288	LR7189 Certified
2/0 AWG STRANDED	2/0 AWG STRANDED	2/0 AWG STRANDED

- 1

STAMP AMP 2/0 W*, LOCATE APPROX AS SHOWN
- 2

TONGUE MATERIAL THK 2.03±0.08 [.080±.003]
- 3

WIRE INSULATION DIA 19.69 [.775] MAX
- 4

BODY: COPPER PER ASTM B-152
SLEEVE: PVC
- 5

BODY: TIN PLATED PER ASTM B-545
SLEEVE: COLOR-YELLOW

50	LOOSE PC	52046-1
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-28-93	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608		
	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK R. HERSEY 9-28-93			
	VOLTAGE RATING: 600 V MAX		APVD M ELLIS 9-28-93	NAME TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE: 2/0 AWG		
CIRCULAR MIL AREA: 60.55-76.26mm² [119,500-150,500] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	PRODUCT SPEC NOT AVAILABLE	SIZE A3 CAGE CODE 00779 DRAWING NO C-52046 RESTRICTED TO -		
		MATERIAL 4	APPLICATION SPEC 114-2161			
			WEIGHT -	CUSTOMER DRAWING		
				SCALE NTS	SHEET 1 OF 1	REV F2