

PLS-041B-3PPI

PLS-041B-3PPI

Standard Level Sensor




Electrical Characteristics		@ 25 °C
Contact form		B
Contact rating max.	W / VA	10
Switching voltage max.	VDC	200
	VAC	140
Switching current max.	A	1
Carry current max.	A	1.2
Breakdown voltage min.	VDC	240
Total resistance max.	mΩ	280

Environmental Characteristics		
Operating temperature	°C	-20 to +80
Storage temperature	°C	-30 to +80

Mechanical Characteristics		
Density of float typ.*	g / cm ³	0.7
Recommended minimum gravity of medium	g / cm ³	Density of float + 20%

* in delivery condition

Dimensions in mm



Features
➤ Polypropylene housing ➤ Suitable for food contact ➤ Covers a wide range of applications ➤ Customized types available

Approvals
RoHS REACH IP 67 CE

Ordering Information		
Packing Unit	10	pcs
Weight per piece	11	g
Weight per pacakge	118	g

PLS-041B-3PPI

PLS-041B-3PPI


Standard Level Sensor



Material Information

	Material	Colour
Housing	PP	white
Cable	UL 1007, AWG 24, 4 mm stripped and tinned	white
Nuts	PA66, M8 , 1 pc preassembled	white
Float	PP foam	white
Potting	PU / Epoxy	white
Sealing ring	Silicone	white

Operation View




Remarks

When mounted near ferromagnetic parts switching distance of PLS-041B-3 may vary.

Electromagnetical influences and magnetic fields may change the switching behaviour of the Level Sensor.

Mounting



When mounted stem up, operating functions are reversed.