





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C	REVISED PER 0G3A-0923-04	30NOV04	MF	DD


- 1 CONTINUOUS STRIP ON REELS.
- 2 WIRE RANGE: #12-#10 AWG,
INSULATION RANGE: .125-.220 DIA.



SECTION B-B



SECTION C-C

—		—		—	
—		—		—	
—		—		—	
.000080 MIN TIN PLATE		TEMP 2 COLD ROLLED STEEL		62612-2	
—		ANNEALED STAINLESS STEEL		62612-1	
FINISH		MATERIAL		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17NOV2004 MICHAEL S. FEHER		tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK 30NOV2004 DONALD F. DECKER			
		APVD 30NOV2004 DONALD F. DECKER			
		PRODUCT SPEC —			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RING, ANTIROTATIONAL, 8 STUD SIZE —	
		0 PLC ± -			
		1 PLC ± -			
		2 PLC ± -			
		3 PLC ± .010			
4 PLC ± -		APPLICATION SPEC —		SIZE A2	
MATERIAL SEE TABLE		WEIGHT —			
				DRAWING NO C=62612	
				RESTRICTED TO —	