




## Trench IGBT Modules

### SEMiX 202GB066HD

#### Target Data

#### Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient

#### Typical Applications

- Matrix Converter
- Resonant Inverter
- Current Source Inverter

#### Remarks

- Case temperatur limited to  $T_C=125^{\circ}\text{C}$  max.
- Product reliability results are valid for  $T_j=150^{\circ}\text{C}$
- SC data:  $t_p \leq 6 \mu\text{s}$ ;  $V_{GE} \leq 15 \text{ V}$ ;  $T_j = 150^{\circ}\text{C}$ ;  $V_{CC} = 360 \text{ V}$




| Absolute Maximum Ratings |                                                               | $T_{case} = 25^{\circ}\text{C}$ , unless otherwise specified |                    |
|--------------------------|---------------------------------------------------------------|--------------------------------------------------------------|--------------------|
| Symbol                   | Conditions                                                    | Values                                                       | Units              |
| <b>IGBT</b>              |                                                               |                                                              |                    |
| $V_{CES}$                |                                                               | 600                                                          | V                  |
| $I_C$                    | $T_c = 25 (80)^{\circ}\text{C}$ , $T_j = 150^{\circ}\text{C}$ | 240 (170)                                                    | A                  |
| $I_C$                    | $T_c = 25 (80)^{\circ}\text{C}$ , $T_j = 175^{\circ}\text{C}$ | 270 (200)                                                    | A                  |
| $I_{CRM}$                | $t_p = 1 \text{ ms}$                                          | 400                                                          | A                  |
| $V_{GES}$                |                                                               | $\pm 20$                                                     | V                  |
| $T_j, (T_{stg})$         |                                                               | $-40 \dots +175 (125)$                                       | $^{\circ}\text{C}$ |
| $V_{isol}$               | AC, 1 min.                                                    | 4000                                                         | V                  |
| <b>Inverse diode</b>     |                                                               |                                                              |                    |
| $I_F$                    | $T_c = 25 (80)^{\circ}\text{C}$ , $T_j = 150^{\circ}\text{C}$ | 190 (130)                                                    | A                  |
| $I_F$                    | $T_c = 25 (80)^{\circ}\text{C}$ , $T_j = 175^{\circ}\text{C}$ | 210 (160)                                                    | A                  |
| $I_{FRM}$                | $t_p = 1 \text{ ms}$                                          | 400                                                          | A                  |
| $I_{FSM}$                | $t_p = 10 \text{ ms}$ ; sin.; $T_j = 25^{\circ}\text{C}$      | 1000                                                         | A                  |

| Characteristics                |                                                                                                    | $T_{case} = 25^{\circ}\text{C}$ , unless otherwise specified |             |                    |
|--------------------------------|----------------------------------------------------------------------------------------------------|--------------------------------------------------------------|-------------|--------------------|
| Symbol                         | Conditions                                                                                         | min.                                                         | typ.        | max. Units         |
| <b>IGBT</b>                    |                                                                                                    |                                                              |             |                    |
| $V_{GE(th)}$                   | $V_{GE} = V_{CE}$ , $I_C = 6,4 \text{ mA}$                                                         |                                                              | 5,8         | V                  |
| $I_{CES}$                      | $V_{GE} = 0$ , $V_{CE} = V_{CES}$ , $T_j = 25 (^{\circ})^{\circ}\text{C}$                          |                                                              |             | 0,1 mA             |
| $V_{CE(TO)}$                   | $T_j = 25 (150)^{\circ}\text{C}$                                                                   |                                                              | 0,9 (0,85)  | 1 (0,9) V          |
| $r_{CE}$                       | $V_{GE} = 15 \text{ V}$ , $T_j = 25 (150)^{\circ}\text{C}$                                         |                                                              | 2,75 (4,25) | 4,5 (6) m $\Omega$ |
| $V_{CE(sat)}$                  | $I_C = 200 \text{ A}$ , $V_{GE} = 15 \text{ V}$ ,<br>$T_j = 25 (150)^{\circ}\text{C}$ , chip level |                                                              | 1,45 (1,7)  | 1,9 (2,1) V        |
| $C_{ies}$                      | under following conditions                                                                         |                                                              |             | nF                 |
| $C_{oes}$                      | $V_{GE} = 0$ , $V_{CE} = 25 \text{ V}$ , $f = 1 \text{ MHz}$                                       |                                                              |             | nF                 |
| $C_{res}$                      |                                                                                                    |                                                              |             | nF                 |
| $L_{CE}$                       |                                                                                                    |                                                              |             | nH                 |
| $R_{CC+EE'}$                   | terminal-chip, $T_c = 25 (125)^{\circ}\text{C}$                                                    |                                                              |             | m $\Omega$         |
| $t_{d(on)}/t_r$                | $V_{CC} = 300 \text{ V}$ , $I_C = 200 \text{ A}$                                                   |                                                              |             | ns                 |
| $t_{d(off)}/t_f$               | $V_{GE} = \pm 15 \text{ V}$                                                                        |                                                              |             | ns                 |
| $E_{on} (E_{off})$             | $R_{Gon} = R_{Goff} = 6 \Omega$ , $T_j = 150^{\circ}\text{C}$                                      |                                                              | 5 (9)       | mJ                 |
| <b>Inverse Diode</b>           |                                                                                                    |                                                              |             |                    |
| $V_F = V_{EC}$                 | $I_F = 200 \text{ A}$ ; $V_{GE} = 0 \text{ V}$ ; $T_j = 25 (150)^{\circ}\text{C}$ , chip level     |                                                              | 1,4 (1,4)   | 1,6 V              |
| $V_{(TO)}$                     | $T_j = 25 (150)^{\circ}\text{C}$                                                                   |                                                              | 1 (0,85)    | 1,1 V              |
| $r_T$                          | $T_j = 25 (150)^{\circ}\text{C}$                                                                   |                                                              | 2 (2,8)     | 2,6 m $\Omega$     |
| $I_{RRM}$                      | $I_F = 200 \text{ A}$ ; $T_j = 25 (150)^{\circ}\text{C}$                                           |                                                              |             | A                  |
| $Q_{rr}$                       | $di/dt = \text{A}/\mu\text{s}$                                                                     |                                                              |             | $\mu\text{C}$      |
| $E_{rr}$                       | $V_{GE} = -15 \text{ V}$                                                                           |                                                              |             | mJ                 |
| <b>Thermal characteristics</b> |                                                                                                    |                                                              |             |                    |
| $R_{th(j-c)}$                  | per IGBT                                                                                           |                                                              | 0,22        | K/W                |
| $R_{th(j-c)D}$                 | per Inverse Diode                                                                                  |                                                              | 0,4         | K/W                |
| $R_{th(j-c)FD}$                | per FWD                                                                                            |                                                              |             | K/W                |
| $R_{th(c-s)}$                  | per module                                                                                         |                                                              | 0,045       | K/W                |
| <b>Temperature sensor</b>      |                                                                                                    |                                                              |             |                    |
| $R_{25}$                       | $T_c = 25^{\circ}\text{C}$                                                                         |                                                              | $5 \pm 5\%$ | k $\Omega$         |
| $B_{25/85}$                    | $R_2 = R_1 \exp[B(1/T_2 - 1/T_1)]$ ; $T[K]$ ; B                                                    |                                                              | 3420        | K                  |
| <b>Mechanical data</b>         |                                                                                                    |                                                              |             |                    |
| $M_s/M_t$                      | to heatsink (M5) / for terminals (M6)                                                              | 3/2,5                                                        | 5 / 5       | Nm                 |
| w                              |                                                                                                    |                                                              | 250         | g                  |



Case SEMiX 2



This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.