


## Carbon Film Resistors

# General Type

## Normal & Miniature Style [ CFR Series ]



### INTRODUCTION


The CFR Series Carbon Film Resistors are manufactured by coating a homogeneous film of pure carbon on high grade ceramic rods. After a helical groove has been cut in the resistive layer, tinned connecting leads of electrolytic copper are welded to the end-caps. The resistors are coated with layers of tan color lacquer.

### FEATURES

Power Rating	1/6W, 1/4W, 1/2W, 1W, 2W, 3W
Resistance Tolerance	±2%, ±5%
T.C.R.	see Table I

### DERATING CURVE


For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with the curve below.



### TABLE I TEMPERATURE COEFFICIENT

STYLE	MAX. VALUE OF TEMP. COEFFICIENT PPM/°C		
	under 100K Ω	100K Ω - 1M Ω	1M Ω - 10M Ω
CFR100, CFR200, CFR2WS, CFR3WS	±350	-500	-1,500
CFR-12, CFR-25, CFR-50, CFR25S, CFR50S, CFR1WS	+350 / -500	-700	-1,500

### DIMENSIONS



Unit: mm

STYLE		DIMENSION			
Normal	Miniature	L	øD	H	ød
CFR-12	CFR25S	3.4±0.3	1.9±0.2	28±2.0	0.45±0.05
CFR-25	CFR50S	6.3±0.5	2.4±0.2	28±2.0	0.55±0.05
CFR-50	CFR1WS	9.0±0.5	3.3±0.3	26±2.0	0.55±0.05
CFR100	CFR2WS	11.5±1.0	4.5±0.5	35±2.0	0.8±0.05
CFR200	CFR3WS	15.5±1.0	5.0±0.5	33±2.0	0.8±0.05

Note:

### ELECTRICAL CHARACTERISTICS

STYLE	CFR-12	CFR25S	CFR-25	CFR50S	CFR-50	CFRIWS	CFRI00	CFR2WS	CFR200	CFR3WS
Power Rating at 70°C	1/6W	1/4W		1/2W		1W		2W		3W
Maximum Working Voltage	150V	200V	250V	300V	350V	400V	500V			
Maximum Overload Voltage	300V	400V	500V	600V	700V	800V	1,000V			
Voltage Proof	300V	400V	500V			700V	1,000V			
Resistance Range	1 Ω - 10M Ω & 0 Ω for E24 series value									
Operating Temp. Range	-55°C to +155°C									
Temperature Coefficient	see Table I									

Note: Special value is available on request

### ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 Sec.	±0.75%+0.05 Ω
Voltage Proof	IEC 60115-1 4.7	in V-block for 60 Sec., test voltage by type	By type
Temperature Coefficient	IEC 60115-1 4.8	-55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6	in V-block for 60 Sec.	>1,000M Ω
Solderability	IEC 60115-1 4.17	235±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05 Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±3.0%+0.05 Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV for 1,000 Hr. (1.5 Hr. on, 0.5 Hr. off)	±3.0%+0.05 Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇌ Room Temp. ⇌ +155°C ⇌ Room Temp. (5 cycles)	±1.0%+0.05 Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05 Ω

Note: Rated Continuous Working Voltage (RCWV) =  $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Yageo:

[CFR-25JR-52-100R](#) [CFR-25JR-52-110K](#) [CFR-25JR-52-33K](#) [CFR-25JR-52-47R](#) [CFR-12JR-52-220K](#) [CFR-12JR-52-390R](#) [CFR-12JR-52-470R](#) [CFR-12JR-52-47K](#) [CFR-12JR-52-620R](#) [CFR-25JR-52-15K](#) [CFR-25JR-52-1K2](#) [CFR-25JR-52-20K](#) [CFR-25JR-52-33R](#) [CFR-25JR-52-470K](#) [CFR-25JR-52-56K](#) [CFR-50JR-52-1K](#) [CFR-50JR-52-2K2](#) [CFR-50JR-52-470R](#) [CFR100JR-73-2K4](#) [CFR-25JR-52--200R](#) [CFR-25JR-52-1K](#) [CFR-50JR-52-220R](#) [CFR-25JR-52-1K5](#) [CFR-25JR-52-22R](#) [CFR-12JR-52-1M](#) [CFR-25JR-52-120K](#) [CFR-25JR-52-120R](#) [CFR-25JR-52-240R](#) [CFR-25JR-52-270R](#) [CFR-25JR-52-3K](#) [CFR-25JR-52-4R7](#) [CFR-25JR-52-510R](#) [CFR-25JR-52-56R](#) [CFR-25JR-52-680R](#) [CFR-25JR-52-68K](#) [CFR-25JR-52-6K8](#) [CFR-25JR-52-75R](#) [CFR-25JR-52-820R](#) [CFR-25JR-52-82R](#) [CFR-25JR-52-8K2](#) [CFR-25JR-52-91R](#) [CFR-50JR-52-100R](#) [CFR-50JR-52-10K](#) [CFR-50JR-52-120R](#) [CFR-50JR-52-3K9](#) [CFR-50JR-52-680R](#) [CFR-25JR-52-10M](#) [CFR-12JB-52-110K](#) [CFR-25JB-1K0](#) [CFR-50JR-52-270R](#) [CFR-25JR-52-2K2](#) [CFR-12JR-52-39K](#) [CFR-25JR-52-470R](#) [CFR-25JR-52-220R](#) [CFR-25JR-52-390R](#) [CFR-12JR-52-100K](#) [CFR-25JR-52-5K6](#) [CFR-25JR-52-22K](#) [CFR-25JR-52-47K](#) [CFR-25JR-52-100K](#) [CFR-12JR-52-120K](#) [CFR-25JR-52-220K](#) [CFR-25JR-52-620R](#) [CFR-12JR-52-1K](#) [CFR-25JR-52-1K8](#) [CFR-50JR-52-330R](#) [CFR-25JR-52-200K](#) [CFR-12JR-52-3K9](#) [CFR-25JR-52-10K](#) [CFR-25JR-52-2K7](#) [CFR-25JR-52-150K](#) [CFR-25JR-52-5K1](#) [CFR-25JR-52-2K](#) [CFR-25JR-52-3K3](#) [CFR-25JR-52-3K9](#) [CFR-12JR-52-4K7](#) [CFR-12JR-52-10K](#) [CFR-25JR-52-4K7](#) [CFR-25JR-52-330R](#)