

REV. D

DIMENSIONS ARE IN INCHES			UNLESS OTHERWISE NOTED	TOLERANCES ARE:		TITLE:	DWG NO:
ONE PLACE DECIMALS ±	THREE PLACE DECIMALS ±	.005	ANGLES	± 2°		LEAD SOCKET CARRIER STRIP	SCS-1XX-X-X
TWO PLACE DECIMALS ± .010	FOUR PLACE DECIMALS ±	.0020					
							SHEET 1 OF 1

SCS-1XX-X-XX


NO. OF POSITIONS
-01 THRU -50LEAD STYLE
SPECIFY LEAD STYLE
FROM TABLE 1

PLATING

- G: GOLD CONTACT, GOLD SHELL
(SPECIFY -GG IN SOCKET SUFFIX -XX)
- T: GOLD CONTACT, TIN SHELL
(SPECIFY -GT IN SOCKET SUFFIX -XX)
- S: LOW GOLD CONTACT, TIN SHELL
(SPECIFY -ST IN SOCKET SUFFIX -XX)
- TT: TIN CONTACT, TIN SHELL
(SPECIFY -TT IN SOCKET SUFFIX -XX)

TABLE 1

STYLE	LEAD SOCKET
-1A	SC-1W1-XX-2
-1B	SC-1W1-XX-1
-1C	SC-1W1-XX-3
-2	SC-1P1-XX
-3	SC-1S1-XX
-4	SC-2S1-XX
-5A	SC-2P1-XX
-7	SC-1P3-XX
-8	SC-2P3-XX
-9	SC-2P2-XX
-10	SC-3P1-XX
-11	SC-4P1-XX
-12	SC-5P1-XX
-14	SC-1M1-XX
-15	SC-1M2-XX
-18	SC-6P1-XX
-19	SC-8P1-XX
-21A	EZ-1W1-XX-2
-21B	EZ-1W1-XX-1
-21C	EZ-1W1-XX-3
-22	EZ-1P1-XX
-23	EZ-1S1-XX
-28	EZ-2P3-XX
-29	EZ-2P2-XX
-30	EZ-3P1-XX
-31	EZ-4P1-XX
-32	EZ-5P1-XX
-34	EZ-1M1-XX
-35	EZ-1M2-XX
-38	EZ-6P1-XX
-39	EZ-8P1-XX
-41	SP-101-XX



NOTE:

1. CARRIER (T-1SS2) TO BE FULLY INSERTED INTO LEAD SOCKETS. INSERTION DEPTH WILL VARY FOR THE DIFFERENT LEAD STYLES.

Do not scale
from this print

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL,
INCLUDING PHOTOCOPYING, RECORDING,
OR BY ANY INFORMATION STORAGE
AND RETRIEVAL SYSTEM, WITHOUT THE
WRITTEN CONSENT OF SAMTEC INC.

PLOT SCALE 1 = .166

MATERIAL:

T-1SS2
BRASS, 1/2 HARD

LEAD SOCKET

SHELL: BRASS 1/2 HARD
CONTACT: BeCu, ALLOY 172H

samtecMISC\MKTG
SCS-MKT

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: TY 7-28-82

SCS-1XX-X-X

SHEET 1 OF 1