



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FX	00		C1	REVISED PER ECO-11-005030	11MAR11	RK	HMR



638187-2 REELED LEFT TO RIGHT, OFF TOP, CARRIER INSIDE									638187-4
638187-1 REELED LEFT TO RIGHT, OFF TOP, CARRIER INSIDE									638187-3
1.6	1.80	2.04	1.45	0.90	2.40	2.30	0.35	22	638187-2
1.6	1.80	2.04	1.45	0.90	2.40	2.30	0.34-0.36		
1.7	2.46	2.75	1.30	1.20	2.90	3.00	0.50	18-20	638187-1
1.7	2.46	2.75	1.30	1.20	2.90	3.00	0.75		
1.7	2.46	2.75	1.30	1.20	2.90	3.00	1.00		
1.7	2.46	2.75	1.30	1.20	2.90	3.00	--		
H	F	E	D	C	B	A	METRIC WIRE SIZE	AWG	PART NUMBER

1 MATERIAL: 0.25 THK COPPER ALLOY, PRE-PLATED WITH 0.0008 MIN THK BRIGHT TIN.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J MCNEAL 04-09-98		 TE Connectivity							
				CHK C PAUL 04-09-98									
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD C PAUL 04-09-98		NAME RECEPTACLE CONTACT, DUAL BEAM							
		0 PLC ± -		PRODUCT SPEC									
		1 PLC ± 0.2		—									
		2 PLC ± 0.1		APPLICATION SPEC		SIZE A2		CAGE CODE 00779		DRAWING NO C-638187		RESTRICTED TO —	
		3 PLC ± -											
		4 PLC ± -											
		ANGLES ± 5°											
MATERIAL		FINISH		WEIGHT —									
		—		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1		REV C1			