

# Screwdrivers

## Screwdrivers

Introduction – Screwdrivers	F.2
Introduction – Electric screwdrivers	F.4
Rechargeable torque screwdriver	F.5
Bits	F.6
Introduction – Torque screwdrivers	F.8
Uninsulated torque screwdriver	F.9
VDE-insulated torque screwdriver	F.10
Special tools SAI	F.12
Cable gland tools	F.14
Combined cutting and screw driving tool	F.15
Introduction – Screwdrivers	F.16
VDE insulated screwdriver	F.17
Uninsulated screwdriver	F.19
Weidmüller wrench set	F.21
Pin and electrical cabinet key	F.22

# Screwdrivers

Precisely the proper torque! It's indispensable when you require your work to be precise, effective and repeatable: for example when screwing in sensitive or expensive components, during assembly, final testing, or during quality inspection. This is the perfect job for Weidmüller's manual torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

The Weidmüller screwdriver assortment is the perfect solution; it features the ergonomic design and versatility required for demanding professional applications. Weidmüller safeguards your safety, health, comfort and efficiency with our ergonomic design.


F

In order to establish secure manual screw connections, all Weidmüller screwdrivers and manual torque screwdrivers feature a special handle geometry, slip protection, and a special SoftFinish® zone. These qualities enable optimal handling and ensure electrical safety and hand protection during even the most critical applications.

Weidmüller offers a wide variety of electric screwdrivers, standard bits and innovative quick-change holders – the perfect additions to the manual torque screwdriver. Weidmüller electric screwdrivers are the ideal tool for achieving a high level of repetitive accuracy. This accuracy is made possible by their ergonomic design and standard integrated automatic torque control.

Weidmüller also offers innovative solutions for special applications such as cable glands or the fastening of sensor cables.





# Electric screwdrivers

F



Crimped conductors can be fastened in their corresponding connecting spaces either by the direct plug-in technique or by means of screws.

## Electric screwdrivers / Weidmüller bits

Weidmüller **screwdrivers** are ideal one-hand tools due to their ergonomic design. They guarantee fatigue-free working in any installation direction. They also have an automatic torque limit and high repetition accuracy.

The Weidmüller **bits** are standard bits with high quality, wide range and top-rate performance. Weidmüller uses processor-controlled hardening processes to guarantee consistently high product quality.

The high-grade material enables torques far above those stipulated in the relevant DIN standards:

- DIN 5261 for PH/PZ bits
- DIN 5263 for slotted bits
- Camcar standard for TORX bits

This means long service life at high torques, producing ideal conditions for standard work.



## Product benefits

- Suitable for all screw driving tasks  
Ideal for both manual and machine screw driving tasks due to the high hardness values of 59 – 61 HRC
- Good wear resistance and therefore a long service life
- Optimum fit in DIN screws for low wear and optimum torque transmission
- Manufactured with consistently high product quality based on the relevant ISO standards

## Rechargeable torque screwdriver

## DMS 3



## DMS 3 Set



## DMS 3 rechargeable torque screwdriver

- One-hand operation under all working conditions
- Switchable forward and reverse
- Two speeds: 200 and 400 rpm
- Precise torque settings from approx. 0.3 ... 3 Nm in 6 steps
- Consistent performance during battery discharge
- Grip swings easily from rod to pistol form
- Takes 1/4" bits held ball-bearing clamping mechanism (form E6.3)
- Safety lock prevents inadvertent operation
- Easy changeover from battery drive to manual operation up to 15 Nm

## Technical data

## Screwdriver

Motor	2.4 V DC
Idling speed	200/400 rpm
Max. torque	3.0 Nm
Chuck	1/4" E 6.3 DIN 3126
Length	239 mm
Weight	400 g

## Battery

Type	2 Ni-Cd batteries each 1.2 V
Weight	122 g

## Charger

Input	230 V AC, 50 Hz, 50 mA
Output	2.9 V AC, 1.4 A, 4.1 VA
Charging time	1 hour
Weight	700 g

## Ordering data

Type	Qty.	Order No.
DMS 3	1	9007440000
Screwdriver incl. battery		

Type	Qty.	Order No.
DMS 3 set 1 (screwdriver incl. battery, charger, bits, plastic carrying case)	1	9007470000
DMS 3 set 2 (as set 1 with 1 additional battery)	1	9007480000

\*) see picture


## Accessories

Type	Qty.	Order No.
Spare battery	1	9007450000
Charger	1	9007460000

## Bits


## Bits drive 1/4" E6.3

1/4" hexagon drive, acc. to DIN 3126,  
Shape E6.3 for direct machine connection



## Bit E6.3 S

Slotted bits DIN 5264,  
1/4" drive E6.3 DIN 3126




Type	Size / AF	a	b	c	Order No.
BIT E6.3 0,4x2,5x70		0.4	2.0	70	9202750000
BIT E6.3 0,5x3,0x70		0.5	3.0	70	9024000000
BIT E6.3 0,5X3,0X110		0.5	3.0	110	9205600000
BIT E6.3 0,6x3,5x70		0.6	3.5	70	9024020000
BIT E6.3 0,6X3,5X110		0.6	3.5	110	9205610000
BIT E6.3 0,8X4,0X110		0.8	4.0	110	9205620000
BIT E6.3 0,8x4,0x70		0.8	4.0	70	9024030000
BIT E6.3 0,8X4,5X110		0.8	4.5	110	9205630000
BIT E6.3 1,0x5,5x70		1.0	5.5	70	9024040000
BIT E6.3 1,0X5,5X110		1.0	5.5	110	9205640000
BIT E6.3 1,2x6,5x70		1.2	6.5	70	9202740000
BIT E6.3 1,2X6,5X110		1.2	6.5	110	9205650000

## F

## Bit E6.3 PH

Crosshead bits, Phillips-recess type PH/DIN 5260.  
1/4" drive E6.3 DIN 3126


BIT E6.3 PH1x70	1	70	9024080000
BIT E6.3 PH2x70	2	70	9024090000



## Bit E6.3 PZ

Crosshead bits, Pozidrive type PZ/DIN 5262,  
1/4" drive E 6.3 DIN 3126


BIT E6.3 PZ1x70	1	70	9024100000
BIT E6.3 PZ2x70	2	70	9024110000



## Bit E6.3 Z


Slotted bits with peg DIN 5264,  
1/4" drive E6.3 DIN 3126

BIT E6.3Z 0,6X3,5X70	0.6	3.5	70	9205670000
BIT E6.3Z 0,8X4,0X70	0.8	4.0	70	9205660000



### Bits drive 1/4" E6.3

1/4" hexagon drive, acc. to DIN 3126,  
Shape C6.3 for direct machine connection  
(DMS2 1/4" C6.3)



### Bit-Box DMS3

Weidmüller Bit Box, 9-piece with universal holder  
drive: 1/4" E6.3 DIN 3126; output: 1/4" E6.3; bits: 1/4" C6.3



Type	Size / AF	a	b	c	Order No.
UBH 1/4" E6.3					
BIT C6,3 0,5x4,0x25		0.5	4.0	25	
BIT C6,3 0,6x4,5x25		0.6	4.5	25	
BIT C6,3 PH0x25	0			25	
BIT C6,3 PH1x25	1			25	
BIT C6,3 PH2x25	2			25	
BIT C6,3 PZ0x25	0			25	
BIT C6,3 PZ1x25	1			25	
BIT C6,3 PZ2x25	2			25	
Bit-Box WI DMS 3					25 9024970000

### UBH 1/4 E6.3

Short universal bit holder, magnetic  
drive: 1/4" E6.3 DIN 3126, output: 1/4" E6.3



UBH 1/4 E6.3

9009520000

F

### UBH SWH 1/4 EC 6.3

Universal quick-change holder with locking function. True one-hand  
operation for quick bit changes Drive: 1/4" E6.3 DIN 3126, output:  
1/4" E6.3 + C6.3 double bits



UBH SWH 1/4 EC 6.3

9205680000

### BHS 1/4

The bit holder has a flexible shaft intended for angled screws.  
For all 1/4" -drive bits C6.3 DIN 3126 with SoftFinish grip.



BHS 1/4

9009630000

# DMS manual / DMSI manual

## Torque screwdrivers with insulation up to 1000 V (VDE)

### DMSI manual

The “DMSI manual” with integral window scale combined with a Weidmüller 1000 V insulated (VDE) interchangeable blade ensures controlled tightening of screws plus reliability in electrical applications.


Every 1000 V insulated handle (VDE) and blade (VDE) is tested and provides the necessary safety up to 1000 V AC/1500 V DC.

F

### Torque screwdrivers

#### DMSI manual

This is a versatile tool suitable for a variety of jobs, with integral scale for easy reading of the torque value plus a Weidmüller interchangeable blade.



#### Each model is available with two torque ranges:


- 0.5 to 1.7 Nm
- 2.0 to 8.0 Nm
- setting tool included

#### Advantages:

- Compact and especially lightweight design
- Torque set with special tool (included) to ensure the right setting
- Ergonomic handle size to match the torque range
- Every tool checked and given an ID No., 100% quality control with verification and product reference
- Audible, unmistakable click upon reaching the torque, no unnecessary effort
- Interchangeable blade made from high-quality wear-resistant tool steel
- All tools comply with the accuracy stipulations of:  
EN ISO 6798, BS EN 26789, ASME B107.14M
- Operating accuracy:  $\pm 6\%$  of set scale value

## Uninsulated torque screwdriver

## Uninsulated torque screwdriver



## DMS manual

Torque screwdriver  
EN ISO 6798, BS EN 26789, ASME B107.14M



## WK K S

Interchangeable bits for torque screwdriver  
output acc. to DIN 5264, ISO 2380/1



## WK K PZ

Interchangeable bits for torque screwdriver  
output acc. to DIN 5260-PZ, ISO 8764/1-PZ



## WK K PH

Interchangeable bits for torque screwdriver  
output acc. to DIN 5260-PH, ISO 8764/1-PH



## WGK 1/4" C6.3 E6.3

Interchangeable bit with bit holder for torque screwdrivers  
Drive: 1/4" C6.3 and 1/4" E6.3



Type	Size / AF	a	b	c	Order No.
------	-----------	---	---	---	-----------

DMS MANUAL 0.5-1.7	0.5 - 1.7 Nm				9918370000
DMS MANUAL 2.0-8.0	2.0 - 8.0 Nm				9918380000

WK S 0,4x2,5	max. 0.4 Nm	0.4	2,5	175	9918520000
WK S 0,5x3,0	Max. 0.6 Nm	0.5	3,0	175	9918530000
WK S 0,6x3,5	Max. 1.1 Nm	0.6	3,5	175	9918540000
WK S 0,8x4,0	Max. 2,5 Nm	0.8	4,0	175	9918550000
WK S 1,0x5,5	Max. 3,8 Nm	1,0	5,5	175	9918560000


WK K PZ0	Max. 9 Nm	175	9918600000
WK K PZ1	Max. 3,8 Nm	175	9918610000
WK K PZ2	Max. 5,5 Nm	175	9918620000

WK K PH0	Max. 9 Nm	175	9918570000
WK K PH1	Max. 3,8 Nm	175	9918580000
WK K PH2	Max. 5,5 Nm	175	9918590000

WK 1/4" C6,3 E6,3			9202510000
-------------------	--	--	------------

## VDE-insulated torque screwdriver

## VDE-insulated torque screwdriver



## DMSI manual

## VDE-insulated torque screwdriver

EN ISO 6798, BS EN 26789, ASME B107.14M



Type	Size / AF	a	b	c	Order No.
DMSI MANUAL 0.5-1.7	0.5 - 1.7 Nm				9918390000
DMSI MANUAL 2.0-8.0	2.0 - 8.0 Nm				9918400000

## WK SI

## VDE-insulated interchangeable bits for VDE-insulated torque screwdriver; output acc. to DIN 5264, ISO 2380/1



WK SI 0,4x2,5	max. 0.4 Nm	0.4	2,5	220	9918410000
WK SI 0,5x3,0	Max. 0.6 Nm	0.5	3,0	220	9918420000
WK SI 0,6x3,5	Max. 1.1 Nm	0.6	3,5	220	9918430000
WK SI 0,8x4,0	Max. 2,5 Nm	0.8	4,0	220	9918440000
WK SI 1,0x5,5	Max. 3,8 Nm	1,0	5,5	220	9918450000

## WK IK PH

## VDE-insulated interchangeable bits for VDE-insulated torque screwdriver; output acc. to DIN 5260-PH, ISO 8764/1-PH



WK IK PH0	Max. 9 Nm	220	9918460000
WK IK PH1	Max. 3.8 Nm	220	9918470000
WK IK PH2	Max. 5.5 Nm	220	9918480000

## WK IK PZ

## VDE-insulated interchangeable bits for VDE-insulated torque screwdriver; output acc. to DIN 5260-PZ, ISO 8764/1-PZ



WK IK PZ0	Max. 9 Nm	220	9918490000
WK IK PZ1	Max. 3.8 Nm	220	9918500000
WK IK PZ2	Max. 5.5 Nm	220	9918510000



## Special tools SAI

**The Torque Screwty**

- Easier work
- Screw-on circular plug, safety sealed

**The perfect tool for all situations**

Screwty is the ideal, universal tool for tightening and releasing cable glands on all common sensor and actuator cables. The Screwty can also reach those round plugs normally considered inaccessible! No great force is required – simply turn the tool to tighten or release the plug-in connector as required.

The Screwty also fits the majority (more than 90 %) of the cables and plug-in connectors of other suppliers and is therefore a unique tool useful throughout the world. The Screwty consists of a handle with a conventional 1/4" fitting. This means it can be used for all sizes: for M12 and M8 round plugs, and the M12F and M8F types, also for plugs and sockets on custom cables.

The Screwty is suitable for the following round plugs:

Size	M8	M8F	M12	M12F
	10 ±0.3 mm	11.9 ±0.3 mm	14.5 ±0.3 mm	19.8 ±0.3 mm
Thread	M8x1	M8x1	M12x1	M12x1



**Simply turn the ratchet to tighten or loosen the cable gland.**

An adjustable torque fitting is also available for the Screwty – for guaranteeing extra reliability during installation.

The torque can be infinitely adjusted between 0.5 and 1.7 Nm. This accurate setting enables all round plugs to be tightened precisely with a certain torque.

Weidmüller specifies the following torques for its round plugs:

Size	M8	M8F	M12	M12F
Torque	0.5-0.6 Nm	0.5-0.6 Nm	0.8-1.2 Nm	0.8-1.2 Nm
Thread	M8x1	M8x1	M12x1	M12x1

The Screwty can also be fitted with other blades to create a torque screwdriver.



**Use of a M12 Screwty**

1. Position Screwty,
2. tighten connector,
3. finished!



**Use of a M23 Screwty**

**Screwy standard****Ordering data**

Type	Use	Qty.	Order No.
Screwy M12	moulded M12 lines	1	1900000000
Screwy M8	moulded M8 lines	1	1900010000
Screwy M12 F	M12 plugs for custom assembly	1	1900020000
Screwy M8 F	M8 plugs for custom assembly	1	1900030000

**Screwy Set****Ordering data**

Type	Qty.	Order No.
Screwy Set	1	1910000000
<b>Fittings</b>		
Type	Contents	
Screwy Set	1 Screwy standard handle + 1 M12, M8, M12 F, M8 F attachments	

**Screwy attachments****Ordering data**

Type	Qty.	Order No.
Screwy® M12 KO o. SD	1	1900100000
Screwy® M8 KO o. SD	1	1900110000
Screwy® M12F KO o. SD	1	1900120000
Screwy® M8F KO o. SD	1	1900130000
Screwy® M23 LS	1	1981560000

**Legend:**

F	for custom assemblies
DM	torque
KO or SD	ratchet only (attachment)
Screwy	screwdriver
Screwy DM	torque screwdriver, interchangeable blade
WK	interchangeable blade
LS	power plug

**Screwy with torque fitting**

Setting aid for Screwy with torque fitting (included)

**Ordering data**

Type	Use	Qty.	Order No.
Screwy-M12-DM	moulded M12 lines with torque requirement	1	1900001000
Screwy-M8-DM	moulded M8 lines with torque requirement	1	1900011000
Screwy-M12 F-DM	M12 plugs, custom assembly w. torque requirement	1	1900021000
Screwy-M8 F-DM	M8 plugs, custom assembly with torque requirement	1	1900031000

**Fittings**

Type	Contents
Screwy-M12-DM	1 interchangeable blade, 1 torque handle, 1 setting aid for Screwy torque, 1 Screwy M12 attachment
Screwy-M8-DM	1 interchangeable blade, 1 torque handle, 1 setting aid for Screwy torque, 1 Screwy M18 attachment
Screwy-M12 F-DM	1 interchangeable blade, 1 torque handle, 1 setting aid for Screwy torque, 1 Screwy M12 F attachment
Screwy-M8 F-DM	1 interchangeable blade, 1 torque handle, 1 setting aid for Screwy torque, 1 Screwy M18 F attachment

**Screwy Set-DM****Ordering data**

Type	Qty.	Order No.
Screwy Set-DM	1	1920000000
<b>Fittings</b>		
Type	Contents	
Screwy Set-DM	1 interchangeable blade, 1 torque handle, 1 setting aid for Screwy torque, 1 each of Screwy M12, M8, M12 F, M8 F attachments	

**Screwy interchangeable handle/interchangeable bit****Ordering data**

Type	Use	Qty.	Order No.
1/4" handle		1	4294820000
WK-1/4" (Screwy)		1	1862200000

## Cable gland tools

### Cable gland tools

Tightening tool for all types of cable glands

- Can tighten or loosen several rows of cable glands
- No deforming of the cable glands

### FleCaFix 11/24

Cable gland tool



- Spanner size: 11 to 24 AF
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

### FleCaFix 24/36

Cable gland tool



- Spanner size: 24 to 36 AF
- Infinite adjustment of spanner size
- Ratchet function: not necessary to remove tool between turns
- Authentic one-hand tool

F



### Technical data

#### Tool data

Length / Width / Height	mm	190 / 30 / 60
Weight	g	190
Distance across flats (AF)	mm	11.0...24.0

#### Note

204 / 30 / 60
240
24.0...36.0

### Ordering data

#### Version

Type	Qty	Order No.
FLECAFIX 11/24	1	9015900000

Type	Qty	Order No.
FLECAFIX 24/36	1	9015980000

#### Note

## Combined cutting and screw driving tool

That does not damage the edge; for cutting of copper cables.

- Solid cables with a diameter of up to 1.5 mm<sup>2</sup>
- Flexible cables with a diameter of up to 2.5 mm<sup>2</sup>

### swifty®



### swifty®set



#### swifty®

- Cable cutting tool to mount on non-insulated screw drivers with a blade diameter of 3.5 mm
- Minimum manual force required
- Automatic opening of the cutter
- Ergonomically designed grip

#### swifty®set

- Efficient operation:
- Only one tool for cable-processing in IDC-technology
- Suitable for screw and tension clamps
- Readily available pocket size
- For right-handed and left-handed use
- One-hand operation

## Technical data

### Maximum cutting capacity

#### Copper cable:

Solid cable (conductor cross-section)	mm <sup>2</sup>	1.5
Flexible cable (conductor cross-section)	mm <sup>2</sup>	2.5

### Tool data

Length x width x height	mm	35 / 18 / 40
Weight	g	20

## Ordering data

Type	Qty.	Order No.
swifty® (without screwdriver)	1	9006020000

Type	Qty.	Order No.
swifty®set (with screwdriver)	1	9006060000
Screwdriver (SD 0.6x3.5x100)	1	9008330000

# Screwdrivers

Weidmüller screwdrivers come in four different grip sizes, and are the result of a consistent grip concept which takes into account both the human hand and the different requirements when working.

- Perfect handling with all grip sizes
- Maximum torques
- Optimum transmission of axial force
- Complete range including all commercial sizes

F



## SoftFinish grip



Weidmüller's SoftFinish grip zone for use in dry conditions and for general applications offers customers a complete range of screwdrivers that enables far higher torques as well as substantially more comfort due to the soft material of the grip.

### Product benefits:

- Made of special soft material which is kind to the skin, the SoftFinish zone enables maximum torques
- Perfect ergonomic grip design for comfortable screw driving and optimum handling
- You can choose from long-life extremely stressable blades in standard sizes
- ChromTop blade tip offers maximum corrosion protection and greatest possible dimensional accuracy of the blade geometry in the screw head over many years

## SoftFinish electric




VDE-insulated screwdriver according to DIN EN 60900, IEC 900 for work on live equipment

### Product benefits:

- The protective insulation moulded directly on the screwdriver blade ensures electrical safety, even in critical applications
- Safe for working at up to 1500 volts DC and 1000 volts AC
- Each screwdriver is individually tested in a water bath at 10,000 volts according to DIN EN 60900
- Perfect ergonomic grip design for comfortable screw driving and optimum handling
- Made of special soft material which is kind to the skin, the SoftFinish zone prevents slipping in critical situations and at the same time enables maximum torques

**VDE-insulated screwdriver**

VDE-insulated screwdriver, for working on live parts up to 1000 VAC and 1500 VDC. DIN EN 60900, IEC 900, Safety tested „GS“, each piece tested. Bit made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**SDI S**

**VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip**



Type	Blade type	Size / AF	a	b	c	Order No.
SDI 0.4X2.0X60	A	0.4	2.0	60	9205690000	
SDI 0.4x2.5x75	A	0.4	2.5	75	9008370000	
SDI 0.5x3.0x100	B	0.5	3.0	100	9008380000	
SDI 0.6x3.5x100	B	0.6	3.5	100	9008390000	
SDI 0.8x4.0x100	B	0.8	4.0	100	9008400000	
SDI 1.0x4.5x125	B	1.0	4.5	125	9008910000	
SDI 1.0X4.5X175	B	1.0	4.5	175	9205700000	
SDI 1.0x5.5x125	B	1.0	5.5	125	9008410000	
SDI 1.0X5.5X175	B	1.0	5.5	175	9205710000	
SDI 1.2x6.5x150	B	1.2	6.5	150	9008420000	
SDI 1,6x8,0x175	B	1.6	8.0	175	9008430000	

**SDIK PH**

**VDE-insulated crosshead screwdriver, Phillips type, SDIK PH DIN 7438, ISO 8764/2-PH, output acc. to ISO 8764-PH, SoftFinish grip**



SDIK PH0	0	60	9008560000
SDIK PH1	1	80	9008570000
SDIK PH2	2	100	9008580000
SDIK PH3	3	150	9008590000

**SDIK PZ**

**VDE-insulated crosshead screwdriver Pozidrive type, SDIK PZ DIN 7438, ISO 8764/2-PZ, output acc. to ISO 8764-PZ, SoftFinish grip**



SDIK PZ1	1	80	9008900000
SDIK PZ2	2	100	9008890000

VDE-insulated screwdriver with pilot tip, for working on live parts up to 1000 VAC and 1500 VDC, DIN EN 60900, IEC 900, Safety tested „GS“, each piece tested. Bit made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**SDIZ**


**VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip**



SDIZ 0.6X3.5X100	0.6	3.5	100	9008450000
SDIZ 0.8X4.0X100	0.8	4.0	100	9008460000
SDIZ 0.8X5.5 150/248				9008640000

**VDE-insulated screwdriver****VDE-insulated screwdriver**

VDE-insulated screwdriver with pilot tip, for working on live parts up to 1000 VAC and 1500 VDC, DIN EN 60900, IEC 900, Safety tested „GS“, each piece tested. Bit made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**SDIS 2.5-5.5/PH/1/2****6-part set: VDE insulated slotted and crosshead PH screwdriver set**

Type	Blade type	Size / AF	a	b	c	Order No.
SDI 0,4x2,5x75			0.4	2.5	80	
SDI 0,5x3,0x100			0.5	3.0	100	
SDI 0,8x4,0x100			0.8	4.0	100	
SDI 1,0x5,5x125			1.0	5.5	125	
SDI PH 1		1			80	
SDI PH 2		2			100	
SDIS 2,5-5,5/PH1/2						9009730000

F

**SDIS 2.5-5.5/PZ/1/2****Six-piece set: VDE-insulated slotted and PZ-crosshead screwdriver set**

SDI 0,4x2,5x75	A	0.4	2.5	80	
SDI 0,5x3,0x100	B	0.5	3.0	100	
SDI 0,8x4,0x100	B	0.8	4.0	100	
SDI 1,0x5,5x125	B	1.0	5.5	125	
SDI PZ 1		1		80	
SDI PZ 2		2		100	
SDIS 2,5-5,5/PZ1/2					1128540000

Weidmüller SoftFinish VDE-insulated electric screwdriver for working on live components with up to 1000 V AC and 1500 V DC, DIN EN 60900, IEC 900. Safety tested „GS“; each product tested.


**SDIS 2.0-5.5****VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip**

SDI 0,4x2,0x60	A	0.4	2.0	60	
SDI 0,4x2,5x75	A	0.4	2.5	75	
SDI 0,5x3,0x100	B	0.5	3.0	100	
SDI 0,6x3,5x100	B	0.6	3.5	100	
SDI 0,8x4,0x100	B	0.8	4.0	100	
SDI 1,0x5,5x125	B	1.0	5.5	125	
SDIS 2.0-5.5					9205550000

**Uninsulated screwdriver**

Weidmüller SoftFinish screwdriver for general uses, blade made from fully hardened.

High-alloy chromium-vanadium-molybdenum steel, matt chrome finish.

**SD S**

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip



Type	Blade type	Size / AF	a	b	c	Order No.
SD 0,4x2,0x60	B	0.4	2.0	60		9037160000
SD 0,4x2,5x75	A	0.4	2.5	75		9009030000
SD 0,5x3,0x80	A	0.5	3.0	80		9008320000
SD 0,6x3,5x100	A	0.6	3.5	100		9008330000
SD 0,6x3,5x200	A	0.6	3.5	200		9010110000
SD 0,8x4,0x100	A	0.8	4.0	100		9008340000
SD 0,8x4,5x125	A	0.8	4.5	125		9009020000
SD 1,0x5,5x150	A	1.0	5.5	150		9008350000
SD 1,2x6,5x150	A	1.2	6.5	150		9009010000

**SDK PH**

Crosshead screwdriver, Phillips, SDK PH DIN 5262, ISO 8764/2-PH, output to ISO 8764-PH, ChromTop tip, SoftFinish grip



SDK PH0	0	60	9008470000
SDK PH1	1	80	9008480000
SDK PH2	2	100	9008490000
SDK PH3	3	150	9008500000

**SDK PZ**

Crosshead screwdriver, Pozidriv, SDK PZ DIN 5262, ISO 8764/2-PZ, output to ISO 8764/1-PZ, ChromTop tip, SoftFinish grip



SDK PZ0	0	60	9008520000
SDK PZ1	1	80	9008530000
SDK PZ2	2	100	9008540000
SDK PZ3	3	150	9008550000

**SD TH**

Torx® TH screwdriver with hole in tip of blade (tamper-resistant), SD TH for screwing Torx® and Torx®-TH security screws (pin in centre of Torx recess), chrome top tip, SoftFinish grip. The SD TH20 can be used with the Klippon K housing series.



SD TH20	20	100	9009160000
---------	----	-----	------------

**SK**

The SK 10.0x125 Allen key, SK DIN 3125, drive output acc. to DIN 475/2, SoftFinish grip. It can be used with all sizes from the Klippon TB and Klippon STB housing series.




SK 10,0x125	10	125	9009070000
-------------	----	-----	------------

## Uninsulated screwdriver

### Uninsulated screwdriver

Weidmüller SoftFinish screwdriver for general uses, blade made from fully hardened.

High-alloy chromium-vanadium-molybdenum steel, matt chrome finish.



### Set S 2.5/3.0/4.0/5.5/PH 1/2

6-part set: slotted and crosshead PH screwdriver set with circular blades



Type	Blade type	Size / AF	a	b	c	Order No.
SD 0,4x2,5x75	A		0.4	2.5	75	
SD 0,5x3,0x80	A		0.5	3.0	80	
SD 0,8x4,0x100	A		0.8	4.0	100	
SD 1,0x5,5x150	A		1.0	5.5	150	
SD PH 1		1			80	
SD PH 2		2			100	
SDS 2,5-5,5/PH1/2						9009740000

F



### Set S 2.0/2.5/3.0/3.5/4.0/5.5

Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip



SD 0,4x2,0x60	B	0.4	2.0	60	
SD 0,4x2,5x75	A	0.4	2.5	75	
SD 0,5x3,0x80	A	0.5	3.0	80	
SD 0,6x3,5x100	A	0.6	3.5	100	
SD 0,8x4,0x100	A	0.8	4.0	100	
SD 1,0x5,5x150	A	1.0	5.5	150	
SDS 2.0-5.5					9205560000



### System 11+1 S-PH-PZ-SK

12-part set of interchangeable blades for slotted head, crosshead PH/PZ and hexagon screws, SoftFinish grip



SD		0.5	3.0	140	
SD		0.8	4.0	140	
SD		1.0	5.0	140	
SD		1.2	6.0	140	
PH 1		1		140	
PH 2		2		140	
PZ 1		1		140	
PZ 2		2		140	
SK		3		140	
SK		4		140	
SK		5		140	
SYSTEM 11+1					140 9009750000

**Weidmüller wrench set**

Allen key made from fully hardened, high-alloy chromium-vanadium steel, produced acc. to DIN ISO 2936 L (DIN 911), high-quality refined surface.

**SK WSD S**

9-piece offset screwdriver set in Prostar holder, with **MagicRing**: holds standard screws (size 3 and larger) in any position thanks to spring steel ring, with **ball point**: for working at angles up to 25°.

**SK S****7-piece Allen key set****SK S**

7-piece Allen key set with **MagicRing and ball point**: holds standard screws (size 3 and larger) in any position thanks to spring steel ring, with ball point: for working at angles up to 25°.

**TH S****8-piece Torx®-TH screwdriver set**

with hole in the blade point (tamper-proof), for screwing Torx® and Torx®-TH tamper-proof screws (centre pin in profile)



Type	Blade type	Size / AF	a	b	c	Order No.
		1.5				
		2				
		2.5				
		3				
		4				
		5				
		6				
		8				
		10				
SK WSD-S 1,5-10,0						9008850000

2						
2.5						
3						
4						
5						
6						
8						
SKS 2,0-8,0						9008860000

2						
2.5						
3						
4						
5						
6						
8						
SKS 2,0-8,0 MR						9008870000

9						
10						
15						
20						
25						
27						
30						
40						
TH-S 9-40						9008880000

## Pin and electrical cabinet key

### IS 4 / IS 6 / IS 8

#### Wrench with pegged pilot tip

Hexagon screwdriver with cross-grip made from high-quality plastics

- Surface nickel-plated
- Made from hardened chromium-vanadium steel
- According to DIN 6911
- Designed for screws acc. to DIN 6912

#### Ordering data

Type	Qty	Order No.
IS 4 DIN 6911	1	0485100000
IS 6 DIN 6911	1	0407900000
IS 8 DIN 6911	1	0235000000



#### Technical data

Blade length (C) 60 mm / 80 mm / 90 mm  
Weight 34 g

### IS 2 KG / IS 3 KG / IS 4 KG

#### Socket wrench

Hexagon screwdriver with cross-grip made from high-quality plastics

- Surface nickel-plated
- Made from hardened chromium-vanadium steel
- According to DIN 6911
- Designed for screws acc. to DIN 6912

#### Ordering data

Type	Qty	Order No.
IS 2 KG	1	1806630000
IS 3 KG	1	1806650000
IS 4 KG	1	1806660000

#### Technical data

Blade length (C) 100 mm  
Weight 26 g



## F

## Cross-Key Master


#### Universal key

- With bit holder and reversible bit (drives - refer to symbols)
- Material: die cast zinc
- Dimensions: 62 x 90 mm
- **Applications:**

For almost all commercial locking systems in buildings including: doors, window handles, radiator bleed valves, sanitary installations, HVAC, gas and water supply.

#### Ordering data

Type	Qty	Order No.
CROSS-KEY MASTER	1	9918150000



## Cross-Key Universal


#### Universal electrical cabinet key

- With bit holder and reversible bit (drives - refer to symbols)
- Material: die cast zinc
- Dimensions: 72 x 72 mm
- **Applications:**

For locking systems used in electrical engineering, fits all standard electrical cabinet locks.

#### Ordering data

Type	Qty	Order No.
CROSS-KEY UNIVERSAL	1	9918130000



## Cross-Key Universal S

#### Universal mini electrical cabinet key

- With bit holder and reversible bit (drives - refer to symbols)
- Material: die cast zinc
- Dimensions: 42 x 42 mm
- **Applications:**

For locking systems used in electrical engineering, fits all standard electrical cabinet locks.

#### Ordering data

Type	Qty	Order No.
CROSS-KEY UNIVERSAL S	1	9918140000

