

F


E

D


C

B



A






SECTION Y-Y
SCALE 10:1
INSULATION GRIP



SECTION Z-Z
SCALE 10:1
CONDUCTOR GRIP





SECTION U-U
SCALE 10:1



PART NUMBERS		GRIP CODE	WIRE GAUGE			PLATING	DIM A +0,20	DIM B +0,30	DIM ØC +0,10	DIM ØD +0,20
D-WIND (LEFT PAYOFF)	B-WIND (RIGHT PAYOFF)		ISO mm ²	JASO mm ²	SAE gauge					
34803-0211	34803-0213	S	0.22-0.35	0.3	22	TIN	1.80	2.40	0.90	1.36
34803-0212	34803-0214	L	0.50-0.75	0.50-0.85	20	(Sn)	2.15	2.50	1.20	1.72

ISO VIEWS
NOT TO SCALE



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL: COPPER ALLOY
2. PLATING MARK: TIN (Sn) - NO MARK
3. PACKAGING PER PK-31301-053
4. CRIMPING PER AS-34803-001
5. PROBING AT ANY LOCATION ON THE TERMINAL BEAM IS NOT PERMITTED

ENTER DESCRIPTION EC NO: UAU2011-0319 DRAWN:KFERGUSON CHKD: APPR:BMOSER		DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
A1		REV			mm	INCH	DRAWN BY K.FERGUSON	DATE 1-15-10	CTX64 FEMALE TERMINAL		
				4 PLACES	± ---	± ---	CHECKED BY	DATE			
				3 PLACES	± 0.08	± ---	D.HEMNANI	1-15-10	MOLEX INCORPORATED		
				2 PLACES	± 0.08	± ---	APPROVED BY	DATE			
				1 PLACE	± 0.08	± ---	B.MOSER	1-15-10			
			ANGULAR ± 1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
					SEE TABLE		SD-34803-001		1 OF 1		
					SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				