


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/16/06	D. PARHAM
B	ECN 3241: 1.30 WAS 1.5	3/19/08	D. CASTRO



NOTES:

ELECTRICAL:

UNLESS OTHERWISE SPECIFIED, WIRING IS STRAIGHT THROUGH FROM PIN TO PIN.
EACH ADAPTOR SHALL BE SUBJECTED TO AND PASS A CONTINUITY TEST.
INSULATION RESISTANCE: 20 MOHMS
CONTACT RESISTANCE: 1 OHM MAX

PACKAGING:

INDIVIDUALLY PACKAGE EACH ADAPTOR UTILIZING APPROPRIATE SIZED BAG

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2[51] / -0 >60 [1524] ≤120 [3048] = +4 / -0 >120 [3048] ≤300 [7620] = +6 / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	01/13/2006		
	CHECKED BY J. KIEZULAS	01/13/2006	CATEGORY AUDIO/VIDEO	
	APPROVED BY C. McCORMICK	01/16/2006	PRODUCT DESCRIPTION ADAPTOR DVI-D F/ HDMI F	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321	DWG. NO. DVIHDF
COLOR VARIATIONS MAY OCCUR		SCALE: NONE	CAD FILE: DVIHDF.SLDRW	REV. B
		SHEET 1 OF 1		