




LOC	DIST	REVISIONS					
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B1	REVISED PER ECO-11-005301	11APR11	RK	HMR



NOTE :

1. MATERIALS:

HOUSING: THERMOPLASTIC WITH GLASS FIBER FILLED,
UL94V-0 RATED, COLOR: (SEE TABLE)

CONTACTS: BRASS, THICKNESS= 0.3mm.

BOARD LOCK: BRASS, THICKNESS= 0.6mm.

SPRING LATCH: STAINLESS STEEL.

SHELL: STEEL, THICKNESS= 0.6mm.

SCREW: STEEL.

QUARTRANGLE RIVET: BRASS.

2. FINISH:

CONTACT: GOLD PLAED (SEE TABLE) ON CONTACT AREA,
100 μ " MIN TIN-Cu ON SOLDER TAIL,
50 μ " MIN. NICKEL UNDERPLATED ALL OVER.


SHELL AND SCREW: 50μ" MIN. NICKEL PLATED.

BOARD LOCK: 150 μ " MIN. TIN-Cu PLATED.

QUARTRANGLE RIVET: 50μ" MIN. NICKEL PLATED.


△3 HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL94V-0 RATED, COLOR: (SEE TABLE)

	W/O	BLACK		GOLD FLASH	4-1734044-3
OBSOLETE	W/	 BLACK	RIVET (M3)	15μ"	3-1734044-3
	W/O	BURGUNDY	SCREW	15μ"	2-1734044-1
OBSOLETE	W/O	 BLACK	RIVET (M3)	15μ"	1-1734044-3
	W/O	BLACK	RIVET	15μ"	1-1734044-2
	W/O	BLACK	SCREW	15μ"	1-1734044-1
	W/O	BLACK	RIVET (M3)	GOLD FLASH	 1734044-3
	W/O	BLACK	RIVET	GOLD FLASH	1734044-2
	W/O	BLACK	SCREW	GOLD FLASH	1734044-1
	GROUND TABS	HSG. COLOR	LOCK TYPE	GOLD PLATED	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CHIEN 27OCT2008 CHK S. CHIEN 27OCT2008 APVD W. KODAMA 27OCT2008		 TE Connectivity	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RCPT. ASS'Y, 36P RIGHT ANGLE, CENTRONICS.	
		0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± — ANGLES ± 3°			
MATERIAL SEE NOTE		FINISH SEE NOTE			
		PRODUCT SPEC 108-57098			
		QUALIFICATION TEST REPORT 501-57055			
		WEIGHT — GRAMS		SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-1734044	RESTRICTED TO —
				SCALE —	SHEET 1 OF 3
				REV B1	

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			


DETAIL A :





X-1734044-1







X-1734044-2




ONLY FOR 0-1734044-3 4



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK APVD PRODUCT SPEC APPLICATION SPEC WEIGHT		 TE Connectivity NAME RCPT. ASS'Y, 36P RIGHT ANGLE, CENTRONICS. SIZE CAGE CODE DRAWING NO RESTRICTED TO	
DIMENSIONS: MM 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	CUSTOMER DRAWING		SCALE —	SHEET 2 OF 3
MATERIAL —	—	A3 00779 C=1734044		REV B1	



UPPER COVER



LOWER COVER

PCS/TRAY	PACKING QUANTITY/OUTER BOX	N.W.(KGS)	G.W.(KGS)
12	192	8	9

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:						CHK	
APVD		PRODUCT SPEC						NAME	
MATERIAL		FINISH		APPLICATION SPEC		RCPT. ASS'Y, 36P RIGHT ANGLE, CENTRONICS.			
WEIGHT		CUSTOMER DRAWING		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
A3		00779		C=1734044		REV		B1	