


## Standard Recovery Diodes (Stud Version), 300 A



DO-205AB (DO-9)

### FEATURES

- Alloy diode
- Popular series for rough service
- Stud cathode and stud anode version
- RoHS compliant
- Designed and qualified for industrial level



### TYPICAL APPLICATIONS

- Welders
- Power supplies
- Motor controls
- Battery chargers
- General industrial current rectification

### PRODUCT SUMMARY

$I_{F(AV)}$	300 A
-------------	-------

### MAJOR RATINGS AND CHARACTERISTICS

PARAMETER	TEST CONDITIONS	VALUES	UNITS
$I_{F(AV)}$		300	A
	$T_C$	150	°C
$I_{FSM}$	50 Hz	6550	A
	60 Hz	6850	
$I^2t$	50 Hz	214	kA <sup>2</sup> s
	60 Hz	195	
$V_{RRM}$	Range	100 to 600	V
$T_J$		- 65 to 200	°C

### ELECTRICAL SPECIFICATIONS

#### VOLTAGE RATINGS

TYPE NUMBER	VOLTAGE CODE	$V_{RRM}$ , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	$V_{RSM}$ , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	$I_{RRM}$ MAXIMUM AT $T_J = 175\text{ °C}$ mA
300U(R)	10	100	200	40
	20	200	300	
	30	300	400	
	40	400	500	
	60	600	700	

FORWARD CONDUCTION						
PARAMETER	SYMBOL	TEST CONDITIONS			VALUES	UNITS
Maximum average forward current at case temperature	I <sub>F(AV)</sub>	180° conduction, half sine wave			300	A
					130	°C
Maximum peak, one cycle forward, non-repetitive surge current	I <sub>FSM</sub>	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T <sub>J</sub> = T <sub>J</sub> maximum	6550	A
		t = 8.3 ms			6850	
		t = 10 ms	100 % V <sub>RRM</sub> reapplied		5500	
		t = 8.3 ms			5750	
Maximum I <sup>2</sup> t for fusing	I <sup>2</sup> t	t = 10 ms	No voltage reapplied		214	kA <sup>2</sup> s
		t = 8.3 ms			195	
		t = 10 ms	100 % V <sub>RRM</sub> reapplied		151	
		t = 8.3 ms			138	
Maximum I <sup>2</sup> √t for fusing	I <sup>2</sup> √t	t = 0.1 to 10 ms, no voltage reapplied			2140	kA <sup>2</sup> √s
Maximum value of threshold voltage	V <sub>F(TO)</sub>	T <sub>J</sub> = 200 °C			0.610	V
Maximum value of forward slope resistance	r <sub>f</sub>				0.751	mΩ
Maximum forward voltage drop	V <sub>FM</sub>	I <sub>pk</sub> = 942 A, T <sub>J</sub> = 25 °C			1.40	V

THERMAL AND MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction operating and storage temperature range	$T_J$ , $T_{Stg}$		- 65 to 200	°C
Maximum thermal resistance, junction to case	$R_{thJC}$	DC operation	0.18	K/W
Maximum thermal resistance, case to heatsink	$R_{thCS}$	Mounting surface, smooth, flat and greased	0.08	
Maximum allowed mounting torque + 0 - 20 %		Not lubricated threads	37	Nm
		Lubricated threads	28	
Approximate weight			250	g
Case style		(JEDEC) see dimensions - link at the end of datasheet	DO-205AB (DO-9) <sup>(1)</sup>	

**Note**

(1) 302U-A uses case style B-26

$\Delta R_{thJC}$ CONDUCTION				
CONDUCTION ANGLE	SINUSOIDAL CONDUCTION	RECTANGULAR CONDUCTION	TEST CONDITIONS	UNITS
180°	0.020	0.015	$T_J = T_J \text{ maximum}$	K/W
120°	0.024	0.025		
90°	0.031	0.034		
60°	0.045	0.047		
30°	0.077	0.077		

**Note**

- The table above shows the increment of thermal resistance  $R_{thJC}$  when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics




Fig. 8 - Thermal Impedance  $Z_{thJC}$  Characteristic



**ORDERING INFORMATION TABLE**


Device code	300	U	R	60	A
	1	2	3	4	5
1	- • 300 = Standard 300U device • 302 = 300U top threaded version				
2	- U = Essential part number				
3	- • R = Stud reverse polarity (anode to stud) • None = Stud normal polarity (cathode to stud)				
4	- Voltage code x 10 = $V_{RRM}$ (see Voltage Ratings table)				
5	- A = Essential part number				

Note: For metric device M16 x 1.5 contact factory


LINKS TO RELATED DOCUMENTS	
Dimensions	<a href="http://www.vishay.com/doc?95340">http://www.vishay.com/doc?95340</a>

## DO-205AB (DO-9) and B-26 for 300U(R) Series

### DIMENSIONS FOR 300U(R)-A SERIES - DO-205AB (DO-9) in millimeters (inches)



### DIMENSIONS FOR 302U(R)-A SERIES - B-26 in millimeters (inches)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VS-302UR60A](#) [VS-300U10A](#) [VS-300U60A](#) [300UR40AM](#) [VS-300UR30A](#) [VS-300U20A](#) [VS-300U30A](#) [VS-300U40A](#)  
[VS-300UR10A](#) [VS-300UR20A](#) [VS-300UR40A](#) [VS-300UR60A](#)