



THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	, 19
© COPYRIGHT 19	BY AMP INCORPORATED.	ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS					
AL	2	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	ES00-0040-01	10JUL2001	JC	JP
			AI	REVISED PER ECO-09-025714	16DEC09	KK	AEG

	PART NUMBER	SECTION mm2	L1	L2	D1	D2	COLOR	QTY/BAG	
	737730-1	0.5	12.0	6.0	1.0	2.6	WHITE	200	
	737730-2		14.0	8.0					
	737730-3		16.0	10.0					
	737731-1	0.75	12.0	6.0	1.2	2.8	GREY	200	
	737731-2		14.0	8.0					
	737731-3		16.0	10.0					
	737731-4		18.0	12.0					
	737732-1	1.0	12.0	6.0	1.4	3.0	RED	200	
	737732-2		14.0	8.0					
	737732-3		16.0	10.0					
	737732-4		18.0	12.0					
	737733-1	1.5	14.0	8.0	1.7	3.5	BLACK	200	
	737733-2		16.0	10.0					
	737733-3		18.0	12.0					
	OBSOLETE	737733-4		24.0	18.0				
	737734-1	2.5	14.0	8.0	2.2	4.2	BLUE	100	
	737734-2		18.0	12.0					
OBSOLETE	737734-3			24.0					18.0
	737735-1	4.0	17.0	10.0	2.8	4.8	GREY	100	
	737735-2		20.0	12.0					
	737735-3		26.0	18.0					
	737736-1	6.0	20.0	12.0	3.5	6.3	YELLOW	100	
	737736-2		26.0	18.0					
	737737-1	10.0	22.0	12.0	4.5	7.6	RED	50	
	737737-2		28.0	18.0					
	737738-1	16.0	24.0	12.0	5.8	8.8	BLUE	50	
	737738-2		28.0	18.0					
	737739-1	25.0	30.0	16.0	7.3	11.2	YELLOW	50	
	737739-2		30.0	18.0					
	737739-3		36.0	22.0					
	737740-1	35.0	30.0	16.0	8.3	12.7	RED	25	
	737740-2		30.0	18.0					
	737740-3		39.0	25.0					
		737741-1	50.0	36.0	20.0	10.3	15.0	BLUE	25
	5 OBSOLETE	737741-2		40.0	25.0				



- | | |
|--|---|
| <p>1. DIMENSIONS BASED ON
DIN 46228.4</p> <p>2. COLOR BASED ON DIN 47002</p> <p>3. USE HAND TOOL 790081-1
FOR 0.5-4.0 mm2.</p> <p>USE HAND TOOL 790081-2
FOR 6.0-16.0 mm2</p> <p> FINISH FOR METAL SLEEVE:
TIN</p> <p> OBSOLETE PARTS: OBSOLETE
CIS STREAMLINING PER D.RENAUD/D.SINISI</p> | <p>1. DIMENSIONES BASADAS EN
DIN 46228.4</p> <p>2. COLOR BASADO EN DIN 47002</p> <p>3. USAR HERRAMIENTA MANUAL
790081-1 PARA 0.5-4.0mm2.</p> <p>USAR HERRAMIENTA MANUAL
790081-2 PARA 6.0-16.0mm2.</p> <p> ACABADO PARA EL CASQUILLO
METALICO: ESTAÑADO.</p> |
|--|---|



THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 10 JUL 2001 F. J. CARBONELL		AMP Tyco Electronics Corp, AMP España, S.A. Barcelona. Spain.	
		CHK 10 JUL 2001 J. PASCUAL			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME WIRE PIN PUNTERA	
		0 PLC ±- 1 PLC ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±-			
MATERIAL Cu-E PA 6.6		FINISH 			
		WEIGHT -			
CUSTOMER DRAWING				SIZE A3	CAGE CODE 00779
				DRAWING NO C-737730	SCALE -
				SHEET 1	OF 1
				REV A	