





基板穴推奨寸法

(基板厚 $t = 0.8 \sim 1.6$)


NOTE :
1. 使用ターミナル : 5378*

28.4	26.0	39-01-0149	5379-14	14
22.4	20.0	0119	11	11
20.4	18.0	0109	10	10
18.4	16.0	0099	09	9
16.4	14.0	0089	08	8
14.4	12.0	0079	07	7
12.4	10.0	0069	06	6
10.4	8.0	0059	05	5
8.4	6.0	0049	04	4
6.4	4.0	0039	03	3
4.4	2.0	39-01-0029	5379-02	2
B	A	EDP. NO.	ENG. NO.	毎 部 C K T. N O.

REVISED EC NO: J2012-0322 DRAWN:SKAWAKAMI CHKD:TN/ITSU APPR:MYAGI A	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		10 UNDER	±0.2	DRAWN BY STADOKORO	DATE 1984/12/14	TITLE 2.0 BOARD IN CONNECTOR HOUSING					
		10 OVER 30 UNDER	±0.25	CHECKED BY YYAMADA	DATE 1984/12/14						
		30 OVER	±0.3	APPROVED BY MENOMOTO	DATE 1984/12/14	MOLEX INCORPORATED					
		ANGULAR ±3 °		MATERIAL NO.							DOCUMENT NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		RSD-5379-001				1 OF 1	
				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

CONFIDENTIAL

(NON-ACCUMULATIVE)





RECOMMENDED P.C. BOARD DIM.
(THICKNESS : 0.8t ~ 1.6t)

NOTE:

1. TERMINAL APPLICATION : 5378*
2. ■: CRITICAL DIMENSION

28.4	26.0	39-01-0149	5379-14	14
22.4	20.0	0119	11	11
20.4	18.0	0109	10	10
18.4	16.0	0099	09	9
16.4	14.0	0089	08	8
14.4	12.0	0079	07	7
12.4	10.0	0069	06	6
10.4	8.0	0059	05	5
8.4	6.0	0049	04	4
6.4	4.0	0039	03	3
4.4	2.0	39-01-0029	5379-02	2
B	A	EDP. NO.	ENG. NO.	CKT.


REVISED EC NO: J2012-0322 DRAWN:SKAWAKAMI CHKD:N.I.TSU APPR:MYAGI	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY DATE HII 1986/12/11		TITLE 2.0 BOARD IN CONNECTOR HOUSING				
		10 OVER 30 UNDER	± 0.25	CHECKED BY DATE YYAMADA 1986/12/12						
		30 OVER	± 0.3	APPROVED BY DATE MENOMOTO 1986/12/12						
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		RSD-5379-002		1 OF 1			
	REV			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



基板取付穴推奨寸法 (t=0.8~1.6)
RECOMMENDED PC BOARD HOLE DIMENSION (t=0.8~1.6)

注記
NOTE

1. 使用ターミナル: 5378シリーズ
USE WITH TERMINAL: 5378 SERIES.



26.0	28.4	39-01-0149	5379-14	14
20.0	22.4	0119	11	11
18.0	20.4	0109	10	10
16.0	18.4	0099	09	9
14.0	16.4	0089	08	8
12.0	14.4	0079	07	7
10.0	12.4	0069	06	6
8.0	10.4	0059	05	5
6.0	8.4	0049	04	4
4.0	6.4	0039	03	3
2.0	4.4	39-01-0029	5379-02	2
B	A	EDP. NO.	ENG. NO.	回路番号 CKT. NO.

REVISED	EC NO: J2012-0322	DRAWN:SKAWAKAMI	2011/09/02	CHKD: I.ITSU	2011/09/02	APPR:MYAGI	2011/09/07	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION	
									10 UNDER	± 0.2	DRAWN BY HIJIMA	DATE 1996/06/14	TITLE 2.0 BOARD IN CONNECTOR HOUSING				
									10 OVER 30 UNDER	± 0.25	CHECKED BY MFUKUKSHIMA	DATE 1996/06/14					
									30 OVER	± 0.3	APPROVED BY MENOMOTO	DATE 1996/06/14					
									ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.				
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-5379-001				1 OF 1
REV									SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							