



## Product: [7731A](#)

75 Ohm SDI Coax, RG-11, 14 AWG Solid BC, Foil + 95% TC Braid, PVC Jkt, CMR

### Product Description

75 Ohm SDI Coax, RG-11, 14 AWG Solid Bare Copper Conductor, PE Insulation, Foil + 95% Tinned Copper Braid Shield, PVC Jacket, CMR

### Technical Specifications

#### Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p
------------------------	---

#### Construction Details

RG Type:	11
----------	----

#### Conductor

AWG	Stranding	Nom. Diameter	Material
14	Solid	0.064 in	BC - Bare Copper

#### Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.280 in

#### Outer Shield Material

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		95%

#### Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.400 in

### Electrical Characteristics

#### Return Loss (RL)

Frequency [MHz]	Min. Return Loss [dB]
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

#### Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.16 dB/100ft
3.58 MHz	0.29 dB/100ft
5 MHz	0.34 dB/100ft
7 MHz	0.39 dB/100ft
10 MHz	0.46 dB/100ft
67.5 MHz	1.05 dB/100ft
71.5 MHz	1.09 dB/100ft
88.5 MHz	1.21 dB/100ft

100 MHz	1.28 dB/100ft
135 MHz	1.47 dB/100ft
143 MHz	1.51 dB/100ft
180 MHz	1.69 dB/100ft
270 MHz	1.97 dB/100ft
360 MHz	2.31 dB/100ft
540 MHz	2.87 dB/100ft
720 MHz	3.40 dB/100ft
750 MHz	3.45 dB/100ft
1000 MHz	3.60 dB/100ft
1000 MHz	4.12 dB/100ft
1500 MHz	5.10 dB/100ft
2000 MHz	6.04 dB/100ft
2250 MHz	6.43 dB/100ft
3000 MHz	7.63 dB/100ft
4500 MHz	9.56 dB/100ft
6000 MHz	11.53 dB/100ft

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
2.5 Ohm/1000ft	1.5 Ohm/1000ft	16.1 pF/ft	75 Ohm	84%

#### Voltage

UL Voltage Rating
300 V (CMR, CMG)

#### Mechanical Characteristics

##### Temperature

UL Rating	Operating
60°C	-20°C to +75°C

##### Bend Radius

Installation Min.
4 in

Bulk Cable Weight:	87 lbs/1000ft
Max. Pull Tension:	145 lbs

#### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, UV Resistance
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1666 Vertical Shaft, FT4
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	7732A

#### History

Update and Revision:	Revision Number: 0.331 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Belden Wire & Cable:

[7731A 0104000](#) [7731A 0064000](#) [7731A 0014000](#) [7731A N3U1000](#) [7731A N3U4000](#) [7731A 0084000](#) [7731A 0034000](#) [7731A 0024000](#) [7731A 0074000](#) [7731A 0094000](#) [7731A 0044000](#) [7731A 0021000](#) [7731A 002500](#) [7731A 0091000](#) [7731A 008500](#) [7731A 0041000](#) [7731A 009500](#) [7731A 005500](#) [7731A 003500](#) [7731A 006500](#) [7731A 0051000](#) [7731A 0011000](#) [7731A 0061000](#) [7731A 004500](#) [7731A 0081000](#) [7731A 010500](#) [7731A 001500](#) [7731A 007500](#) [7731A 0031000](#) [7731A 0071000](#) [7731A 0101000](#)