

## M52957AFP

## DISTANCE DETECTION SIGNAL PROCESSING FOR 3V SUPPLY VOLTAGE

## DESCRIPTION

M52957AFP is a semiconductor integrated circuit containing distance detection signal processing circuit for 3V supply voltage.

This device transforms each optical inflow current I1 and I2 from PSD SENSOR into the voltage, and integrates that output after doing calculation corresponds to  $I1/(I1+I2)$ , and outputs it as the time data(pulse term).

## FEATURES

- Wide supply voltage range  $V_{CC}=2.2$  to  $5.5V$
- Includes clamp level switching circuit  
(Switch is 16 kinds by outside control)
- Includes STANDBY function
- Includes POWER ON RESET function

## APPLICATION


Auto focus control for the CAMERA  
Sensor for short distance etc

### RECOMMENDED OPERATING CONDITION

Supply voltage ..... 2.2 to 5.5V

Rated supply voltage ..... 3.0V

### PIN CONFIGURATION (TOP VIEW)




Outline 16P2E

Note: pin4,13 is connected only engineering sample

### BLOCK DIAGRAM

Note: pin4,13 is connected only engineering sample



**ABSOLUTE MAXIMUM RATINGS** (Ta=25°C ,unless noted)

Parameter	Symbol	Ratings	Unit	Remark
Supply voltage	Vcc	7.0	V	note 1
Power dissipation	Pd	320	mW	Ta=25°C
Thermal derating	Kθ	- 3.2	mW/ °C	Ta≥25°C
Pin supply voltage	VIF	7.0	V	Pin5,7,8,9,10,11
Another pin supply voltage	VI/O	- 0.3 to Vcc+0.3	V	note 2
Output pin inflow current	Isout	0.5	mA	NPN open collector
Operating temperature	Topr	- 10 to 50	°C	
Storage temperature	Tstg	- 40 to 125	°C	

note 1:As a principle,do not provide a supply voltage reversely.

note 2:As a principle,do not provide the terminals with the voltage over supply voltage or under ground voltage.

ELECTRICAL CHARACTERISTICS (Ta=25°C,Vcc=3.0V, unless otherwise noted)

Classification	Parameter	Symbol	Test conditions	Limits			Unit	Note
				Min.	Typ.	Max.		
	Operating supply voltage range	VCC		2.2	3.0	5.5	V	
Consuming current	Usual consuming current	ICC1		-	5.9	7.7	mA	
	While Rapid charge consuming current 1	ICC2	While CH rapid charge consuming current	-	17.7	23.0	mA	*1
	While Rapid charge consuming current 2	ICC3	While CH and CINT rapid charge consuming current	-	19.0	24.7	mA	*1
	While STAND BY consuming current	ICC4		-	-	1.0	μA	*1
HOLD pin	HOLD"H" input voltage	VHOH		1.1	-	7.0	V	
	HOLD "L" input voltage	VHOL		0	-	0.3	V	
	HOLD"H" input current	IHOH	VIH=5.5V	-	-	1.0	μA	
	HOLD "L" input current	IHOL	VIL=0V	-100	-75	-50	μA	
INT pin	INT "H" input voltage	VINH		1.1	-	7.0	V	
	INT "L" input voltage	VINL		0	-	0.3	V	
	INT "H" input current	IINH	VIH=5.5V	-	-	1.0	μA	
	INT "L" input current	IINL	VIL=0V	-100	-75	-50	μA	
CLALV pin	CLALV "H" input voltage	VCLH		1.1	-	7.0	V	
	CLALV "L" input voltage	VCLL		0	-	0.3	V	
	CLALV "H" input current	ICLH	VIH=5.5V	-	-	1.0	μA	
	CLALV "L" input current	ICLL	VIL=0V	-100	-75	-50	μA	
RESET pin	RESET"H" input voltage	VREH		1.1	-	7.0	V	
	RESET "L" input voltage	VREL		0	-	0.3	V	
	RESET "H" input current	IREH	VIH=5.5V	-	-	1.0	μA	
	RESET "L" input current	IREL	VIL=0V	-100	-75	-50	μA	
STB pin	STB "H" input voltage	VSTH		VCC-0.3	-	7.0	V	
	STB "L" input voltage	VSTL		0	-	0.3	V	
	STB "H" input current	ISTH	VIH=5.5V	-	-	3.0	μA	
	STB "L" input current	ISTL	VIL=0V	-150	-100	-50	μA	
HOLD C	CH rapid charge current	ICHQC	IPSD=5μA , VCH=0V	-2000	-1000	-500	μA	*1
	CH stationary charge current	ICHC	VCH=0V	-30	-20	-10	μA	*1
	CH stationary discharge current	ICHDC	VCH=1.5V	10	20	30	μA	*1

## ELECTRICAL CHARACTERISTICS (cont.)(Ta=25°C,Vcc=3.0V, unless otherwise noted)

Classification	Parameter	Symbol	Test conditions	Limits			Unit	Note
				Min.	Typ.	Max.		
Double integration	CINT rapid charge current	ICINTC	VCI=1V (CINT stable period)	84	120	156	μA	*1
	CINT reference voltage	VCINT	GND criterion	1.6	1.8	2.0	V	*1
	The first integration current	ICI1	VCINT=1.5V	4.06	5.80	7.54	μA	*1
	The second integration current	ICI2	VCHF=2V, VCHN=0V	-3.20	-2.46	-1.27	μA	*1
	The first integration current stability percentage	ΔICI1		—	—	10	%	*2
	The second integration current stability percentage	ΔICI2		—	—	10	%	*2
	The first and second integration current ratio	ICI12	ICI1   /   ICI2	2.12	2.36	2.60		
AF input condition 1	AF output time(9:1)-1	D(9:1) - 1	Near side9 : Far side1	11.78	13.40	15.02	msec	*3
	AF output time(6:4)-1	D(6:4) - 1	Near side6 : Far side4	7.77	8.95	10.13	msec	*3
	AF output time(3:7)-1	D(3:7) - 1	Near side3 : Far side7	3.77	4.51	5.25	msec	*3
	AF slope -1	ΔAF - 1		6.57	8.89	11.21	msec	*3
	AF linearity-1	LAF - 1		0.9	1.0	1.1		*3
AF input condition 2	AF output time(9:1)-2	D(9:1) - 2	Near side9 : Far side1	11.78	13.40	15.02	msec	*3
	AF output time(6:4)-2	D(6:4) - 2	Near side6 : Far side4	7.77	8.95	10.13	msec	*3
	AF output time(3:7)-2	D(3:7) - 2	Near side3 : Far side7	3.77	4.51	5.25	msec	*3
	AF slope -2	ΔAF - 2		6.57	8.89	11.21	msec	*3
	AF linearity-2	LAF - 2		0.9	1.0	1.1		*3
AF input condition 3	AF output time(9:1)-3	D(9:1) - 3	Near side9 : Far side1	11.78	13.40	15.02	msec	*3
	AF output time(6:4)-3	D(6:4) - 3	Near side6 : Far side4	7.77	8.95	10.13	msec	*3
	AF output time(3:7)-3	D(3:7) - 3	Near side3 : Far side7	3.77	4.51	5.25	msec	*3
	AF slope -3	ΔAF - 3		6.57	8.89	11.21	msec	*3
	AF linearity-3	LAF - 3		0.9	1.0	1.1		*3
AF input condition 1 minus 2	ΔAF output time(9:1)	ΔD(9:1)	Near side9 : Far side1 (Condition 1-2)	—	—	280	μsec	
	ΔAF output time(6:4)	ΔD(6:4)	Near side6 : Far side4 (Condition 1-2)	—	—	280	μsec	
	ΔAF output time(3:7)	ΔD(3:7)	Near side3 : Far side7 (Condition 1-2)	—	—	280	μsec	

## ELECTRICAL CHARACTERISTICS (cont.)(Ta=25°C,Vcc=3.0V, unless otherwise noted)

Classification	Parameter	Symbol	Test conditions	Limits			Unit	Note
				Min.	Typ.	Max.		
Data	SOUT leak current	ISOUTL	VIN = 5.5V	—	—	1.0	μA	
	SOUT saturation voltage	VSOUTS	IOUT=500μA	—	—	0.3	V	
Sensor	Signal light saturation current	ΔINF		3.0	—	—	μA	*4
	Stationary light remove current	IPSD		—	—	30	μA	*4
	Clamp level	ICLAM	Change quantity for Typ. current	-30	—	30	%	

\*1 Set up the logic control terminal, correspond to the parameter.

\*2 Change ratio between the first integration current and the second integration current at a voltage of CINT that is {CINT reference voltage(VCINT)-0.1V} and 1V.

$$\Delta I_{C1} = \left( 1 - \frac{\text{The first integration current (CINT=1V)}}{\text{The first integration current (CINT=VCINT-0.1V)}} \right) \times 100\%$$

$$\Delta I_{C2} = \left( 1 - \frac{\text{The second integration current (CINT=1V)}}{\text{The second integration current (CINT=VCINT-0.1V)}} \right) \times 100\%$$

\*3 Connect the resistance of 120KΩ instead of PSD and establish current output from PHOTO COUPLER correspond to the parameter. And input the varied resistance ratio. And measure the pulse width of SOUT output at that time, obtain AF slope and AF linearity from the equations below.

Input condition1: IPSD (Stationary light current)=0 I1+I2=100nA  
 Input condition2: IPSD (Stationary light current)=0 I1+I2=50nA  
 Input condition3: IPSD (Stationary light current)=10μA I1+I2=100nA

D(9:1) ••• The pulse width of SOUT output at input with I1:I2=9:1

D(6:4) ••• The pulse width of SOUT output at input with I1:I2=6:4

D(3:7) ••• The pulse width of SOUT output at input with I1:I2=3:7




AF slope :  $\Delta AF = D(9:1) - D(7:3)$

AF linearity :  $L(AF) = (D(9:1) - D(6:4)) / (D(6:4) - D(7:3))$


PSD quite resistance : 120KΩ

\*4 The input current of one side channel when stationary light remove circuit and I/V transform AMP is not saturated.

## DESCRIPTION OF PIN


Pin name	Circuit diagram	Parameter	Limits			Unit	Test conditions and note
			Min.	Typ.	Max.		
HOLD INT CLALV RESET		"H"input voltage	1.1	—	7.0	V	
		"L"input voltage	0	—	0.3	V	
		"H"input current	—	—	1.0	μA	VIH=5.5V
		"L"input current	-100	-75	-50	μA	VIL=0V
STB		"H"input voltage	VCC-0.3	—	7.0	V	
		"L"input voltage	0	—	0.3	V	
		"H"input current	—	—	3.0	μA	VIH=5.5V
		"L"input current	-150	-100	-50	μA	VIL=0V
SOUT		"L"output voltage	—	—	0.3	V	IOL=500μA
		"H"leak current	—	—	1.0	μA	VIN=5.5V

## APPLICATION EXAMPLE



## Controls

- (1) STB ••••• This terminal enables IC to operate. IC is Standby at HIGH in this terminal. IC can operate at LOW in this terminal.
- (2) RESET ••••• This terminal resets the whole IC including a logic. This terminal resets IC at HIGH. This terminal cancel resetting IC at the edge from HIGH to LOW. IC includes power on reset function. The control from external is also possible. The reset term in IC takes OR between power on reset and control signal from external.



While this terminal is HIGH, dielectric divide pole countermeasures circuit of integration condenser is active.

(3) CLALV •••••

This terminal sets up clamp level.

As including D/A of 4bit, 16way clamp level setting is possible by inputting clock after reset is canceled(include none clamp).

Set up current value of each bit is on the right table.  
The number of input clock and set up clamp level is as follows.


bit	Set up current (Typ.)
1	0.125 nA
2	0.25 nA
3	0.5 nA
4	1.0 nA

Clock value	Clamp level(Typ.)	Clock value	Clamp level(Typ.)
0	None clamp	12	1.500 nA
1	0.125 nA	13	1.625 nA
2	0.250 nA	14	1.750 nA
3	0.375 nA	15	1.875 nA
4	0.500 nA	16	None clamp
5	0.625 nA	17	0.125 nA
6	0.750 nA	18	0.250 nA
7	0.875 nA	19	0.375 nA
8	1.000 nA	20	0.500 nA
9	1.125 nA	:	:
10	1.250 nA	:	:
11	1.375 nA	:	:

Clamp level is established with fall edge of input clock.  
It repeats the same value after 16 clock.

(4) HOLD )••••• These terminals implement the following controls by inputting HIGH/LOW.  
INT

- a.CINT rapid charge ON , OFF
- b.CH rapid charge ON , OFF
- c.Stationary light hold ON , OFF
- d.The first integration ON , OFF
- e.The second integration ON , OFF






- a.CINT rapid charge •••• After reset is canceled, the capacity of CINT is charged rapidly until INT terminal first falls.
- b.CH rapid charge •••• After reset is canceled, the capacity of CH is charged rapidly until INT terminal first rises and falls.
- c.Stationary light hold •••• After reset is canceled, holds the stationary light while HOLD terminal is HIGH.
- d.The first integration •••• After reset is canceled, as HOLD terminal is HIGH and INT terminal is HIGH, the first integration is implemented while INT terminal is HIGH. Therefore, the first integration must be finished (INT terminal from HIGH to LOW) until stationary light hold will be completed (HOLD terminal from HIGH to LOW)
- e.The second integration •••• After reset is canceled, the second integration is implemented as HOLD terminal is LOW and INT terminal is HIGH. And, the second integration is completed by exceeding judgment level of CINT terminal although INT terminal is HIGH.
- (5)SOUT ••••• When the second integration starts, This terminal becomes from HIGH to LOW. If CINT terminal exceeds judge level or INT terminal becomes from HIGH to LOW, this terminal becomes from LOW to HIGH.

(notice) As the signal from microcomputer, the signal that controls IRED ON/OFF is required except for above mentioned control signals. But applying the timing of HOLD is available.

SEQUENTIAL TIME CHART EXAMPLE




## Mask Option

(1) The second integration current value can be doubled.(  $2.5\mu \rightarrow 5.0\mu\text{A}$  )


(2) Control terminal variation

### ① Full spec (typical)



This type uses CLALV,STB,RESET,INT,HOLD,SOUT terminal as I/F terminal to the microcomputer. This is the typical type at M52957AFP.

### ② Most simplified type




This type does not connect CLALV,STB,RESET terminals to the microcomputer. When above mentioned terminals are not connected to the microcomputer without changing mask,connect each terminal to the ground. In this case,clamp level becomes 0 and standby function is lost. Power on reset in IC is used as reset.

### ③ Explanation of the terminal that can be simplified.

(a)CLALV ••••• In the typical type,16way clamp levels can be set by the external control,but also the terminal can be simplified by mask option as follows.

(I) Clamp level fixation ••••• Selects 1 point from 16 steps of clamp level and fixes it.

(II) Clamp level 2 step changeover••• Selects 2 points from clamp level and switches it by changing CLALV terminal HIGH/LOW. However,as selecting 2 points,there is a following constraint.



Fixes 3 parts of 4 switches correspond to each bit in figure to ON or OFF,controls another part by CLALV terminal .

- (b) STB ••••• When no standby function required such as VCC is switched ON/OFF, STB terminal can be eliminated.
- (c) RESET ••••• Since IC include power on reset circuit, RESET terminal can be eliminated. As merit of controlling RESET terminal from outside, distance detection time can be shortened because there is no need to switch VCC or STB Terminal ON /OFF at consecutive distance detection.

————— Note regarding these materials —————

- These materials are intended as reference to assist our customers in the selection of the Mitsubishi semiconductor product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Mitsubishi Electric Corporation or a third party.
- Mitsubishi Electric Corporation assumes no responsibility for any damage, or infringement of any third-party's right, originating in the use of any product data, diagrams, charts of circuit application examples contained in these materials.
- All information contained in these materials, including product data, diagrams and charts, represent information on products at the time of publication of these materials, and are subject to change by Mitsubishi Electric Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for the latest product information before purchasing a product listed herein.
- Mitsubishi Electric Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor when considering the use of a product contained herein for special applications, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear repeater use.
- The prior written approval of Mitsubishi Electric Corporation is necessary to reprint or reproduce in whole or in part these materials.
- If these products or technologies are subject to the Japanese export control restrictions, they must be exported under license from the Japanese government and cannot be imported into a country other than the approved destination. Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
- Please contact Mitsubishi Electric Corporation or an authorized Mitsubishi Semiconductor product distributor for further details on these materials or the products contained therein.