



PRODUCT NUMBER	ROW	DIM"A"	DIM"B"
70437-X11 NOTE 10 LEAD FREE OPTION	E	6.50	4.30
	D	6.50	4.30
	C	6.50	4.30
	B	6.50	4.30
	A	6.50	4.30
70437-X12 NOTE 10 LEAD FREE OPTION	E	5.75	4.30
	D	5.75	4.30
	C	5.75	4.30
	B	5.75	4.30
	A	7.25	4.30
70437-X13 NOTE 10 LEAD FREE OPTION	E	5.75	4.30
	D	5.00	4.30
	C	5.75	4.30
	B	5.75	4.30
	A	6.50	4.30
70437-X14 NOTE 10 LEAD FREE OPTION	E	5.75	4.30
	D	5.75	4.30
	C	7.25	4.30
	B	5.75	4.30
	A	5.75	4.30
70437-X16 NOTE 10 LEAD FREE OPTION	E	5.75	4.30
	D	5.75	4.30
	C	5.75	4.30
	B	5.75	4.30
	A	5.75	4.30
70437-X17 NOTE 10 LEAD FREE OPTION	E	8.00	4.30
	D	8.00	4.30
	C	8.00	4.30
	B	8.00	4.30
	A	8.00	4.30
70437-X18 NOTE 10 LEAD FREE OPTION	E	5.00	4.30
	D	5.00	4.30
	C	5.00	4.30
	B	5.00	4.30
	A	5.00	4.30
70437-X19 NOTE 10 LEAD FREE OPTION	E	6.50	4.30
	D	6.50	4.30
	C	6.50	4.30
	B	8.00	4.30
	A	6.50	4.30
70437-X20 NOTE 10 LEAD FREE OPTION	E	6.50	4.30
	D	6.50	4.30
	C	6.50	4.30
	B	6.50	4.30
	A	7.25	4.30

NO REAR PLUG-UP

PRODUCT NUMBER	ROW	DIM"A"	DIM"B"
70437-X21 NOTE 10 LEAD FREE OPTION	E	6.50	13.60
	D	6.50	13.60
	C	6.50	13.60
	B	6.50	13.60
	A	6.50	13.60
70437-X22 NOTE 10 LEAD FREE OPTION	E	5.75	13.60
	D	5.75	13.60
	C	5.75	13.60
	B	5.75	13.60
	A	7.25	13.60
70437-X23 NOTE 10 LEAD FREE OPTION	E	5.75	13.60
	D	5.00	13.60
	C	5.75	13.60
	B	5.75	13.60
	A	6.50	13.60
70437-X24 NOTE 10 LEAD FREE OPTION	E	5.75	13.60
	D	5.75	13.60
	C	7.25	13.60
	B	5.75	13.60
	A	5.75	13.60
70437-X26 NOTE 10 LEAD FREE OPTION	E	5.75	13.60
	D	5.75	13.60
	C	5.75	13.60
	B	5.75	13.60
	A	5.75	13.60
70437-X27 NOTE 10 LEAD FREE OPTION	E	8.00	13.60
	D	8.00	13.60
	C	8.00	13.60
	B	8.00	13.60
	A	8.00	13.60
70437-X28 NOTE 10 LEAD FREE OPTION	E	5.00	13.60
	D	5.00	13.60
	C	5.00	13.60
	B	5.00	13.60
	A	5.00	13.60
70437-X29 NOTE 10 LEAD FREE OPTION	E	6.50	13.60
	D	6.50	13.60
	C	6.50	13.60
	B	8.00	13.60
	A	6.50	13.60
70437-X30 NOTE 10 LEAD FREE OPTION	E	6.50	13.60
	D	6.50	13.60
	C	6.50	13.60
	B	6.50	13.60
	A	7.25	13.60

REAR PLUG-UP
OR WIRE WRAP

PRODUCT NUMBER	ROW	DIM"A"	DIM"B"
70437-X31 NOTE 10 LEAD FREE OPTION	E	6.50	17.00
	D	6.50	17.00
	C	6.50	17.00
	B	6.50	17.00
	A	6.50	17.00
70437-X32 NOTE 10 LEAD FREE OPTION	E	5.75	17.00
	D	5.75	17.00
	C	5.75	17.00
	B	5.75	17.00
	A	7.25	17.00
70437-X33 NOTE 10 LEAD FREE OPTION	E	5.75	17.00
	D	5.00	17.00
	C	5.75	17.00
	B	5.75	17.00
	A	6.50	17.00
70437-X34 NOTE 10 LEAD FREE OPTION	E	5.75	17.00
	D	5.75	17.00
	C	7.25	17.00
	B	5.75	17.00
	A	5.75	17.00
70437-X36 NOTE 10 LEAD FREE OPTION	E	5.75	17.00
	D	5.75	17.00
	C	5.75	17.00
	B	5.75	17.00
	A	5.75	17.00
70437-X37 NOTE 10 LEAD FREE OPTION	E	8.00	17.00
	D	8.00	17.00
	C	8.00	17.00
	B	8.00	17.00
	A	8.00	17.00
70437-X38 NOTE 10 LEAD FREE OPTION	E	5.00	17.00
	D	5.00	17.00
	C	5.00	17.00
	B	5.00	17.00
	A	5.00	17.00
70437-X39 NOTE 10 LEAD FREE OPTION	E	6.50	17.00
	D	6.50	17.00
	C	6.50	17.00
	B	8.00	17.00
	A	6.50	17.00
70437-X40 NOTE 10 LEAD FREE OPTION	E	6.50	17.00
	D	6.50	17.00
	C	6.50	17.00
	B	6.50	17.00
	A	7.25	17.00

REAR PLUG-UP
AND WIRE WRAP

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family METRAL (tm)	
ltr	ecr no	dr	date	tolerances unless otherwise specified							
N				angles	line to	X #3		MM		title 5 ROW P.F. HEADER HOUSING ASSEMBLY - EE	
				0° ±2'		XX #18		scale 1:1		dwg no	
				dr	S. STONER	1995-03-07		FCI		sheet 2 of	
				engr	R. DOUTRICH	1995-03-07				70437	
				chr	S. STONER	1995-03-07				size A4	
				appd	S. STONER	1995-03-07				type CUSTOMER Drawing	
sheet index	revision	sheet									