

LM118, LM218, LM318 HIGH-PERFORMANCE OPERATIONAL AMPLIFIERS

SLOS063A – JUNE 1976 – REVISED APRIL 1994

- **Small-Signal Bandwidth** . . . 15 MHz Typ
- **Slew Rate** . . . 50 V/μs Min
- **Bias Current** . . . 250 nA Max (LM118, LM218)
- **Supply Voltage Range** . . . ±5 V to ±20 V
- **Internal Frequency Compensation**
- **Input and Output Overload Protection**
- **Same Pin Assignments as General-Purpose Operational Amplifiers**

description


The LM118, LM218, and LM318 are precision, high-speed operational amplifiers designed for applications requiring wide bandwidth and high slew rate. They feature a factor-of-ten increase in speed over general-purpose devices without sacrificing dc performance.

These operational amplifiers have internal unity-gain frequency compensation. This considerably simplifies their application, since no external components are necessary for operation. However, unlike most internally compensated amplifiers, external frequency compensation may be added for optimum performance. For inverting applications, feed-forward compensation boosts the slew rate to over 150 V/μs and almost double the bandwidth. Overcompensation can be used with the amplifier for greater stability when maximum bandwidth is not needed. Further, a single capacitor may be added to reduce the settling time for 0.1% error band to under 1 μs.


The high speed and fast settling time of these operational amplifiers make them useful in A/D converters, oscillators, active filters, sample-and-hold circuits, and general-purpose amplifiers.

The LM118 is characterized for operation from –55°C to 125°C. The LM218 is characterized for operation from –25°C to 85°C, and the LM318 is characterized for operation from 0°C to 70°C.

**D, JG, OR P PACKAGE
(TOP VIEW)**




**FK PACKAGE
(TOP VIEW)**



NC – No internal connection

symbol



Pin numbers shown are for the D, JG, and P packages.

PRODUCTION DATA information is current as of publication date.
Products conform to specifications per the terms of Texas Instruments
standard warranty. Production processing does not necessarily include
testing of all parameters.

**TEXAS
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1994, Texas Instruments Incorporated
On products compliant to MIL-STD-883, Class B, all parameters are
tested unless otherwise noted. On all other products, production
processing does not necessarily include testing of all parameters.

8961724 0092712 822

2–13

LM118, LM218, LM318
HIGH-PERFORMANCE OPERATIONAL AMPLIFIERS


SLOS063A – JUNE 1976 – REVISED APRIL 1994

AVAILABLE OPTIONS

T _A	V _{IOMax} AT 25°C	PACKAGE			
		SMALL OUTLINE (D)	CHIP CARRIER (FK)	CERAMIC DIP (JG)	PLASTIC DIP (P)
0°C to 70°C	10 mV	LM318D	—	—	LM318P
–25°C to 85°C	4 mV	LM218D	—	—	LM218P
–55°C to 125°C	4 mV	LM118D	LM118FK	LM118JG	LM118P

The D package is available taped and reeled. Add the suffix R to the device type (e.g., LM318DR).

schematic



Component values shown are nominal.

8961724 0092713 769



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

LM118, LM218, LM318 HIGH-PERFORMANCE OPERATIONAL AMPLIFIERS

SLOS063A – JUNE 1976 – REVISED APRIL 1994

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

	LM118	LM218	LM318	UNIT
Supply voltage, V_{CC+} (see Note 1)	20	20	20	V
Supply voltage, V_{CC-} (see Note 1)	-20	-20	-20	V
Input voltage, V_I (either input, see Notes 1 and 2)	± 15	± 15	± 15	V
Differential input current, V_{ID} (see Note 3)	± 10	± 10	± 10	mA
Duration of output short circuit (see Note 4)	unlimited	unlimited	unlimited	
Continuous total power dissipation	See Dissipation Rating Table			
Operating free-air temperature range, T_A	-55 to 125	-25 to 85	0 to 70	°C
Storage temperature range	-65 to 150	-65 to 150	-65 to 50	°C
Case temperature for 60 seconds	FK package	260		°C
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	D or P package	260	260	°C
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds	JG package	300		°C

- NOTES: 1. All voltage values, unless otherwise noted, are with respect to the midpoint between V_{CC+} and V_{CC-} .
2. The magnitude of the input voltage must never exceed the magnitude of the supply voltage or 15 V, whichever is less.
3. The inputs are shunted with two opposite-facing base-emitter diodes for overvoltage protection. Therefore, excessive current flows if a different input voltage in excess of approximately 1 V is applied between the inputs unless some limiting resistance is used.
4. The output can be shorted to ground or either power supply. For the LM118 and LM218 only, the unlimited duration of the short circuit applies at (or below) 85°C case temperature or 75°C free-air temperature.

DISSIPATION RATING TABLE

PACKAGE	$T_A \leq 25^\circ\text{C}$ POWER RATING	DERATING FACTOR	DERATE ABOVE T_A	$T_A = 70^\circ\text{C}$ POWER RATING	$T_A = 85^\circ\text{C}$ POWER RATING	$T_A = 125^\circ\text{C}$ POWER RATING
D	500 mW	5.8 mW/°C	64°C	464 mW	377 mW	145 mW
FK	500 mW	11.0 mW/°C	105°C	500 mW	500 mW	275 mW
JG	500 mW	8.4 mW/°C	90°C	500 mW	500 mW	210 mW
P	500 mW	8.0 mW/°C	88°C	500 mW	500 mW	200 mW



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

2-15

8961724 0092714 6T5

LM118, LM218, LM318
HIGH-PERFORMANCE OPERATIONAL AMPLIFIERS

SLOS063A—JUNE 1976—REVISED APRIL 1994

electrical characteristics at specified free-air temperature (see Note 5)

PARAMETER	TEST CONDITION†	TA‡	LM118, LM218			LM318			UNIT
			MIN	TYP	MAX	MIN	TYP	MAX	
VIO Input offset voltage	VO = 0	25°C		2	4		4	10	mV
		Full range			6			15	
IIO Input offset current	VO = 0	25°C		6	50		30	200	nA
		Full range			100			300	
IIB Input bias current	VO = 0	25°C		120	250		150	500	nA
		Full range			500			750	
VICR Common-mode input voltage range	VCC± = ±15 V	Full range	±11.5			±11.5			V
VOM Maximum peak output voltage swing	VCC± = ±15 V, RL = 2 kΩ	Full range	±12	±13		±12	±13		V
AVD Large-signal differential voltage amplification	VCC± = ±15 V, VO = ±10 V, RL ≥ 2 kΩ	25°C	50	200		25	200		V/mV
		Full range	25			20			
BT Unity-gain bandwidth	VCC± = ±15 V	25°C		15			15		MHz
ri Input resistance		25°C	1*	3		0.5	3		MΩ
CMRR Common-mode rejection ratio	VIC = VICRmin	Full range	80	100		70	100		dB
kSVR Supply-voltage rejection ratio (ΔVCC/ΔVIO)		Full range	70	80		65	80		dB
ICC Supply current	VO = 0, No load	25°C		5	8		5	10	mA

* On products compliant to MIL-STD-883, Class B, this parameter is not production tested.
† All characteristics are measured under open-loop conditions with common-mode input voltage unless otherwise specified.
‡ Full range for LM118 is -55°C to 125°C, full range for LM218 is -25°C to 85°C, and full range for LM318 is 0°C to 70°C.
NOTE 5: Unless otherwise noted, VCC = ±5 V to ±20 V. All typical values are at VCC± = ±15 V and TA = 25°C.

operating characteristics, VCC± = ±15 V, TA = 25°C

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SR Slew rate at unity gain	ΔVI = 10 V, CL = 100 pF, See Figure 1	50*	70		V/μs

* On products compliant to MIL-STD-883, Class B, this parameter is not production tested.




Figure 1. Slew Rate