


Nimbus D



Nimbus D		65		95		125		175	
Rated power at 10° C	[W]	30	50	40	60	50	75	80	100
External profile temp. (approx.)	[°C]	130	205	135	205	160	190	190	200
Voltage range		110 - 240 V, AC/DC							
Protection class		II							
System of protection		IP 20							
Connection wires 2 x 0,5 mm², silicone		500 mm long							
Fixing		DIN Clip for 35 mm rail EN50 022							
Approvals		VDE, UL, CSA							
Dimensions	LxWxH [mm]	65x70,7x24		95x70,7x24		125x70,7x24		175x70,7x24	
Weight	[kg]	0,13	0,14	0,18	0,19	0,23	0,24	0,33	0,34
Recommended fuse (time-delay)	240 V	4 A	6,3 A	4 A	6,3 A	4 A	6,3 A	6,3 A	6,3 A
	110 V	2 A	4 A	2 A	4 A	2 A	4 A	4 A	6,3 A

Ordering Example: Nimbus D 95, 40 W, 110-240 V
Special design 12 - 24 V.



Special Features

- Rugged aluminium extrusion profile
- Compact design with high power density
- Self-regulating PTC-Technology
- Safety by temperature limitation
- Fixing clip can be mounted either at the wide side or at the narrow side (see position 1 on the drawing)

Optional

- Connection cable
2 x 0,75 mm², Silicone

- 1 Fixing clip
for 35 mm DIN top hat rail
EN50 022
- 2 Aluminium profile
- 3 Silicon wire 0,5 mm²
- 4 Glass silk tube

DBK David+Baader GmbH

Components

Rheinstrasse 72 - 74
D - 76870 Kandel

Phone: + 49 (0) 72 75 7 03 - 231
Fax: + 49 (0) 72 75 7 03 - 249

info@dbk-group.de
www.dbk-components.com