



Extension terminal, 2.5-35 mm<sup>2</sup>

Part no. Z-EK/35/UL  
Article no. 104901

### Delivery programme

Basic function		Busbar
Basic function accessories		Extension terminals
Application		Switchgear for industrial and commercial applications
Product range		Z-SV

### Approvals

Product Standards	IEC/EN 60898; UL 489; CE marking
UL File No.	E257181
UL Category Control No.	NMTR2, DIHS2
CSA File No.	-
CSA Class No.	-
North America Certification	UL recognized
Specially designed for North America	Yes, large creepage and creepage distances
Suitable for	Feeder circuits, branch circuits
Max. Voltage Rating	Refer to main components FAZ, FAZ-NA, FAZ-RT
Degree of Protection	IEC: IP20, UL/CSA Type: -

### Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Busbar terminal (EC000001)			
Electric engineering, automation, process control engineering / Electrical installation, device / Clamp (not overhead line) / Switch board (ecl@ss8-27-14-11-46 [BAA025009])			
Busbar thickness	mm	0 - 0	
Busbar width	mm	0 - 0	
Suitable for		-	
Width clamp	mm	0	
Max. conductor cross section	mm <sup>2</sup>	0	
Max. rated operation current I <sub>e</sub>	A	0	
Suitable for round conductor connection		Yes	
Suitable for sector conductor connection		No	
Suitable for strip conductor connection		No	