

RECEIVED 1 1 DEC 2003

+LORN 豪恩
Electret Condenser Microphone Units

深圳市豪恩电声科技有限公司

Shenzhen Horn Electroacoustic Technology Co., Ltd

SPEC.SHEET NO: N031206007

Address:
Block 9, Shuiwei Ind Zone, Shuiwei New
Village, Dalang, Longhua, Shenzhen,
Guangdong, China 518109

Tel: (86)755-28121370/ 28121371/28109416/28109419
Fax: (86)755-28109417
E-mail: rd@horn.com.cn
Website: www.horn.com.cn

CUSTOMER : Digi-Key Corporation

APPROVAL SHEET

PRODUCT NAME	PART NUMBER	DIMENSION	REMARK
Electret Condenser Microphone	EM6015-44BC10&33	$\phi 6.0 \times 1.5(\text{mm})$	D.S.PCB

APPROVED BY	CHECKED BY	ISSUED BY
		

APPROVED BY

DATE:

PART NUMBER : EM6015-44BC10&33

Address:
Block 9, Shuiwei Ind Zone, Shuiwei New
Village, Dalang, Longhua, Shenzhen,
Guangdong, China 518109


Tel: (86)755-28121370/ 28121371/28109416/28109419
Fax: (86)755-28109417
E-mail: rd@horn.com.cn
Website: www.horn.com.cn

SPECIFICATION

Item	Symbol	Test conditions	Min	Standard	Max	Unit
Sensitivity	S	$f=1\text{KHz}, P_{in}=1\text{Pa}$	-46	-44	-42	dB 0dB=1V/Pa
Directivity		Omnidirectional				
Impedance	Zout				2.2	K Ω
Input sound Pressure level	S.P.L				100	dB
Operation voltage	Vs	-	1.0	2	10	V
Current consumption	I	$f=1\text{KHz}, P_{in}=1\text{Pa}$			500	μA
Sensitivity reduction	ΔS	$f=1\text{KHz}, P_{in}=1\text{Pa}$ $V_s=2 \rightarrow 1.5\text{V}$			-3	dB
S/N ratio	S/N(A)	$f=1\text{KHz}, P_{in}=1\text{Pa}$ A=curve	60			dB

Measurement Circuit (Test Condition $V_s=2\text{V}$ $R_L=2.2\text{K}\Omega$

$T_a=20^\circ\text{C}$ $R.H=65\%$)




Address:
Block 9, Shuiwei Ind Zone, Shuiwei New
Village, Dalang, Longhua, Shenzhen,
Guangdong, China 518109

Tel: (86)755-28121370/ 28121371/28109416/28109419
Fax: (86)755-28109417
E-mail: rd@horn.com.cn
Website: www.horn.com.cn


Dimensional Drawing

unit: mm



PART	MIN	STANDARD	MAX	REMARK
A	$\phi 5.9$	$\phi 6.0$	$\phi 6.1$	
B	1.4	1.5	1.6	
C	0.1	0.2	0.3	

Typical Frequency Response Curve



Address:
Block 9, Shuiwei Ind Zone, Shuiwei New
Village, Dalang, Longhua, Shenzhen,
Guangdong, China 518109

Tel: (86)755-28121370/ 28121371/28109416/28109419
Fax: (86)755-28109417
E-mail: rd@horn.com.cn
Website: www.horn.com.cn

Ambient condition

(1) Operating condition

Ambient temperature: $-10^{\circ}\text{C} \sim +45^{\circ}\text{C}$

Relative humidity: $\leq 85\%$

(2) Storage condition

Ambient temperature: $-20^{\circ}\text{C} \sim +60^{\circ}\text{C}$

Relative humidity: $45\% \sim 75\%$

Reliability Test

1) Vibration Test

To be no interference in operation after vibration of full amplitude 2mm for 30 minutes at three axis, the sensitivity to be within $\pm 3\text{dB}$ from initial sensitivity.

2) Drop Test

To be no interference in operation after dropped to concrete floor each time from 1 meter height of three directions in state of packing, the sensitivity to be within $\pm 3\text{dB}$ from initial sensitivity.

3) High Temperature Test

To be no interference in operation after high temperature test $70 \pm 3^{\circ}\text{C}$ for 48 hours, the sensitivity to be within $\pm 3\text{dB}$ from initial sensitivity.

4) Isotherm & Iso-humidity Test

To be no interference in operation after storage test at temperature $60 \pm 2^{\circ}\text{C}$ and relative humidity $(93 \pm 3\%)$ for 48 hours, the sensitivity to be within $\pm 3\text{dB}$ from initial sensitivity. the test is performed at temperature 20°C after operation for 6 hours.

5) Low Temperature Test

To be no interference in operation after high temperature test $-20 \pm 3^{\circ}\text{C}$ for 48 hours, the sensitivity to be within $\pm 3\text{dB}$ from initial sensitivity.

6) Temperature Cycle Test

After exposure at $+55 \pm 2^{\circ}\text{C}$ for 1 hour, at $20 \pm 2^{\circ}\text{C}$ for 1 hour, at $-10 \pm 2^{\circ}\text{C}$ for 1 hour, at $20 \pm 2^{\circ}\text{C}$ for 1 hour, with 5 cycles. Change of sensitivity within $\pm 3\text{dB}$ from initial measuring should be done after 2 hours exposed to $20 \pm 2^{\circ}\text{C}$.

7) Collision Test

After collided with the acceleration $100 \pm 10\text{m/s}^2$, at the vertical & horizontal directions for 1000 ± 10 times, at the state of packing. Change of sensitivity within $\pm 3\text{dB}$ from initial.




Electret Condenser Microphone Units

深圳市豪恩电声科技有限公司
SHENZHEN HORN ELECTROACOUSTIC TECHNOLOGY CO.,LTD

TEST RESULT OF SAMPLES

NO.	1KHz (dB)	CURRENT (mA)	NOTES
1	-43.7	0.1	(1KHz、0dB=1V/Pa)
2	-44.4	0.1	
3	-43.7	0.1	
4	-44.3	0.12	
5	-44.4	0.11	
6	-44.2	0.12	
7	-44.1	0.11	
8	-44.5	0.11	
9	-44	0.1	
10	-44.3	0.1	
11	-44	0.13	
12	-44.3	0.11	
13	-43.5	0.11	
14	-44.1	0.1	
15	-43.7	0.14	



Customer: Digi-Key Corporation

Date: 2003.12.09


Part number: EM6015-44BC10&33

Sensitivity: -44±2dB

Test condition: 2.2K Ω 2V

Tester: G1

SHENZHEN HORN ELECTROACOUSTIC TECHNOLOGY CO.,LTD.
 X:1.000kHz *Y:-44.53dB* ZA:Live Curve SSR Fund.



MODEL: EM6015-44BC10&33
 CODE: 5#
 SENSITIVITY: -44.53dB (1kHz)
 TEST CONDITION: 2.2KΩ 2V

09-DEC-2003 09:41:33

Mode: SSR





Electret Condenser Microphone Units

深圳市豪恩电声科技有限公司

SHENZHEN HORN ELECTROACOUSTIC TECHNOLOGY CO., LTD

TEL: 86-755-28121370/28121371/28109416/28109419

FAX: 86-755-28109417

Website: www.horn.com.cn

E-mail: rd@horn.com.cn

Certificate of Confirmed Products

Date: Dec. 07. 2003

NO: W031206007

SUPPLIER	HORN	BUYER	Digi-Key Corporation	
TITLE	ECM	MODEL	EM6015-44BC10&33	
SIZE	$\phi 6.0 \times 1.5\text{mm}$	TEST CONDITION	2.2K Ω 2V	
QUANTITY		SAMPLE: 15PCS		
SPECIFICATIONS				
Sensitivity		$-44 \pm 2\text{dB}$ (0dB=1V/Pa. 1KHz)		
Directivity		Omnidirectional		
Impedance		Low impedance		
Standard operation voltage		2V		
Operation voltage		1.0-10V		
Current consumption		Max 500uA		
Maximum input S.P.L		100dB		
S/N ratio		More than 60 dB		
Sensitive reduction		within-3dB at 1.5V		
The test result from customers		Signature: _____ . _____ . 2003		
Final confirmed	Pass	Refuse	Accepted basis on	
Remarks				

***** The form must be confirmed by return fax after your test as your best regards! *****