


	10	9	8	7	6	5	4	3	2	19073
	MATERIAL NUMBER	ENG. NO.	MATERIAL NUMBER TAPE MOUNTED	ENG. NO.	STUD SIZE	"S" ±.005	"W" MAX	"C" MIN	"L" MAX	
F	190730081	BB-837-04	-----	-----	04	.119 (3.02)	.322 (8.18)	.285 (7.24)	.885 (22.48)	
	190730083	BB-837-06	190730084	BB-837-06T	06	.146 (3.71)				
	190730085	BB-837-08	190730086	BB-837-08T	08	.173 (4.39)				
	190730087	BB-837-10	190730088	BB-823-10T	10	.198 (5.03)				
E	190730302	BB-839-06	190730093	BB-839-06T	06	.146 (3.71)	.352 (8.94)	.310 (7.87)	.936 (23.77)	
	190730094	BB-839-08	190730096	BB-839-08T	08	.173 (4.39)				
	190730097	BB-839-10	190730099	BB-839-10T	10	.198 (5.03)				



SALES DRAWING

- NOTES:
1. MATERIAL: COPPER (.031/0.79) THICK
PLATING: ELECTROPLATE TIN
 2. FERRULE: TIN-PLATED BRASS
 3. INSULATION: BLUE NYLON
 4. MWID=MAXIMUM WIRE INSULATION DIA.
 5. ALL DIMENSIONS IN INCHES (MM).
 6. WIRE SIZE: 16-14 AWG
1.0-2.5 MM²

EC NO: ETC2004-0123 DRWN:DMYRICK 2004/01/05 CHKD:SBEITZEL 2004/01/05 APPR:RDEROSS 2004/01/06		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 4:1	DESIGN UNITS INCH		THIRD ANGLE PROJECTION	REVISE ON CAD ONLY			
			 = 0  = 0	mm	INCH	DIMENSION STYLE		TITLE					
						IN/MM		RING TONGUE TERMINAL AVIKRIMP, 800-SERIES 16-14 AWG					
				4 PLACES ± --- ± ---		DRAWN BY	DATE	 MOLEX INCORPORATED					
3 PLACES ± --- ± .005		DMYRICK	03/12/15										
B	REV		2 PLACES ± 0.13 ± .01		CHECKED BY	DATE	SEE CHART SD-19073-006						
			1 PLACE ± 0.25 ± ---		SBEITZEL	03/12/15							
			ANGULAR ± 1 °		APPROVED BY	DATE	MATERIAL NO.	DOCUMENT NO.	SHEET NO.				
DRAFT WHERE APPLICABLE		RDEROSS	03/12/15	1 OF 1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
MUST REMAIN WITHIN DIMENSIONS													