



SCREW OPTIONS	L
FOR -1S	.188
FOR -2S	.250
FOR -3S	.438

SV P/N	DESCRIPTION	PCB THICKNESS
SF1211-66214-1S	INCL. TWO .188 SCREWS	.005 TO .123
SF1211-66214-2S	INCL. TWO .250 SCREWS	.060 TO .185
SF1211-66214-3S	INCL. TWO .438 SCREWS	.248 TO .373
SF1211-66214	NO SCREWS	.005 TO .373

MATERIAL:

BODIES & SCREWS: STAINLESS STEEL

CONTACT: BERYLLIUM COPPER

INSULATOR: PTFE

FINISHES

BODIES & SCREWS: PASSIVATED

CONTACT: GOLD OVER NICKEL

MATERIAL:	SEE NOTES
FINISH:	SEE NOTES
SURFACE AREA:	N/A
PROPRIETARY	

DIMENSIONS ARE IN INCHES TOLERANCES
 FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm X'X''^\circ$
 DECIMAL: $X \pm .030$
 $.XX \pm .010$
 $.XXX \pm .005$

INTERPRET DIMENSIONS AND TOLERANCES

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS)
2) ALL DIMENSIONS ARE AFTER PLATING.
3) BREAK CORNERS & EDGES .005 R. MAX.
4) CHM. IS TO LAST THREADS.
5) SURFACE ROUGHNESS 63 MIL-STD-10.
6) DIA'S ON COMMON CENTERS TO BE CONCENTRIC
WITHIN .005 IN.
7) REMOVE ALL PUPS.

 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409				
TITLE:	SMP QB JACK 2 HOLE FLANGE WITH MOUNTING SCREWS			
	16			
16	SIZE	CAGE CODE	DWG. NO.	SF1211-66214-XS
16	B	95077		
	SCALE: 10:1			SHEET 1 OF